

# Optocoupler



## PRODUCT CERTIFICATE

No.: CQC08001024729

### NAME AND ADDRESS OF THE APPLICANT

Vishay Semiconductor Malaysia Sdn Bhd  
No. 1710-1, Kawasan Perindustrian Krubong75250 Melaka

### NAME AND ADDRESS OF THE MANUFACTURER

Vishay Semiconductor Malaysia Sdn Bhd  
No. 1710-1, Kawasan Perindustrian Krubong75250 Melaka

### NAME AND ADDRESS OF THE FACTORY

Vishay Semiconductor Malaysia Sdn Bhd(V002589)  
No. 1710-1, Kawasan Perindustrian Krubong75250 Melaka

### NAME, MODEL AND SPECIFICATION

Opto Couplers

Refer to annex, Reinforced Insulation, Altitude up to 5000m, ext.cr>7.5mm, dti≥0.4mm, Thermal Cycling test passd

### THE STANDARDS AND TECHNICAL REQUIREMENTS FOR THE PRODUCTS

GB8898-2011

### CERTIFICATION MODEL

Type Testing of Product + Initial Factory Inspection + Follow up Factory Inspection

This is to certify that the above mentioned products have met the requirements of certification rules CQC11-471543-2012.

Date of issue: Apr.01,2014

Validity of this certificate is subject to positive result of the regular follow up inspection by issuing certification body until the expiry date.

Date of original certification: Nov.24,2008

President:

  
Wang Kejiao



## CHINA QUALITY CERTIFICATION CENTRE

Section 9, No.188, Nansihuan Xilu, Beijing 100070 P.R.China  
<http://www.cqc.com.cn>

C 0054786



# 产品认证证书

证书编号: CQC08001024729

## 申请人名称及地址

威旭半导体马来西亚有限公司  
No. 1710-1, Kawasan Perindustrian Krubong75250 Melaka 马来西亚

## 制造商名称及地址

威旭半导体马来西亚有限公司  
No. 1710-1, Kawasan Perindustrian Krubong75250 Melaka 马来西亚

## 生产企业名称及地址

威旭半导体马来西亚有限公司 (V002589)  
No. 1710-1, Kawasan Perindustrian Krubong75250 Melaka 马来西亚

## 产品名称和系列、规格、型号

光电耦合器

见附表, 加强绝缘, 外部爬电距离 $>7.5\text{mm}$ , 绝缘穿透距离 $\geq 0.4\text{mm}$ , 通过热循环测试, 适用于海拔5000米及以下

## 产品标准和技术要求

GB8898-2011

## 认证模式

产品型式试验+初次工厂检查+获证后监督

上述产品符合CQC11-471543-2012认证规则的要求, 特发此证。

发证日期: 2014年04月01日

证书有效期内本证书的有效性依据发证机构的定期监督获得保持

本证书为变更证书, 证书首次颁发日期: 2008年11月24日

主任: \_\_\_\_\_



# 中国质量认证中心

中国·北京·南四环西路188号9区100070

<http://www.cqc.com.cn>

C 0054786



# 产品认证证书

附录:

证书编号: CQC08001024729

第 1 页 共 1 页

纸号: 54786

型号:

SFH1617A-#XXXX、SFH1617A-#XXXXT、SFH6106-#XXXX、SFH6106-#XXXXT、SFH610A-#XXXX、SFH610A-#XXXXT、SFH655A-#XXXX、SFH655A-#XXXXT、SFH6156-#XXXX、SFH6156-#XXXXT、SFH615A-#XXXX、SFH615A-#XXXXT、SFH617A-#XXXX、SFH617A-#XXXXT、SFH6186-#XXXX、SFH6186-#XXXXT、SFH618A-#XXXX、SFH618A-#XXXXT、SFH619A-#XXXX、SFH619A-#XXXXT

注: 型号中的变量“#”代表CTR等级代码, 可能为字母A-Z或者数字0-9或空白的组合; “XXXX”代表封装形式和VDE局部放电或是客户的代号, 可能为字母A-Z或者数字0-9或空白的组合。T表示包装方式, 可以是编带和卷轴, 如是料管包装, T为空白。

注: 此附录与证书同时使用时有效。

主任: \_\_\_\_\_



## 中国质量认证中心

中国·北京·南四环西路188号9区100070

<http://www.cqc.com.cn>