

High Voltage Power Capacitors

BUSHINGS

Porcelain bushings for indoor and outdoor

| TYPE | IMPULSE WITHSTAND BIL (kV) | MIN. CREEPAGE (mm) | INSTALLATION | HEIGHT (mm) | THREAD | MAX. TORQUE N/m |
|-------|----------------------------|--------------------|--------------|-------------|--------|-----------------|
| D-199 | 75 | 189 | Indoor | 159 | M12 | 20 |
| D-401 | 95 | 317 | In / outdoor | 240 | M16 | 40 |
| D-404 | 125 | 472 | In / outdoor | 270 | M16 | 40 |
| D-406 | 150 | 658 | In / outdoor | 290 | M16 | 40 |
| D-341 | 170 | 810 | In / outdoor | 415 | M16 | 40 |

DRAWINGS OF BUSHINGS

