



CERTIFICATE OF PRODUCT CERTIFICATION

CERTIFICATE NO.: CQC07001021280

Valid from: Jul.26,2024

Valid until:long-term

NAME AND REGISTERED ADDRESS OF THE APPLICANT VISHAY CAPACITORS BELGIUM NV
Kwadestraat 151a- Box 12 B-8800, Roeselare, Belgium

NAME AND REGISTERED ADDRESS OF THE MANUFACTURER VISHAY CAPACITORS BELGIUM NV
Kwadestraat 151a- Box 12 B-8800, Roeselare, Belgium

NAME AND LOCATION OF THE FACTORY Vishay Components India Private Limite
Loni-Kahlbor, Near Pune, PUNE 412201, INDIA

PRODUCT NAME, MODEL AND SPECIFICATION Fixed capacitors for electromagnetic interference suppression and connection to the supply mains
336 2 310V~ X2, 1nF~4.7µF 055/110/56/B

THE STANDARDS AND TECHNICAL REQUIREMENTS FOR THE PRODUCTS GB/T 6346.14-2023

TYPE OF CERTIFICATION SCHEMES type test+follow up factory inspection

This is to certify that the above mentioned product(s) complies with the requirements of certification rules of CQC11-471115-2023.

Date of original issued: Sep.21,2007

The validity of the certificate is subject to positive result of the regular follow up inspection by issuing certification body.

The certificate information is available through the QR code below or CNCA's website: www.cnca.gov.cn



SIGNATURE:



中国质量认证中心
CHINA QUALITY CERTIFICATION CENTRE



CHINA QUALITY CERTIFICATION CENTRE CO., LTD.
Section 9, No. 188, Nansihuan Xilu, Beijing 100070 P. R. China

Tel: +86 10 83886666
http://www.cqc.com.cn