



### CERTIFICATE OF PRODUCT CERTIFICATION

CERTIFICATE NO.: CQC15001128762

Valid from: Nov.09,2023

Valid until:long-term

**NAME AND REGISTERED ADDRESS OF THE APPLICANT** Vishay Electronica Portugal, LDA  
Rua Magalhaes Lima 256 ,4760-363, Vila Nova de Famalicao, Portugal

**NAME AND REGISTERED ADDRESS OF THE MANUFACTURER** Vishay Electronica Portugal, LDA  
Rua Magalhaes Lima 256 ,4760-363, Vila Nova de Famalicao, Portugal

**NAME AND LOCATION OF THE FACTORY** Vishay Components India Private Limited  
Loni - Kahlbor, Near Pune, Pune 412201, India

**PRODUCT NAME, MODEL AND SPECIFICATION** Fixed capacitors for electromagnetic interference suppression and connection to the supply mains  
See Appendix

**THE STANDARDS AND TECHNICAL REQUIREMENTS FOR THE PRODUCTS** IEC60384-14:2013+AMD1:2016

**TYPE OF CERTIFICATION SCHEMES** Type Testing of Product + Follow up Factory Inspection

This is to certify that the above mentioned product(s) complies with the requirements of certification rules of CQC11-471112-2015.

Date of original issued: Aug.05,2015

The validity of the certificate is subject to positive result of the regular follow up inspection by issuing certification body.

The certificate information is available through the QR code below or CNCA's website: www.cnca.gov.cn



SIGNATURE:



CHINA QUALITY CERTIFICATION CENTRE



http://www.cqc.com.cn

Section 9, No.188, Nansihuan Xilu, Beijing 100070 P.R.China

Tel: +86 10 83886666



**CERTIFICATE OF PRODUCT CERTIFICATION**


CERTIFICATE NO. : CQC15001128762

page 1 of 1

paper:

This certificate and attachments shall be used at the same time, and the verification instructions can be found in the main certificate.

F340Y2 Y2 305VAC 0.001 $\mu$ F ~1 $\mu$ F 55/105/56C(<1750mm<sup>3</sup>) or 55/105/56B( $\geq$ 1750mm<sup>3</sup>) III B



**CHINA QUALITY CERTIFICATION CENTRE**

<http://www.cqc.com.cn>

Section 9, No.188, Nansihuan Xilu, Beijing 100070 P.R.China

Tel: +86 10 83886666