


Mounting Accessories For Wirewound Resistors Equipped with B Bands Suitable for RW - RA Models




FEATURES


- These flexible clips, of special alloy, provide effective protection against corrosion and extreme working temperatures. 
- The stainless steel clip-tightener SC increases fixing stability and improves electrical contact.
- The PC clip-holders are ceramic blocks drilled with 3 threaded holes and guarantee an insulation voltage greater than 10 000 V_{RMS}.
- They can be fitted with 6 types of clip and are supplied unassembled, with a packet containing connecting lugs, screws, washers and rubber wedges.

DIMENSIONS in millimeters


CL CLIPS



SC CLIP-TIGHTNERS



PC CLIP-HOLDERS



MODEL	STYLE	TYPE	A	B ± 0.5	D	E ± 0.2	J ± 1	L - 0 - 4	M - 0 - 4	P ± 0.3	WEIGHT IN g
RW	10 x 50	CL 10	25	10.5	16	4.2	18	57	46.5	2.6	5
RA RW	13 x 70	CL 13	30	12.5	18	4.2	24	76	63.5	2	6
RA RW	16 x 94	CL 16	36	14	23	4.2	25	101	87	2.5	10
RA RW	20 x 117	CL 20	43	16	27	4.2	28	123	107	2	13
RA	25 x 138	CL 25	46	17	32	4.2	32	144	127	2	20
RA	25 x 168	CL 25	46	17	32	4.2	32	174	157	2	20
RA	30 x 250	CL 30	51	20	38	5.2	38	258	238	2.5	25



DIMENSIONS in millimeters					
MODEL	STYLE	TYPE	G	N ± 0.2	WEIGHT IN g
RW	10 x 50	SC 10	18 ± 1	4	0.6
RA RW	13 x 70	SC 13	25 ± 1	5	1.2
RA RW	16 x 94	SC 16	25 ± 1	5	1.2
RA RW	20 x 117	SC 20	29 ± 1	5.5	1.5
RA	25 x 138	SC 25	35 ± 1.5	6	2.2
RA	25 x 168	SC 25	35 ± 1.5	6	2.2
RA	30 x 250	SC 30	41 ± 1.5	7	3.5

ORDERING INFORMATION					
	MODEL	TYPE	SPECIAL	PAIR	LEAD (PB)-FREE
For special "electrical traction" resistors (SNCF), quote: CL: BB1 PC: BA9	CL = CLIP CLIP CLIP	10	XXX	...	e

Note

- Clips are sold in pairs

SAP PART NUMBERING GUIDELINES		
ACCRF MODEL	CL STYLE	10 TYPE