


## Carrier Tape for WCSP16, 0.35 mm Pitch, 4 x 4 Array



Version	A <sub>0</sub>	B <sub>0</sub>	K <sub>0</sub>
-1	1.57 ± 0.05	1.57 ± 0.05	0.76 ± 0.05

### Notes

1. 10 sprocket hole pitch cumulative tolerance ± 0.2 mm.
2. Camber in compliance with EIA 481.
3. Pocket position relative to sprocket hole measured as true position of pocket, not pocket hole.
4. Material: PS and C.
5. All sizes in mm unless specified.
6. Surface resistivity -10<sup>5</sup> max. Ω/sq.

T14-0021-Rev. A  
DWG: 93-5323-X