

Custom Capabilities RF Power Barrel Capacitors



OVERALL CAPABILITIES

- Production in Germany
- High quality, service, and flexibility
- ISO 9001, OHSAS 18001, environmental 14001 qualified
- STEP files available
- Operating temperature range -55 °C to +85 °C

MATERIAL / PROCESS CAPABILITIES

- Wide range of capacitance values
- Selection of different class 1 and class 2 ceramics
- Numerous shapes and sizes available
- Fittings specifically designed for your application
- Lead (Pb)-free available

FITTING EXAMPLES



Screw terminal
(metric and UNF/UNC thread available)
for series 5FF, 5FG, and 5FH



Axial wire lead
for series 5FC, 5FD, and 5FE



Screw terminal with hexagon
(metric and UNF/UNC thread available)
for series 5FAE, 7FAA, and 7FAU

CONTACT INFORMATION

For design assistance, contact: powcap@vishay.com

Design request form: www.vishay.com/capacitors/ceramic/rf-barrel/

ORDERING CODE

7F	A	A	500	K	-R
SERIES RATED VOLTAGE	BODY STYLE	CERAMIC DIELECTRIC	C-VALUE	TOLERANCE	LEAD (Pb)-FREE
5F = 5 kV - series 7F = 7.5 kV - series	Depend on the fittings and diameter	Examples: A = NP0 U = N750	Examples: 500 = 50 pF 9R0 = 9 pF	K = 10 % J = 5 %	



ADDITIONAL CAPABILITIES EXAMPLES

TOS 030033

(www.vishay.com/doc?22129)



TOS 020016

(www.vishay.com/doc?22086)



TOF 016010, TOS 016010, TOF 025016, TOS 025016

(www.vishay.com/doc?22085)



ADDITIONAL CUSTOM EXAMPLES

TOS 0057



TOZ 045033



With many years of experience in the development, we can find the best solution for your project together!



Disclaimer

ALL PRODUCT, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE TO IMPROVE RELIABILITY, FUNCTION OR DESIGN OR OTHERWISE.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product.

Vishay makes no warranty, representation or guarantee regarding the suitability of the products for any particular purpose or the continuing production of any product. To the maximum extent permitted by applicable law, Vishay disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Statements regarding the suitability of products for certain types of applications are based on Vishay's knowledge of typical requirements that are often placed on Vishay products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. Parameters provided in datasheets and / or specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein.

Hyperlinks included in this datasheet may direct users to third-party websites. These links are provided as a convenience and for informational purposes only. Inclusion of these hyperlinks does not constitute an endorsement or an approval by Vishay of any of the products, services or opinions of the corporation, organization or individual associated with the third-party website. Vishay disclaims any and all liability and bears no responsibility for the accuracy, legality or content of the third-party website or for that of subsequent links.

Except as expressly indicated in writing, Vishay products are not designed for use in medical, life-saving, or life-sustaining applications or for any other application in which the failure of the Vishay product could result in personal injury or death. Customers using or selling Vishay products not expressly indicated for use in such applications do so at their own risk. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay. Product names and markings noted herein may be trademarks of their respective owners.