

## High Current, Through-Hole Inductor Edge-Wound Series



### APPLICATIONS

- High current and high temperature applications
- DC/DC converters
- High current differential mode chokes
- Inverters

### FEATURES

- High temperature continuous operation, up to 180 °C with no aging
- Low DCR to minimize losses and reduce temperature rise
- Powdered iron alloy core technology provides stable inductance and saturation over operating temperature with satisfactory core losses
- Soft saturation gives predictable inductance decrease with increasing DC current independent of temperature
- Series includes multiple powdered iron core materials for optimized performance in circuit application
- Standard terminal stripped and tinned for through hole mounting but other terminal configurations such as bare copper, SMD, and press fit pin are available upon request
- Hot dipped Sn plating provides low risk of whisker growth
- Custom options are available
- Material categorization: for definitions of compliance please see [www.vishay.com/doc?99912](http://www.vishay.com/doc?99912)



**RoHS**  
COMPLIANT  
HALOGEN  
**FREE**  
**GREEN**  
(5-2008)

### STANDARD ELECTRICAL SPECIFICATIONS


PART NUMBER	L <sub>0</sub> INDUCTANCE ± 20 % AT 100 kHz, 0.25 V, 0 A (μH)	DCR AT 25 °C		HEAT RATING CURRENT DC TYP. <sup>(1)</sup> (A)	SATURATION CURRENT DC		SRF TYP. (MHZ)	DIMENSION	
		TYP. (mΩ)	MAX. (mΩ)		TYP. <sup>(2)</sup> (A)	TYP. <sup>(3)</sup> (A)		A ± 0.4 [mm]	B ± 0.5 [mm]
<b>BEST BALANCE OF CORE LOSS AND SATURATION</b>									
IHDM1008BCEV1R3M20	1.3	0.40	0.48	84	201	259	95	2.6	14.5
IHDM1008BCEV2R2M20	2.2	0.63	0.70	63	158	204	69	2.0	15.0
IHDM1008BCEV3R0M20	3.0	0.86	0.95	57	131	169	48	1.8	15.2
IHDM1008BCEV4R3M20	4.3	1.00	1.15	51	110	142	37	1.6	15.4
IHDM1008BCEV5R6M20	5.6	1.35	1.50	45	97	125	34	1.4	15.6
IHDM1008BCEV6R8M20	6.8	1.70	2.00	37	85	110	30	1.2	15.9
<b>LOWEST CORE LOSS</b>									
IHDM1008BCEV1R2M30	1.2	0.25	0.30	100	157	205	91	3.2	13.8
IHDM1008BCEV2R2M30	2.2	0.40	0.48	85	132	168	70	2.6	14.5
IHDM1008BCEV3R3M30	3.3	0.63	0.70	70	90	116	43	2.0	15.0
IHDM1008BCEV4R7M30	4.7	0.86	0.95	62	78	100	35	1.8	15.2
IHDM1008BCEV6R8M30	6.8	1.00	1.15	55	64	83	29	1.6	15.4
IHDM1008BCEV8R2M30	8.2	1.35	1.50	48	56	71	24	1.4	15.6
IHDM1008BCEV100M30	10	1.70	2.00	40	53	68	22	1.2	15.9

### Notes

- The -20 series provides a good balance between core losses, saturation current, and high frequency stability up to 800 kHz
  - The -30 series provides lower core losses with slightly lower saturation current
  - All test data is referenced to 25 °C ambient
  - Operating temperature range -40 °C to +180 °C
  - The part temperature (ambient + temp. rise) should not exceed 180 °C under worst case operating conditions. Circuit design, component placement, PWB trace size and thickness, airflow and other cooling provisions all affect the part temperature. Part temperature should be verified in the end application
  - Isolation voltage, coil to core: 350 V<sub>DC</sub>, 60 s, 5 mA max.
- (1) DC current (A) that will cause an approximate ΔT of 40 °C  
 (2) DC current (A) that will cause L<sub>0</sub> to drop approximately 20 %  
 (3) DC current (A) that will cause L<sub>0</sub> to drop approximately 30 %




**DIMENSIONS** in inches (millimeters)



**DESCRIPTION**









IHDM-1008BC-30	1.2 $\mu$ H	$\pm 20\%$	EV	e3
MODEL	INDUCTANCE	INDUCTANCE TOLERANCE	PACKAGE	JEDEC® LEAD (Pb)-FREE STANDARD

**GLOBAL PART NUMBER**










PERFORMANCE GRAPHS













PERFORMANCE GRAPHS










PERFORMANCE GRAPHS: INDUCTANCE AND Q VS. FREQUENCY





PERFORMANCE GRAPHS: INDUCTANCE AND Q VS. FREQUENCY





## Disclaimer

ALL PRODUCT, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE TO IMPROVE RELIABILITY, FUNCTION OR DESIGN OR OTHERWISE.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product.

Vishay makes no warranty, representation or guarantee regarding the suitability of the products for any particular purpose or the continuing production of any product. To the maximum extent permitted by applicable law, Vishay disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Statements regarding the suitability of products for certain types of applications are based on Vishay's knowledge of typical requirements that are often placed on Vishay products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. Parameters provided in datasheets and / or specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein.

Hyperlinks included in this datasheet may direct users to third-party websites. These links are provided as a convenience and for informational purposes only. Inclusion of these hyperlinks does not constitute an endorsement or an approval by Vishay of any of the products, services or opinions of the corporation, organization or individual associated with the third-party website. Vishay disclaims any and all liability and bears no responsibility for the accuracy, legality or content of the third-party website or for that of subsequent links.

Except as expressly indicated in writing, Vishay products are not designed for use in medical, life-saving, or life-sustaining applications or for any other application in which the failure of the Vishay product could result in personal injury or death. Customers using or selling Vishay products not expressly indicated for use in such applications do so at their own risk. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay. Product names and markings noted herein may be trademarks of their respective owners.