



SMD Magnetics Packaging Methods

TAPE AND REEL in inches [millimeters] - meets EIA RS-481 and IEC 60286 tape and reel packaging standards


User Direction of Feed



Carrier Dimensions

MODEL	PACKAGE CODE			REEL SIZE	CARRIER TAPE WIDTH (W)	COMPONENT PITCH (P)	UNITS/ REEL	PACKAGE CODE			UNITS/ BULK
	PREVIOUS CODE	GLOBAL CODE LEAD (Pb)-BEARING	GLOBAL CODE LEAD (Pb)-FREE					PREVIOUS CODE	GLOBAL CODE LEAD (Pb)-BEARING	GLOBAL CODE LEAD (Pb)-FREE	
ICM-0805	-	-	ER	7	0.315 [8.0]	0.157 [4.0]	2000	-	-	-	-
ICM-1206	-	-	ER	7	0.315 [8.0]	0.157 [4.0]	2000	-	-	-	-
ICM-2824	-	-	ER	13	0.630 [16.0]	0.472 [12.0]	2000	-	-	-	-
ICM-3528	-	-	ER	13	0.945 [24.0]	0.472 [12.0]	900	-	-	-	-
ICM-4743	-	-	ER	13	0.945 [24.0]	0.630 [16.0]	500	-	-	-	-
IDC-2512	-	-	ER	13	0.630 [16.0]	0.315 [8.0]	2500	-	-	-	-
IDC-5020	-	-	ER	13	0.630 [16.0]	0.472 [12.0]	500	-	-	-	-
IDC-7328	-	-	ER	13	0.945 [24.0]	0.945 [24.0]	250	-	-	-	-
IDCP-1813	-	-	ER	13	0.472 [12.0]	0.315 [8.0]	2000	-	-	-	-
IDCP-2218	-	-	ER	13	0.472 [12.0]	0.315 [8.0]	1500	-	-	-	-
IDCP-3020	-	-	ER	13	0.630 [16.0]	0.472 [12.0]	1000	-	-	-	-
IDCP-3114	-	-	ER	13	0.630 [16.0]	0.472 [12.0]	1000	-	-	-	-
IDCP-3722	-	-	ER	13	0.945 [24.0]	0.472 [12.0]	1000	-	-	-	-
IDCP-3916	-	-	ER	13	0.945 [24.0]	0.472 [12.0]	1000	-	-	-	-
IDCS-2512	-	-	ER	13	0.630 [16.0]	0.315 [8.0]	2000	-	-	-	-
IDCS-5020	-	-	ER	13	0.630 [16.0]	0.472 [12.0]	500	-	-	-	-
IDCS-7328	-	-	ER	13	0.945 [24.0]	0.945 [24.0]	250	-	-	-	-
IFCB-0402	-	-	ER	7	0.315 [8.0]	0.079 [2.0]	10 000	-	-	-	-
IFDC-5050HZ	-	-	ER	13	0.945 [24.0]	0.630 [16.0]	500	-	-	-	-
IFLR-2727EZ	-	-	ER	13	0.630 [16.0]	0.630 [16.0]	1000	-	-	-	-
IFLR-4027EZ	-	-	ER	13	0.945 [24.0]	0.630 [16.0]	1000	-	-	-	-
IFLR-4031GC	-	-	ER	13	0.945 [24.0]	0.472 [12.0]	500	-	-	EB	100
IFLR-5151HZ	-	-	ER	13	0.945 [24.0]	0.630 [16.0]	450	-	-	EB	100
IFSC-0806AZ	-	-	ER	7	0.315 [8.0]	0.157 [4.0]	3000	-	-	-	-
IFSC-1008AB	-	-	ER	7	0.315 [8.0]	0.157 [4.0]	2000	-	-	-	-
IFSC-1111AB	-	-	ER	7	0.315 [8.0]	0.157 [4.0]	2000	-	-	-	-
IFSC-1111AZ	-	-	ER	7	0.315 [8.0]	0.157 [4.0]	2000	-	-	-	-
IFSC-1515AH	-	-	ER	13	0.472 [12.0]	0.315 [8.0]	2000	-	-	-	-
IFSC-2020DB-01	-	-	ER	13	0.630 [16.0]	0.472 [12.0]	1000	-	-	-	-
IFSC-3232DB-01	-	-	ER	13	0.630 [16.0]	0.472 [12.0]	1200	-	-	-	-
IHCL-4040DZ	-	-	ER	13	0.945 [24.0]	0.630 [16.0]	500	-	-	-	-
IHHP-0806AB-01	-	-	ER	7	0.315 [8.0]	0.157 [4.0]	2000	-	-	-	-
IHHP-0806AZ-01	-	-	ER	7	0.315 [8.0]	0.157 [4.0]	3000	-	-	-	-
IHHP-1008AB-01	-	-	ER	7	0.315 [8.0]	0.157 [4.0]	2000	-	-	-	-
IHHP-1008AZ-01	-	-	ER	7	0.315 [8.0]	0.157 [4.0]	3000	-	-	-	-
IHLD-2525GG	-	-	ER	13	0.630 [16.0]	0.630 [16.0]	250	-	-	-	-
IHLD-3232HB	-	-	ER	13	0.945 [24.0]	0.630 [16.0]	250	-	-	-	-
IHLD-4032KB	-	-	ER	13	0.945 [24.0]	0.630 [16.0]	250	-	-	-	-



TAPE AND REEL in inches [millimeters] - meets EIA RS-481 and IEC 60286 tape and reel packaging standards

MODEL	PACKAGE CODE			REEL SIZE	CARRIER TAPE WIDTH (W)	COMPONENT PITCH (P)	UNITS/ REEL	PACKAGE CODE			UNITS/ BULK
	PREVIOUS CODE	GLOBAL CODE LEAD (Pb)- BEARING	GLOBAL CODE LEAD (Pb)-FREE					PREVIOUS CODE	GLOBAL CODE LEAD (Pb)- BEARING	GLOBAL CODE LEAD (Pb)-FREE	
IHLE-2020CD	-	-	ER	13	0.472 [12.0]	0.315 [8.0]	2000	-	-	-	-
IHLE-2525CD	-	-	ER	13	0.630 [16.0]	0.472 [12.0]	1000	-	-	-	-
IHLE-3232DD	-	-	ER	13	0.630 [16.0]	0.472 [12.0]	500	-	-	-	-
IHLE-4040DD	-	-	ER	13	0.945 [24.0]	0.630 [16.0]	500	-	-	-	-
IHLE-5050FH	-	-	ER	13	0.945 [24.0]	0.630 [16.0]	500	-	-	-	-
IHLL-0805AZ-1Z	-	-	EZ	7	0.315 [8.0]	0.157 [4.0]	3000	-	-	-	-
IHLL-1008AB-1Z	-	-	EZ	7	0.315 [8.0]	0.157 [4.0]	3000	-	-	-	-
IHLL-1210AB-1Z	-	-	EZ	7	0.315 [8.0]	0.157 [4.0]	3000	-	-	-	-
IHLM-2525CZ	-	-	ER	13	0.630 [16.0]	0.315 [8.0]	2000	-	-	-	-
IHLP-0806AB-5A	-	-	EZ	7	0.315 [8.0]	0.157 [4.0]	3000	-	-	-	-
IHLP-1008ABEZ-5A	-	-	EZ	7	0.315 [8.0]	0.157 [4.0]	3000	-	-	-	-
IHLP-1210ABEZ-5A	-	-	EZ	7	0.315 [8.0]	0.157 [4.0]	3000	-	-	-	-
IHLP-1210BZEZ-5A	-	-	EZ	7	0.315 [8.0]	0.157 [4.0]	2000	-	-	-	-
IHLP-1212ABER	-	-	ER	13	0.472 [12.0]	0.315 [8.0]	3000	-	-	-	-
IHLP-1212ABEV	-	-	EV	13	0.472 [12.0]	0.315 [8.0]	4000	-	-	-	-
IHLP-1212AEER	-	-	ER	13	0.472 [12.0]	0.315 [8.0]	3000	-	-	-	-
IHLP-1212BZER	-	-	ER	13	0.472 [12.0]	0.315 [8.0]	3000	-	-	-	-
IHLP-1212BZEV	-	-	EV	13	0.472 [12.0]	0.315 [8.0]	4000	-	-	-	-
IHLP-1616AB	-	-	ER	13	0.472 [12.0]	0.315 [8.0]	4000	-	-	-	-
IHLP-1616BZ	-	-	ER	13	0.472 [12.0]	0.315 [8.0]	4000	-	-	-	-
IHLP-2020AB	-	-	ER	13	0.472 [12.0]	0.315 [8.0]	4000	-	-	-	-
IHLP-2020BZ	-	-	ER	13	0.472 [12.0]	0.315 [8.0]	2000	-	-	-	-
IHLP-2020CZ	-	-	ER	13	0.472 [12.0]	0.315 [8.0]	2000	-	-	-	-
IHLP-2525AH	-	-	ER	13	0.630 [16.0]	0.315 [8.0]	2000	-	-	-	-
IHLP-2525BD	-	-	ER	13	0.630 [16.0]	0.315 [8.0]	2000	-	-	-	-
IHLP-2525CZ	-	-	ER	13	0.630 [16.0]	0.315 [8.0]	2000	-	-	-	-
IHLP-2525EZ	-	-	ER	13	0.630 [16.0]	0.472 [12.0]	500	-	-	-	-
IHLP-3232CZ	-	-	ER	13	0.630 [16.0]	0.472 [12.0]	1000	-	-	-	-
IHLP-3232DZ	-	-	ER	13	0.630 [16.0]	0.472 [12.0]	500	-	-	-	-
IHLP-4040DZ	-	-	ER	13	0.945 [24.0]	0.630 [16.0]	500	-	-	-	-
IHLP-4040DZ	-	-	EK	13	0.945 [24.0]	0.472 [12.0]	1000	-	-	-	-
IHLP-4040DZ	-	-	EP	13	0.945 [24.0]	0.472 [12.0]	1000	-	-	-	-
IHLP-4040ED	-	-	ER	13	0.945 [24.0]	0.630 [16.0]	500	-	-	-	-
IHLP-5050CE	-	-	ER	13	0.945 [24.0]	0.630 [16.0]	500	-	-	-	-
IHLP-5050EZ	-	-	ER	13	0.945 [24.0]	0.630 [16.0]	250	-	-	-	-
IHLP-5050FD	-	-	ER	13	0.945 [24.0]	0.630 [16.0]	250	-	-	-	-
IHLP-6767DZ	-	-	ER	13	1.26 [32.0]	0.945 [24.0]	250	-	-	-	-
IHLP-6767GZ	-	-	ER	13	1.26 [32.0]	0.945 [24.0]	200	-	-	-	-
IHLP-7575GZ	-	-	ER	13	1.26 [32.0]	0.945 [24.0]	200	-	-	-	-
IHLP-8787MZ	-	-	ER	13	1.73 [44.0]	1.26 [32.0]	100	-	-	-	-
IHLW-4040CF	-	-	ER	13	0.945 [24.0]	0.630 [16.0]	500	-	-	-	-
IHLW-5050CE	-	-	ER	13	0.945 [24.0]	0.630 [16.0]	500	-	-	-	-
IHSM-3825	RC2	RE	ER	13	0.945 [24.0]	0.472 [12.0]	750	P09	PJ	EB	100
IHSM-4825	RC2	RE	ER	13	0.945 [24.0]	0.472 [12.0]	750	P09	PJ	EB	100
IHSM-5832	RC3	RF	ER	13	1.26 [32.0]	0.472 [12.0]	500	P09	PJ	EB	100
IHSM-7832	RC4	RG	ER	13	1.73 [44.0]	0.472 [12.0]	500	P09	PJ	EB	100



TAPE AND REEL in inches [millimeters] - meets EIA RS-481 and IEC 60286 tape and reel packaging standards

MODEL	PACKAGE CODE			REEL SIZE	CARRIER TAPE WIDTH (W)	COMPONENT PITCH (P)	UNITS/ REEL	PACKAGE CODE			UNITS/ BULK
	PREVIOUS CODE	GLOBAL CODE LEAD (Pb)- BEARING	GLOBAL CODE LEAD (Pb)-FREE					PREVIOUS CODE	GLOBAL CODE LEAD (Pb)- BEARING	GLOBAL CODE LEAD (Pb)-FREE	
IHSR-1616AB	-	-	ER	13	0.472 [12.0]	0.315 [8.0]	4000	-	-	-	-
IHSR-2525CZ	-	-	ER	13	0.630 [16.0]	0.315 [8.0]	2000	-	-	-	-
IHSR-4040DZ	-	-	ER	13	0.945 [24.0]	0.472 [12.0]	1000	-	-	-	-
IHSR-6767GZ	-	-	ER	13	1.26 [32.0]	0.945 [24.0]	200	-	-	-	-
IHVR-4025JZ	-	-	EZ	13	0.945 [24.0]	0.472 [12.0]	500	-	-	-	-
ILAS-1206	-	-	ER	7	0.315 [8.0]	0.157 [4.0]	3000	-	-	-	-
ILB-1206	-	-	ER	7	0.315 [8.0]	0.157 [4.0]	3000	-	-	-	-
ILBB-0402	-	-	ER	7	0.315 [8.0]	0.079 [2.0]	10 000	-	-	-	-
ILBB-0603	-	-	ER	7	0.315 [8.0]	0.157 [4.0]	4000	-	-	-	-
ILBB-0805	-	-	ER	7	0.315 [8.0]	0.157 [4.0]	4000	-	-	-	-
ILBB-1210	-	-	ER	7	0.315 [8.0]	0.157 [4.0]	2000	-	-	-	-
ILBB-1806	-	-	ER	7	0.472 [12.0]	0.157 [4.0]	2000	-	-	-	-
ILBB-1812	-	-	ER	7	0.472 [12.0]	0.315 [8.0]	1000	-	-	-	-
ILC-0402	-	-	ER	7	0.315 [8.0]	0.079 [2.0]	10 000	-	-	-	-
ILC-0603	-	-	ER	7	0.315 [8.0]	0.157 [4.0]	4000	-	-	-	-
ILC-0805	-	-	ER	7	0.315 [8.0]	0.157 [4.0]	4000	-	-	-	-
ILHB-0603	-	-	ER	7	0.315 [8.0]	0.157 [4.0]	4000	-	-	-	-
ILHB-0805	-	-	ER	7	0.315 [8.0]	0.157 [4.0]	4000	-	-	-	-
ILHB-1206	-	-	ER	7	0.315 [8.0]	0.157 [4.0]	3000	-	-	-	-
ILHB-1806	-	-	ER	7	0.315 [8.0]	0.157 [4.0]	2000	-	-	-	-
ILHB-1812	-	-	ER	7	0.315 [8.0]	0.157 [4.0]	1000	-	-	-	-
ILSB-0603	-	-	ER	7	0.315 [8.0]	0.157 [4.0]	4000	-	-	-	-
ILSB-0805 (0.047 µH to 2.2 µH)	-	-	ER	7	0.315 [8.0]	0.157 [4.0]	4000	-	-	-	-
ILSB-0805 (2.7 µH to 33 µH)	-	-	ER	7	0.315 [8.0]	0.157 [4.0]	3000	-	-	-	-
ILSB-1206	-	-	ER	7	0.315 [8.0]	0.157 [4.0]	3000	-	-	-	-
IMC-0402	-	-	ER	7	0.315 [8.0]	0.079 [2.0]	10 000	-	-	-	-
IMC-0402-01	-	-	ER	7	0.315 [8.0]	0.079 [2.0]	10 000	-	-	-	-
IMC-0603	-	-	ER	7	0.315 [8.0]	0.157 [4.0]	4000	-	-	-	-
IMC-0603-01	-	-	ER	7	0.315 [8.0]	0.079 [2.0]	3000	-	-	-	-
IMC-0805-01	-	-	ER	7	0.315 [8.0]	0.157 [4.0]	2000	-	-	-	-
IMC-1008	-	-	ER	7	0.315 [8.0]	0.157 [4.0]	2000	-	-	-	-
IMC-1210	R98/RB3 R99/RB4	SY/AN SZ/R9	ER/ET ES/EU	7 13	0.315 [8.0] 0.315 [8.0]	0.157 [4.0] 0.157 [4.0]	2000 7500	B13	BN	EB	500
IMC-1210-100	R98/RB3 R99/RB4	SY/AN SZ/R9	ER/ET ES/EU	7 13	0.315 [8.0] 0.315 [8.0]	0.157 [4.0] 0.157 [4.0]	2000 7500	B13	BN	EB	500
IMC-1812	R73/R92 R13/R91	RV/RX RQ/RW	ER/ET ES/EU	7 13	0.472 [12.0] 0.472 [12.0]	0.315 [8.0] 0.315 [8.0]	500 2000	B13	BN	EB	500
IMC-2220	-	-	ER	13	0.630 [16.0]	0.472 [12.0]	1000	-	-	-	-
IMCH-1812	-	-	ER	7	0.472 [12.0]	0.315 [8.0]	500	-	-	-	-
ISC-1008	-	-	ER	13	0.472 [12.0]	0.157 [4.0]	750	-	-	-	-
ISC-1210	R98/RB3 R99/RB4	SY/AN SZ/R9	ER/ET ES/EU	7 13	0.315 [8.0] 0.315 [8.0]	0.157 [4.0] 0.157 [4.0]	2000 7500	B13	BN	EB	500
ISC-1812	R73/R92 R13/R91	RV/RX RQ/RW	ER/ET ES/EU	7 13	0.472 [12.0] 0.472 [12.0]	0.315 [8.0] 0.315 [8.0]	500 2000	B13	BN	EB	500
LPE-3325	R94	RY	ER	13	0.945 [24.0]	0.472 [12.0]	1000	-	-	-	-



TAPE AND REEL in inches [millimeters] - meets EIA RS-481 and IEC 60286 tape and reel packaging standards											
MODEL	PACKAGE CODE			REEL SIZE	CARRIER TAPE WIDTH (W)	COMPONENT PITCH (P)	UNITS/ REEL	PACKAGE CODE			UNITS/ BULK
	PREVIOUS CODE	GLOBAL CODE LEAD (Pb)- BEARING	GLOBAL CODE LEAD (Pb)-FREE					PREVIOUS CODE	GLOBAL CODE LEAD (Pb)- BEARING	GLOBAL CODE LEAD (Pb)-FREE	
LPE-3325-CST	-	-	ER	13	0.945 [24.0]	0.472 [12.0]	1000	-	-	-	-
LPE-4841	R94	RY	ER	13	0.945 [24.0]	0.630 [16.0]	600	-	-	-	-
LPE-5047	R94	RY	ER	13	0.945 [24.0]	0.630 [16.0]	600	-	-	-	-
LPE-6562	R94	RY	ER	13	1.26 [32.0]	0.787 [20.0]	300	-	-	-	-
LPE-6855	R94	RY	ER	13	1.26 [32.0]	0.787 [20.0]	450	-	-	-	-
LPT-3535	RC5	RH	ER	13	0.945 [24.0]	0.630 [16.0]	600	-	-	-	-
LPT-4545	RC5	RH	ER	13	0.945 [24.0]	0.630 [16.0]	600	-	-	-	-