


ESCC (e) 4001/026 Qualified *R* Failure Rate High Precision Thick Film Chip Resistors



FEATURES

**HALOGEN
FREE**

- Load life stability at ± 70 °C for 2000 h: 2.5 % under P_n
- Temperature coefficient to: 100 ppm/°C
- HCHP option R0094: for high frequency applications (up to 10 GHz)
- Tolerances down to 1 %
- *R* failure rate (level E7)
- SMD wraparound chip resistor
- Generic specification ESCC 4001
- Detailed specification ESCC 4001/026
- Robust terminations
- Large ohmic value range 1 Ω to 10 M Ω
- ESCC (e) qualified
- Material categorization: for definitions of compliance please see www.vishay.com/doc?99912

LINKS TO ADDITIONAL RESOURCES




Vishay Sfernice thick film chip resistors CHPFR are specially designed to meet the requirements of the ESCC 4001/026 specification. They have undergone the CNES evaluation (Space French National Agency). They are in level 1 of the ESCC EPPL (European Preferred Part List) and ESCC qualified. At the end of production a 100 % overload screening is performed.

Thin film technology terminations, with nickel barrier, are very convenient for high operating conditions. They can withstand thousands of very severe thermal shocks.

- SnPb (W/A) terminations over nickel barrier for solder reflow (variant 11 to 15)
- Gold (W/A) terminations gold over nickel barrier for gluing (variant 16 to 20)

DIMENSIONS in millimeters





VARIANT NUMBER	STYLE	DIMENSIONS in millimeters									
		A		B		C		D		E	
		MIN.	MAX.	MIN.	MAX.	MIN.	MAX.	MIN.	MAX.	MIN.	MAX.
11, 16	0603	1.36	1.68	0.72	0.98	0.38	0.53	0.17	0.51	0.25	0.51
12, 17	0805 ⁽¹⁾	1.75	2.07	1.14	1.4	0.38	0.53	0.17	0.51	0.25	0.51
13, 18	1206	2.89	3.21	1.47	1.73	0.38	0.53	0.17	0.51	0.25	0.51
14, 19	2010	4.92	5.24	2.41	2.67	0.5	0.63	0.25	0.64	0.25	0.64
15, 20	2512	6.19	6.51	2.93	3.32	0.5	0.63	0.25	0.64	0.25	0.64

Note

⁽¹⁾ Model CHPFR0805 being same size than case 0705 with same performances, only codification of CHPFR0805 remains

CLIMATIC SPECIFICATIONS	
Operating temperature range	-55 °C; +155 °C
Soldering temperature (T_{sol})	Thick film (ruthenium oxyde)

MECHANICAL SPECIFICATIONS	
Substrate	Alumina
Technology	Thick film (ruthenium oxyde)
Protection	Epoxy coating
Terminations	B (W/A): SnPb over nickel barrier for solder reflow G (W/A) type: gold over nickel barrier for gluing

TYPICAL HF PERFORMANCE OF HCHP

POWER DERATING CURVE

SUGGESTED LAND PATTERN (please refer to IPC-7351A)


CHIP SIZE	$Z_{max.}$	$G_{min.}$	$X_{max.}$
0603	2.38	0.34	0.98
0805	2.77	0.73	1.40
1206	3.91	1.87	1.73
2010	5.94	3.64	2.67
2512	7.21	4.91	3.32

PACKAGING

Waffle-pack or tape and reel when specified

SIZE	NUMBER OF PIECES PER PACKAGE		TAPE WIDTH	
	WAFFLE PACK 2" x 2"	TAPE AND REEL ⁽¹⁾		
		MIN.	MAX.	
0603	100	100	5000	8 mm
0805			4000	
1206	140		2000	12 mm
2010	60			
2512	45			12 mm

Note
⁽¹⁾ MOQ for tape and reel: 50 pieces



STANDARD ELECTRICAL SPECIFICATIONS							
MODEL	SIZE	RESISTANCE RANGE R_n Ω	POWER RATING ⁽¹⁾ W	TOLERANCE ⁽²⁾ \pm %	TEMPERATURE COEFFICIENT ⁽²⁾ ($\pm 10^{-6}/^{\circ}\text{C}$)	CRITICAL RESISTANCE k Ω	TERMINAL MATERIAL AND FINISH
CHPFR	0603	1 to 10M	0.1	1, 2, 5	100, 200	25	E4
CHPFR	0805	1 to 10M	0.2	1, 2, 5	100, 200	50	E4
CHPFR	1206	1 to 10M	0.25	1, 2, 5	100, 200	160	E4
CHPFR	2010	1 to 10M	0.5	1, 2, 5	100, 200	180	E4
CHPFR	2512	1 to 10M	0.8	1, 2, 5	100, 200	112.5	E4
CHPFR	0603	1 to 10M	0.1	1, 2, 5	100, 200	25	E2
CHPFR	0805	1 to 10M	0.2	1, 2, 5	100, 200	50	E2
CHPFR	1206	1 to 10M	0.25	1, 2, 5	100, 200	160	E2
CHPFR	2010	1 to 10M	0.5	1, 2, 5	100, 200	180	E2
CHPFR	2512	1 to 10M	0.8	1, 2, 5	100, 200	112.5	E2

Notes

- (1) At $T_{\text{amb}} > +70^{\circ}\text{C}$ derate linearly to 0 W at $T_{\text{amb}} = +155^{\circ}\text{C}$
(2) Restrictions might apply depending on ohmic value please refer to Table 1

TABLE 1

RESISTANCE (Ω)	VALUE SERIES	AVAILABLE TOLERANCE (\pm %)	AVAILABLE TEMPERATURE COEFFICIENT ($\pm 10^{-6}/^{\circ}\text{C}$)
$1 \leq R_n < 10$	Any value in the resistance range to 3 significant figures	2, 5	200
$10 \leq R_n < 1\text{M}$		1, 2, 5	100, 200
$R_n \geq 1\text{M}$		2, 5	200

MAXIMUM RATINGS						
CHARACTERISTICS	VARIANT NUMBER	STYLE	SYMBOLS	LIMITS	UNITS	REMARKS
Limiting element voltage	11, 16	0603	U_L	50	V	-
	12, 17	0805				
	13, 18	1206				
	14, 19	2010				
	15, 20	2512				
Rated voltage	All	All	U_R	$\sqrt{(P_n \times R_n)}$	V	(1)
Isolation voltage	11, 16	0603	U_I	100	V	-
	12, 17	0805				
	13, 18	1206				
	14, 19	2010				
	15, 20	2512				
Operating temperature range	All	All	T_{op}	-65 to +155	$^{\circ}\text{C}$	T_{amb}
Storage temperature range	All	All	T_{stg}	-65 to +155	$^{\circ}\text{C}$	-
Soldering temperature	All	All	T_{sol}	+260	$^{\circ}\text{C}$	(2)
Maximum weight	11, 16	0603		0.002	g	-
	12, 17	0805				
	13, 18	1206				
	14, 19	2010				
	15, 20	2512				

Notes

- (1) Shall never exceed limiting element voltage. R_n = rated resistance
(2) Duration 10 s maximum



PERFORMANCE		
TEST	CONDITIONS	LIMITS REQUIRED BY THE ESCC4001/026 SPECIFICATION
Insulation resistance	ESCC4001 § 8.3.1.2 V = 100 V	1000 MΩ
Low temperature electrical measurement	ESCC4001 § 8.3.1.1 TC = 100 ppm/°C TC = 200 ppm/°C	± 0.8 % ± 1.6 %
High temperature electrical measurement	ESCC4001 § 8.3.3 TC = 100 ppm/°C TC = 200 ppm/°C	± 1.36 % ± 2.72 %
Rapid change of temperature	ESCC4001 § 8.8	± 0.25 + (0.05 Ω x 100/R _n) %
Robustness of terminations	ESCC4001 § 8.11.2	± 0.25 + (0.05 Ω x 100/R _n) %
Resistance to solder heat	ESCC4001 § 8.12	± 0.5 + (0.05 Ω x 100/R _n) %
Climatic sequence	ESCC4001 § 8.10	± 1 + (0.05 Ω x 100/R _n) %
Load life	ESCC4001 § 8.13 1000 h 2000 h	± 1.5 + (0.05 Ω x 100/R _n) % ± 2.5 + (0.05 Ω x 100/R _n) %

GLOBAL PART NUMBER INFORMATION																	
LIMITED TO 18 DIGITS: if more digits are necessary a codification of some digits might be necessary																	
C	H	P	F	R	0	6	0	3	K	1	0	0	1	F	B	T	
GLOBAL MODEL	SIZE	TCR	VALUE	TOLERANCE	TERMINATION	PACKAGING											
CHPFR	0603 0805 1206 2010 2512	K = 100 ppm L = 200 ppm	The first 3 digits are significant figures and the last digit specifies the number of zeros to follow. Example: 1R50 = 1.5 Ω 22R1 = 22.1 Ω 3901 = 3900 Ω 1004 = 1 MΩ	F = ± 1 % G = ± 2 % J = ± 5 %	B: SnPb over nickel barrier G: gold	For more information see Codification of Packaging table											

GLOBAL PART NUMBER INFORMATION																	
ESCC Code: 400102613R1003F4																	
4	0	0	1	0	2	6	1	3	R	1	0	0	3	F	4		
ESCC SPEC	VARIANT	FAILURE RATE	RESISTANCE VALUE	TOLERANCE	TEMPERATURE COEFFICIENT												
4001026	0603 = 11, 16 0805 = 12, 17 1206 = 13, 18 2010 = 14, 19 2512 = 15, 20	R	The first 3 digits are significant figures and the last digit specifies the number of zeros to follow. Example: 3901 = 3900 Ω 1004 = 1 MΩ	F = ± 1 % G = ± 2 % J = ± 5 %	4 = 100 ppm/°C 6 = 200 ppm/°C												

Note

- MOQ for tape and reel: 50 pieces

CROSS REFERENCE BETWEEN ESA PART NUMBER AND VISHAY PART NUMBER						
ESA PART NUMBER	VISHAY PART NUMBER	EXPLANATIONS				
4001026131003F4	CHPFR1206K1003FB	4001026 = CHPFR	13 = 1206 with B terminations	1003 = 1003 (100 kΩ)	F = F (tol. 1 %)	4 = K (TCR 100 ppm/°C)



HYPER FREQUENCY OPTION																	
Hyper Frequency Option Numbering: HCHP0603K1001FBT55																	
H	C	H	P	0	6	0	3	K	1	0	0	1	F	B	T	5	5
GLOBAL MODEL	SIZE	TCR	VALUE			TOLERANCE	TERMINATION	PACKAGING	OPTION								
HCHP	0603 0805 1206 2010 2512	K = 100 ppm L = 200 ppm	The first 3 digits are significant figures and the last digit specifies the number of zeros to follow. Example: 1R50 = 1.5 Ω 22R1 = 22.1 Ω 3901 = 3900 Ω 1004 = 1 MΩ			F = ± 1 % G = ± 2 % J = ± 5 %	B: SnPb over nickel barrier G: gold	Blank = waffle pack T = tape and reel	094 = HiRel production								

CROSS REFERENCE BETWEEN ESA PART NUMBER AND CHPFR PART NUMBER	
VARIANT ESA	VISHAY MODELS
11	CHPFR0603/B terminations
12	CHPFR0805/B terminations
13	CHPFR1206/B terminations
14	CHPFR2010/B terminations
15	CHPFR2512/B terminations
16	CHPFR0603/G terminations
17	CHPFR0805/G terminations
18	CHPFR1206/G terminations
19	CHPFR2010/G terminations
20	CHPFR2512/G terminations

CODIFICATION OF PACKAGING	
WAFFLE PACK	
W	100 min., 1 mult.
WA	100 min., 100 mult. (available only in size 1206)
PLASTIC TAPE	
T	100 min., 1 mult.
TA	100 min., 100 mult.
TB	250 min., 250 mult.
TC	500 min., 500 mult.
TD	1000 min., 1000 mult.
TE	2500 min., 2500 mult.
TF	Full tape (quantity depending on size of chips)
PAPER TAPE	
PT	100 min., 1 mult.
PA	100 min., 100 mult.
PB	250 min., 250 mult.
PC	500 min., 500 mult.
PD	1000 min., 1000 mult.
PE	2500 min., 2500 mult.
PF	Full tape (quantity depending on size of chips)

CODIFICATION OF OPTIONS ON TWO DIGITS	
OPTION	OPTION 2 DIGITS
..	..
0099	99
0100	0A
0101	0B
0102	0C
0103	0D
0104	0E
0105	0F
..	..
0124	0Y
0125	0Z
0126	1A
0127	1B
0128	1C
..	..
0320	8M
0321	8N
0322	8O
0323	8P
0324	8Q
0325	8R
..	..

CODIFICATION OF SIZES	
CODE 18	CODE 40
C	0603
D	0805
H	1206
J	2010
L	2512



TRACEABILITY DEFINITIONS

The two major traceability elements are defined as:

- The primary process lot number named Front End lot (FE lot). One “FE lot” is composed of several wafers issued from the same thin film deposition sequence.
- The date code named Batch Number (BN). The “BN” is defined after completion of the end of production testing sequence.

The lot homogeneity is given by the “FE lot” and not by the “BN”.

According to the applied rules validated by the ESCC through the product qualification, the following situations are agreed:

- Parts coming from different “FE lot” might have the same “BN”.
- A maximum of two different “BN” might be applied to the same “FE lot” to enable the use of overruns from a previous PO.
- Unless requested / approved by the customer the “BN” will be 2 years old maximum.

SPECIFIC TRACEABILITY REQUIREMENTS

The following specific requirements have to be treated as:

- A customer who requires “Lot Homogeneity” has to mention it on the PO as “SINGLE PRODUCTION LOT”.
- A customer who requires “Lot Homogeneity” in addition to a “Single Batch Number” has to mention it on the PO as “SINGLE PRODUCTION LOT AND OPTION R0101”.

END OF PRODUCTION TESTING

Mandatory testing performed at the end of the production process:

- 100 % overload: voltage $\sqrt{(6.25 P_n \times R_n)}$ or $2 U_L$ whichever is less - duration 2 s



Disclaimer

ALL PRODUCT, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE TO IMPROVE RELIABILITY, FUNCTION OR DESIGN OR OTHERWISE.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product.

Vishay makes no warranty, representation or guarantee regarding the suitability of the products for any particular purpose or the continuing production of any product. To the maximum extent permitted by applicable law, Vishay disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Statements regarding the suitability of products for certain types of applications are based on Vishay's knowledge of typical requirements that are often placed on Vishay products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. Parameters provided in datasheets and / or specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein.

Hyperlinks included in this datasheet may direct users to third-party websites. These links are provided as a convenience and for informational purposes only. Inclusion of these hyperlinks does not constitute an endorsement or an approval by Vishay of any of the products, services or opinions of the corporation, organization or individual associated with the third-party website. Vishay disclaims any and all liability and bears no responsibility for the accuracy, legality or content of the third-party website or for that of subsequent links.

Except as expressly indicated in writing, Vishay products are not designed for use in medical, life-saving, or life-sustaining applications or for any other application in which the failure of the Vishay product could result in personal injury or death. Customers using or selling Vishay products not expressly indicated for use in such applications do so at their own risk. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay. Product names and markings noted herein may be trademarks of their respective owners.