



WET TANTALUM CAPACITORS

HIGH ENERGY TYPES

KEY FACTORS



Capacitance
Performance
Energy
Temperature

QUALIFICATIONS

- DLA 04003/10004/10011/13017/15008/93026

Temperature range

-55 °C to +125 °C



Eight termination / mounting options


Voltage range: 25 V to 125 V




TERMINATION OPTIONS: Tin / Lead

Lead (Pb)-free (100 % tin)
RoHS-compliant


HEIGHT		MAXIMUM CAPACITANCE
Case A =	0.304	30 mF
Case B =	0.594	55 mF
Case C =	0.594	79 mF




VISHAY CAP MAP




APPLICATIONS



LEAD CONFIGURATIONS



FOOTPRINT + PROFILE



Shown at actual size (when viewed or printed at 100 %)