





POWER ELECTRONIC CAPACITORS

HIGH CURRENT, VERY LOW INDUCTANCE

FOOTPRINT



HEIGHT



FEATURES

- Very low inductance
- Extremely low losses at high frequencies
- Low serial resistance
- High current ratings
- High impulse discharge current capability
- Resistance to heavy-duty shock vibration
- High reliability and life expectation
- Integrated flanges for easy mounting

VOLTAGE DC

- 700 V to 2150 V or customizable



CAPACITANCE

- 15 μ F to 230 μ F



LIFE EXPECTANCY

- > 100 000 h
- < 300 FIT



FILLING AGENT

- ESTAdry resin
- UL 94 V-0




STANDARDS

IEC 61071, IEC 61881-1

RoHS
COMPLIANT


CONNECTION




SAFETY

- Self-healing film

APPLICATIONS



VISHAY CAP MAP



For technical questions: esta@vishay.com

© 2019 VISHAY INTERTECHNOLOGY, INC. ALL RIGHTS RESERVED.