




TDFN8 2 x 2 CARRIER TAPE



$A_0 = 2.25 \pm 0.05$
 $B_0 = 2.25 \pm 0.05$
 $K_0 = 0.80 \pm 0.05$

DWG: 93-5277-X

Notes

1. Measured from centerline of sprocket hole to centerline of pocket.
2. Cumulative tolerance of 10 sprocket hole is ± 0.20 mm.
3. Measured from centerline of sprocket hole to centerline of pocket.
4. Other material available. All dimensions in mm unless otherwise stated.
5. Camber not to exceed 1 mm in 100 mm, also not to exceed 1.5 cm in 1 m actually.
6. Vishay part number must be labeled at all reels of carrier tape.
7. Surface resistivity -10^5 max. Ω /sq.