



PowerPAK® 8 x 8L Carrier Tape

T1



T2



Version	A_0	A_1	B_0	B_1	K_0	K_1
T1 / -1	8.55 ± 0.1	-	8.45 ± 0.1	5.85 ± 0.15	2.3 ± 0.1	2.1 ± 0.1
T2 / -2	8.45 ± 0.1	5.85 ± 0.15	8.55 ± 0.1	-	2.3 ± 0.1	2.1 ± 0.1

Notes

- (1) 10 sprocket hole pitch cumulative tolerance ± 0.2 mm
- (2) Camber not to exceed 1 mm in 100 mm, also cannot exceed to 1.5 cm in 1 m actually
- (3) Material: black conductive or black static dissipative
- (4) A_0 and B_0 measured on a plane 0.3 mm above the bottom of the pocket
- (5) K_0 measured from a plane on the inside bottom of the pocket to the top surface of carrier
- (6) It should be measured from:
 - a. sprocket hole to pocket center
 - b. sprocket hole to pocket hole
- (7) All size in mm unless specified
- (8) Tolerance will be ± 0.1 mm unless specified
- (9) Vishay part number must be labeled at all reels of carrier tape
- (10) Surface resistivity: 10^4 to $10^{11} \Omega$
- (11) Version suffix as above table shown

QUANTITY PER REEL	
T1 / T2	2000
ECN: C21-1607-Rev. D, 22-Nov-2021 DWG: 93-5311-X	