




PowerPAIR® 6 x 5 Carrier Tape



SECTION A - A

$A_0 = 6.35$
 $B_0 = 5.35$
 $K_0 = 1.30$

Notes

- (1) 10 sprocket hole pitch cumulative tolerance ± 0.2 mm.
- (2) Camber not to exceed 1 mm in 100 mm, also not to exceed 1.5 cm in 1 m actually.
- (3) Pocket position relative to sprocket hole measured as true position of pocket, not pocket hole.
- (4) Material: PS and C.
- (5) Tolerance will be ± 0.1 mm unless specified.
- (6) Vishay part number must be labeled at all reels of cover and carrier tape.
- (7) Surface resistivity: 10^4 to $10^{11} \Omega$.

QUANTITY PER REEL	
T1	3000

ECN: C15-1433-Rev. E, 02-Nov-15 DWG: 93-5263-X
