


PowerPAK[®] 1212



Version	A_0	B_0	K_0
- 1	3.7 ± 0.1	3.7 ± 0.1	1.4 ± 0.1
- 2 (TW only)	3.6 ± 0.1	3.6 ± 0.1	1.4 ± 0.1

Notes

- (1) 10 sprocket hole pitch cumulative tolerance ± 0.2
- (2) Camber not to exceed 1 mm in 100 mm, also not to exceed 1.5 cm in 1 m actually
- (3) Material: black conductive or black static dissipative
- (4) A_0 and B_0 measured on a plane 0.3 mm above the bottom of the pocket
- (5) K_0 measured from a plane on the inside bottom of the pocket to the top surface of the carrier
- (6) It should be measured from:
 - a. sprocket hole to pocket center
 - and
 - b. sprocket hole to pocket hole
- (7) All sizes in mm unless specified
- (8) Tolerances will be ± 0.1 mm unless specified
- (9) Vishay part number must be labeled at all reels of carrier tape
- (10) Surface resistivity: 1×10^4 to $1 \times 10^{11} \Omega$

QUANTITY PER REEL	
T1	3000
ECN: C18-0765-Rev. G, 02-Jul-2018 DWG: 90-2379-X	