

Optocoupler



产品认证证书

证书编号: CQC14001105199

申请人名称及地址

威旭半导体马来西亚有限公司
No. 1710-1, Kawasan Perindustrian Krubong 75250 Melaka 马来西亚

制造商名称及地址

威旭半导体马来西亚有限公司
No. 1710-1, Kawasan Perindustrian Krubong 75250 Melaka 马来西亚

生产企业名称及地址

亿光电子(中国)有限公司 (V008546)
江苏省吴江经济开发区运西分区中山北路2135号

产品名称和系列、规格、型号

光电耦合器

见附件: 规格: 加强绝缘, 外部爬电距离 > 8mm, 内部绝缘穿透距离 > 0.4mm, 通过10次热循环, (仅适用于海拔5000米及以下)

产品标准和技术要求

GB8898-2011

认证模式

产品型式试验+初次工厂检查+获证后监督

上述产品符合CQC11-471543-2012认证规则的要求, 特发此证。

发证日期: 2014年01月26日

证书有效期内本证书的有效性依据发证机构的定期监督获得保持。

主任: _____



中国质量认证中心

中国·北京·南四环西路188号9区100070

<http://www.cqc.com.cn>

C 0056866



PRODUCT CERTIFICATE

No.: CQC14001105199

NAME AND ADDRESS OF THE APPLICANT

Vishay Semiconductor Malaysia Sdn Bhd
No. 1710-1, Kawasan Perindustrian Krubong 75250 MelakaMalaysia

NAME AND ADDRESS OF THE MANUFACTURER

Vishay Semiconductor Malaysia Sdn Bhd
No. 1710-1, Kawasan Perindustrian Krubong 75250 MelakaMalaysia

NAME AND ADDRESS OF THE FACTORY

EVERLIGHT ELECTRONICS(CHINA)CO.,LTD. (V008546)
No.2135 Zhong Shan North Rd.,Wujiang Economy Development Zone(Yun Xi Area)Wujiang City, Jiang
Su Pre, China

NAME, MODEL AND SPECIFICATION

Optocoupler

See appendix; reinforced insulation, distance through insulation \geq 0.4mm, external creepage distance $>$ 8.0mm, thermal cycling test, Altitude up to 5000m

THE STANDARDS AND TECHNICAL REQUIREMENTS FOR THE PRODUCTS

GB8898-2011

CERTIFICATION MODEL

Type Testing of Product + Initial Factory Inspection + Follow up Factory Inspection

This is to certify that the above mentioned products have met the requirements of certification rules CQC11-471543-2012.

Date of issue: Jan.26,2014

Validity of this certificate is subject to positive result of the regular follow up inspection by issuing certification body until the expiry date.

President: _____

Wang Kejiao



CHINA QUALITY CERTIFICATION CENTRE

Section 9, No.188, Nansihuan Xilu, Beijing 100070 P.R.China
<http://www.cqc.com.cn>

C 0056866



产品认证证书

附录:

第 1 页 共 1 页

证书编号: CQC14001105199

纸号: 56866

HS817, K817P, TCET1100, TCET1101, TCET1102, TCET1103, TCET1104, TCET1105, TCET1106, TCET1107, TCET1108, TCET1109, TCET1110, TCET1111, TCET1112, TCET1113, TCET1114, TCET1115, TCET1116, TCET1117, TCET1118, TCET1119, TCET1200, TCET1201, TCET1202, TCET1203, TCET1204, V0610A, V0615A, K817P1, K817P2, K817P3, K817P4, K817P5, K817P6, K817P7, K817P8, K817P9, HS817G, HS817B, HS817BG, HS817C, HS817CG, HS817D, HS817DG, TCET1100G, TCET1105G, TCET1106G, TCET1107G, TCET1108G, TCET1109-3028, TCET1109G, TCET1101G, TCET1102G, TCET1103-3034, TCET1103D, TCET1103G, TCET1104G, TCET1102GD, TCET1103GD, TCET1110G, TCET1115G, TCET1116G, TCET1117G, TCET1118G, TCET1119G, TCET1111G, TCET1112G, TCET1113G, TCET1114G, TCET1200G, TCET1201G, TCET1202G, TCET1203G, TCET1204G, V0610A-1, V0610A-2, V0610A-3, V0610A-4, V0615A-5, V0615A-6, V0615A-7, V0615A-8, V0615A-9, V0615A-1, V0615A-2, V0615A-3, V0615A-4

注: 此附录与证书同时使用时有效。

主任: _____



中国质量认证中心

中国·北京·南四环西路 188 号 9 区 100070

<http://www.cqc.com.cn>