

RF Power Barrel Capacitors, Class 1 and Class 2 Ceramic



LINKS TO ADDITIONAL RESOURCES



QUICK REFERENCE DATA			
DESCRIPTION	VALUE		
Ceramic class	1	1	2
Ceramic dielectric	NP0 (C0G)	N750 (U2J)	X5U
Type	7FAA	7FAU	5FAE
Voltage (V_{DC})	7500	7500	5000
Min. capacitance (pF)	10	75	500
Max. capacitance (pF)	50	100	1000
Mounting	Screw terminal		

MATERIAL

Capacitor elements made from class 1 or class 2 ceramic dielectric with noble metal electrodes.

Connection terminals:
thread terminal, brass, tin plated.

Allowable torque: 1.47 Nm (13 lbf in)

FINISH

Capacitor finished with protective lacquer.

MARKING

Type designator, capacitance value and tolerance, rated peak voltage, ceramic material code, production date code, manufacturer logo.

FEATURES

- Small size
- Geometry minimizes inductance, and maximizes voltage and heat dissipation capability

APPLICATIONS

- Industrial and medical RF power supplies
- Low power broadcasting equipment
- Antenna coupling
- Induction heating equipment

CAPACITANCE RANGE

10 pF to 1.0 nF

CAPACITANCE TOLERANCE

$\pm 10\%$; $\pm 20\%$

CERAMIC DIELECTRICS

- Class 1: NP0 (C0G), N750 (U2J)
- Class 2: X5U

RATED VOLTAGE

- 5.0 kV_{DC}
- 7.5 kV_{DC}

DIELECTRIC STRENGTH TEST

150 % of rated DC voltage

DISSIPATION FACTOR

- Class 1: max. 0.2 % (1 MHz)
- Class 2: max. 2.0 % (1 kHz)

INSULATION RESISTANCE

- Class 1: 100 000 M Ω (at 25 °C)
- Class 2: 10 000 M Ω (at 25 °C)

OPERATING TEMPERATURE RANGE

- Class 1: -55 °C to +100 °C
- Class 2: -55 °C to +85 °C

SAP PART NUMBER AND ELECTRICAL DATA									
PART NUMBER	CERAMIC	CAP. VALUES (pF)	RATED VOLTAGE (kV _{DC})	MAX. POWER RATING ⁽¹⁾ (kvar)			MAXIMUM CURRENT RATING ⁽¹⁾ (A _{RMS})		
				1 MHz	10 MHz	30 MHz	1 MHz	10 MHz	30 MHz
TYPE 7FAA, 7FAU									
7FAA100K	NP0 (C0G)	10	7.5	1.7	10	10	0.3	2.5	4.5
7FAA200K		20		3.2	10	10	0.8	3.5	7.0
7FAA250K		25		4.4	10	10	0.9	4.0	7.0
7FAA300K		30		5.3	10	10	1.0	2.4	7.5
7FAA500K		50		8.8	10	7.6	1.7	5.7	8.0
7FAU750K	N750 (U2J)	75		10	10	6.3	2.2	7.0	9.5
7FAU101K		100		10	10	4.8	2.5	8.0	0.5
TYPE 5FAE									
5FAE501M	X5U	500	5.0	0.4	0.4	0.2	0.9	1.9	1.9
5FAE801M		800		0.6	0.3	0.2	1.7	3.5	3.5
5FAE102M		1000		0.4	0.2	0.15	1.7	3.7	3.7

Notes

- # 8th digit of the part number: capacitance tolerance code ± 10 % = K, ± 20 % = M
- RoHS-compliant parts on request
- ⁽¹⁾ At rated voltage. Data presented is based on a minimum body temperature rise of 30 °C at +25 °C

DIMENSIONS in millimeters (inches)	
TYPE	5FAE, 7FAA, 7FAU
Diameter D _{max.}	20.7 (0.815)
Thread size	6-32 UNC-2B thread; 4.0 (0.157) depth
Length L _{1 max.} ⁽¹⁾	22.6 (0.890)
Length L _{2 max.} ⁽¹⁾	17.0 (0.670)

Note

- ⁽¹⁾ Dimension L will vary depending upon capacitance value

RELATED DOCUMENTS	
General Information	www.vishay.com/doc?22071



Disclaimer

ALL PRODUCT, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE TO IMPROVE RELIABILITY, FUNCTION OR DESIGN OR OTHERWISE.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product.

Vishay makes no warranty, representation or guarantee regarding the suitability of the products for any particular purpose or the continuing production of any product. To the maximum extent permitted by applicable law, Vishay disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Statements regarding the suitability of products for certain types of applications are based on Vishay's knowledge of typical requirements that are often placed on Vishay products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. Parameters provided in datasheets and / or specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein.

Hyperlinks included in this datasheet may direct users to third-party websites. These links are provided as a convenience and for informational purposes only. Inclusion of these hyperlinks does not constitute an endorsement or an approval by Vishay of any of the products, services or opinions of the corporation, organization or individual associated with the third-party website. Vishay disclaims any and all liability and bears no responsibility for the accuracy, legality or content of the third-party website or for that of subsequent links.

Vishay products are not designed for use in life-saving or life-sustaining applications or any application in which the failure of the Vishay product could result in personal injury or death unless specifically qualified in writing by Vishay. Customers using or selling Vishay products not expressly indicated for use in such applications do so at their own risk. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay. Product names and markings noted herein may be trademarks of their respective owners.