



Interference Suppression Film Capacitors MKP Radial Potted Type



FEATURES

- 15 mm to 27.5 mm lead pitch.
Supplied in box, taped on ammpack or reel
- Material categorization:
for definitions of compliance please see
www.vishay.com/doc?99912


RoHS
COMPLIANT

APPLICATIONS

X1 class

For X1 electromagnetic interference suppression in across the line applications (50 Hz / 60 Hz) with a maximum mains voltage of 275 V_{AC}.

For application limitations please refer to section "Application Notes".


QUICK REFERENCE DATA

| | |
|--|--|
| Capacitance range (E12 series) | 0.01 μ F to 1 μ F (preferred values according to E6) |
| Capacitance tolerance | $\pm 20\%$; $\pm 10\%$; $\pm 5\%$ |
| Rated AC voltage | 275 V _{AC} ; 50 Hz to 60 Hz |
| Permissible DC voltage | 630 V _{DC} |
| Climatic testing class (according to EN 60068-1) | 55/105/56/B |
| Maximum application temperature | 105 °C |
| Rated temperature | 105 °C |
| Leads | Tinned wire |
| Reference standards | IEC 60384-14:2013 IEC 60384-14:2013 / AMD1:2016 EN 60384-14:2013 + AMD1:2016 IEC 60065, pass. flamm. class B UL 60384-14 CSA E384-14 |
| Dielectric | Polypropylene film |
| Electrodes | Metallized film |
| Construction | Mono construction |
| Encapsulation | Plastic case, epoxy resin sealed, flame retardant UL-class 94 V-0 |
| Marking | C-value; tolerance; rated voltage; sub-class; manufacturer's type; code for dielectric material; manufacturer location, year and week; manufacturer's logo or name; safety approvals |

Note


- For more detailed data and test requirements, contact rfi@vishay.com

DIMENSIONS in millimeters





COMPOSITION OF CATALOG NUMBER



Note

(1) For detailed tape specifications refer to packaging information: www.vishay.com/doc?28139

| SPECIFIC REFERENCE DATA | |
|---|-------------------------|
| DESCRIPTION | VALUE |
| Tangent of loss angle: | at 10 kHz |
| C ≤ 100 nF | ≤ 10 x 10 ⁻⁴ |
| 100 nF < C ≤ 470 nF | ≤ 20 x 10 ⁻⁴ |
| C > 470 nF | ≤ 70 x 10 ⁻⁴ |
| Rated voltage pulse slope (dU/dt) _R at 385 V _{DC} : | |
| P = 15 mm | 250 V/μs |
| P = 22.5 mm | 150 V/μs |
| P = 27.5 mm | 100 V/μs |
| R between leads, for C ≤ 0.33 μF at 100 V; 1 min | > 15 000 MΩ |
| RC between leads, for C > 0.33 μF at 100 V; 1 min | > 5000 s |
| R between leads and case; 100 V; 1 min | > 30 000 MΩ |
| Withstanding (DC) voltage (cut off current 10 mA) ⁽¹⁾ ; rise time ≤ 1000 V/s | 3400 V; 1 min |
| Withstanding (AC) voltage between leads and case | 2050 V; 1 min |

Note

(1) See "Voltage Proof Test for Metalized Film Capacitors": www.vishay.com/doc?28169



ELECTRICAL DATA AND ORDERING INFORMATION

| U _{RAC} (V) | CAP. (μF) | DIMENSIONS W x H x L (mm) | MASS (g) ⁽¹⁾ | CATALOG NUMBER BFC2 336 1 AND PACKAGING | | | | | |
|-------------------------|--|---------------------------------|----------------------------|---|-------|---------------------------------------|------|--|------|
| | | | | LOOSE IN BOX | | | | REEL 500 mm ⁽¹⁾⁽²⁾ | |
| | | | | l _t = 3.5 mm ± 0.3 mm | | l _t = 25.0 mm ± 2.0 mm | | H = 18.5 mm; P ₀ = 12.7 mm | |
| | | | | LAST 5 DIGITS OF CATALOG NUMBER | SPQ | LAST 5 DIGITS OF CATALOG NUMBER | SPQ | LAST 5 DIGITS OF CATALOG NUMBER | SPQ |
| 275 | PITCH = 15.0 mm ± 0.4 mm; d _t = 0.6 mm ± 0.06 mm; U _{RAC} = 275 V; C-TOL. = ± 20 % | | | | | | | | |
| | 0.010 | 5.0 x 11.0 x 17.5 | 1 | 19001 | 1000 | 19007 | 1000 | 19002 | 1100 |
| | 0.015 | | | 10153 | | 16153 | | 13153 | |
| | 0.022 | | | 10223 | | 16223 | | 13223 | |
| | 0.033 | 6.0 x 12.0 x 17.5 | 1.4 | 10333 | | 16333 | | 13333 | 900 |
| | PITCH = 15.0 mm ± 0.4 mm; d _t = 0.8 mm ± 0.08 mm; U _{RAC} = 275 V; C-TOL. = ± 20 % | | | | | | | | |
| | 0.047 | 7.0 x 13.5 x 17.5 | 1.8 | 10473 | 1000 | 16473 | 500 | 13473 | 800 |
| | 0.068 | 8.5 x 15.0 x 17.5 | 2.4 | 10683 | | 16683 | | 13683 | 650 |
| | 0.100 | 10.0 x 16.5 x 17.5 | 3 | 10104 | 500 | 16104 | | 13104 | 600 |
| | PITCH = 22.5 mm ± 0.4 mm; d _t = 0.8 mm ± 0.08 mm; U _{RAC} = 275 V; C-TOL. = ± 20 % | | | | | | | | |
| | 0.10 | 7.0 x 16.5 x 26.0 | 2.9 | 19003 | 200 | 19008 | 500 | 19004 | 550 |
| | 0.15 | 8.5 x 18.0 x 26.0 | 3.8 | 10154 | | 16154 | | 13154 | 450 |
| | 0.22 | 10.0 x 19.5 x 26.0 | 6.8 | 10224 | | 16224 | | 13224 | 400 |
| | PITCH = 27.5 mm ± 0.4 mm; d _t = 0.8 mm ± 0.08 mm; U _{RAC} = 275 V; C-TOL. = ± 20 % | | | | | | | | |
| | 0.22 | 11.0 x 21.0 x 31.0 | 7.4 | 19005 | 100 | 19009 | 125 | | |
| | 0.33 | 13.0 x 23.0 x 31.0 | 9.2 | 10334 | | 16334 | | | |
| | 0.47 | 15.0 x 25.0 x 31.0 | 12.3 | 10474 | | 16474 | | | |
| | 0.68 | 18.0 x 28.0 x 31.0 | 16.1 | 10684 | | 16684 | | | |
| | 1.00 | 21.0 x 31.0 x 31.0 | 20.3 | 10105 | 50 | 16105 | 75 | | |
| | PITCH = 15.0 mm ± 0.4 mm; d _t = 0.6 mm ± 0.06 mm; U _{RAC} = 275 V; C-TOL. = ± 10 % | | | | | | | | |
| | 0.010 | 5.0 x 11.0 x 17.5 | 1 | 11103 | 1000 | 17103 | 1000 | 14103 | 1100 |
| | 0.012 | | | 11123 | | 17123 | | 14123 | |
| | 0.015 | | | 11153 | | 17153 | | 14153 | |
| | 0.018 | 6.0 x 12.0 x 17.5 | 1.4 | 11183 | | 17183 | | 14183 | 900 |
| | 0.022 | | | 11223 | | 17223 | | 14223 | |
| | 0.027 | | | 11273 | | 17273 | | 14273 | |
| | PITCH = 15.0 mm ± 0.4 mm; d _t = 0.8 mm ± 0.08 mm; U _{RAC} = 275 V; C-TOL. = ± 10 % | | | | | | | | |
| | 0.033 | 7.0 x 13.5 x 17.5 | 1.8 | 11333 | 1000 | 17333 | 500 | 14333 | 800 |
| | 0.039 | | | 11393 | | 17393 | | 14393 | |
| | 0.047 | 8.5 x 15.0 x 17.5 | 2.4 | 11473 | | 17473 | | 14473 | 650 |
| | 0.056 | | | 11563 | 17563 | 14563 | | | |
| | 0.068 | 10.0 x 16.5 x 17.5 | 3 | 11683 | 500 | 17683 | | 14683 | 600 |
| | 0.082 | | | 11823 | | 17823 | | 14823 | |
| | PITCH = 22.5 mm ± 0.4 mm; d _t = 0.8 mm ± 0.08 mm; U _{RAC} = 275 V; C-TOL. = ± 10 % | | | | | | | | |
| | 0.10 | 7.0 x 16.5 x 26.0 | 2.9 | 11104 | 200 | 17104 | 500 | 14104 | 550 |
| | 0.12 | 8.5 x 18.0 x 26.0 | 3.8 | 11124 | | 17124 | 250 | 14124 | 450 |
| | 0.15 | | | 11154 | | 17154 | | 14154 | |
| | 0.18 | 10.0 x 19.5 x 26.0 | 6.8 | 11184 | | 17184 | 500 | 14184 | 400 |
| | PITCH = 27.5 mm ± 0.4 mm; d _t = 0.8 mm ± 0.08 mm; U _{RAC} = 275 V; C-TOL. = ± 10 % | | | | | | | | |
| | 0.22 | 11.0 x 21.0 x 31.0 | 7.4 | 11224 | 100 | 17224 | 125 | | |
| | 0.27 | | | 11274 | | 17274 | | | |
| | 0.33 | 13.0 x 23.0 x 31.0 | 9.2 | 11334 | | 17334 | | | |
| | 0.39 | 15.0 x 25.0 x 31.0 | 12.3 | 11394 | | 17394 | | | |
| | 0.47 | | | 11474 | | 17474 | | | |
| | 0.56 | | | 11564 | | 17564 | | | |
| | 0.68 | 18.0 x 28.0 x 31.0 | 16.1 | 11684 | | 17684 | | | |
| | 0.82 | 21.0 x 31.0 x 31.0 | 20.3 | 11824 | 50 | 17824 | 75 | | |

Notes



- SPQ = Standard Packing Quantity

⁽¹⁾ Reel diameter = 356 mm is available on request

⁽²⁾ H = In tape height; P₀ = Sprocket hole distance; for detailed specifications refer to Packaging Information.

⁽³⁾ Weight for short lead product only



| APPROVALS | | | | |
|---|---------------------|---------------|-----------------------|--|
| SAFETY APPROVALS X1 | VOLTAGE | VALUE | FILE NUMBERS | LINKS |
| EN 60384-14 (ENEC) (= IEC 60384-14 ed-4 (2013)) | 275 V _{AC} | 10 nF to 1 µF | ENEC16/FI/21/01061/A2 | www.vishay.com/doc?28197 |
| UL 60384-14 | 275 V _{AC} | 10 nF to 1 µF | E354331 | www.vishay.com/doc?28188 |
| CSA E384-14 | 275 V _{AC} | 10 nF to 1 µF | E354331 | |
| CB-Test-Certificate | 275 V _{AC} | 10 nF to 1 µF | FI-39828/A1 | www.vishay.com/doc?28198 |
| The ENEC-approval together with the CB-Certificate replace all national marks of the following countries (they have already signed the ENEC-Agreement): Austria; Belgium; Czech. Republic; Denmark; Finland; France; Germany; Greece; Hungary; Ireland; Italy; Luxembourg; Netherlands; Norway; Portugal; Slovenian; Spain; Switzerland and United Kingdom. | | | | |
|   | | | | |

MOUNTING

Normal Use

The capacitors are designed for mounting on printed-circuit boards. The capacitors packed in bandoleers are designed for mounting in printed-circuit boards by means of automatic insertion machines.

For detailed tape specifications refer to "Packaging information".

Specific Method of Mounting to Withstand Vibration and Shock


In order to withstand vibration and shock tests, it must be ensured that the stand-off pips are in good contact with the printed-circuit board:

- For pitches ≤ 15 mm capacitors shall be mechanically fixed by the leads
- For longer pitches the capacitors shall be mounted in the same way and the body clamped

Space Requirements on Printed Circuit Board

The maximum length and width of film capacitors is shown in Figure:

- Eccentricity as in figure. The maximum eccentricity is smaller than or equal to the lead diameter of the product concerned
- Product height with seating plane as given by "IEC 60717" as reference: $h_{\max.} \leq h + 0.3$ mm



CBA116

SOLDERING CONDITIONS

For general soldering conditions and wave soldering profile, we refer to the application note:

"Soldering Guidelines for Film Capacitors": www.vishay.com/doc?28171

Storage Temperature

$T_{\text{stg}} = -25$ °C to $+35$ °C with RH maximum 75 % without condensation







Ratings and Characteristics Reference Conditions


Unless otherwise specified, all electrical values apply to an ambient temperature of 23 °C ± 1 °C, an atmospheric pressure of 86 kPa to 106 kPa and a relative humidity of 50 % ± 2 %.

For reference testing, a conditioning period shall be applied over 96 h ± 4 h by heating the products in a circulating air oven at the rated temperature and a relative humidity not exceeding 20 %.



CHARACTERISTICS



**APPLICATION NOTES**

- For X2 electromagnetic interference suppression in standard across the line applications (50 Hz / 60 Hz) with a maximum mains voltage of 310 V_{AC}
- For series impedance applications we refer to application note www.vishay.com/doc?28153
- For capacitors connected in parallel, normally the proof voltage and possibly the rated voltage must be reduced. For information depending of the capacitance value and the number of parallel connections contact: dc-film@vishay.com
- These capacitors are not intended for continuous pulse application. For these situations capacitors of the AC and pulse programs must be used
- The maximum ambient temperature must not exceed 110 °C. (125 °C for less than 1000 h) for C ≤ 470 nF and 110 °C for C > 470 nF
- Rated voltage pulse slope:
If the pulse voltage is lower than the rated voltage, the values of the specific reference data can be multiplied by 435 V_{DC} and divided by the applied voltage

INSPECTION REQUIREMENTS**General Notes**

Sub-clause numbers of tests and performance requirements refer to the "Sectional Specification, Publication IEC 60384-14 ed-4 (2013) and Specific Reference Data."

| GROUP C INSPECTION REQUIREMENTS | | | |
|---|----------------|--|---|
| SUB-CLAUSE NUMBER AND TEST | D OR ND | CONDITIONS | PERFORMANCE REQUIREMENTS |
| SUB-GROUP C1A PART OF SAMPLE OF SUB-GROUP C1 | D | | |
| 4.1 Dimensions (detail) Initial measurements | | Capacitance Tangent of loss angle: For C ≤ 470 nF at 100 kHz For C > 470 nF at 10 kHz | As specified in chapters "General Data" of this specification |
| 4.3 Robustness of terminations | | Tensile: load 10 N; 10 s Bending: load 5 N; 4 x 90° | No visible damage |



| GROUP C INSPECTION REQUIREMENTS | | | |
|--|----------------|---|---|
| SUB-CLAUSE NUMBER AND TEST | D OR ND | CONDITIONS | PERFORMANCE REQUIREMENTS |
| SUB-GROUP C1A PART OF SAMPLE OF SUB-GROUP C1 | D | | |
| 4.4 Resistance to soldering heat | | No pre-drying Method: 1A Solder bath: 260 °C Duration: 10 s | |
| 4.19 Component solvent resistance | | Isopropylalcohol at room temperature Method: 2 Immersion time: 5 min ± 0.5 min Recovery time: Min. 1 h, max. 2 h | |
| 4.4.2 Final measurements | | Visual examination | No visible damage Legible marking |
| | | Capacitance | $ \Delta C/C \leq 5\%$ of the value measured initially |
| | | Tangent of loss angle | Increase of $\tan \delta$: ≤ 0.008 Compared to values measured initially |
| | | Insulation resistance | As specified in section "Insulation Resistance" of this specification |
| SUB-GROUP C1B PART OF SAMPLE OF SUB-GROUP C1 | D | | |
| Initial measurements | | Capacitance Tangent of loss angle: For $C \leq 470$ nF at 100 kHz For $C > 470$ nF at 10 kHz | No visible damage Legible marking |
| 4.20 Solvent resistance of the marking: see section "General Notes"; item 5 | | Isopropylalcohol at room temperature Method: 1 Rubbing material: cotton wool Immersion time: 5 min ± 0.5 min | No visible damage |
| 4.6 Rapid change of temperature | | $\theta A = -55$ °C $\theta B = +105$ °C 5 cycles | |
| SUB-GROUP C1B PART OF SAMPLE OF SUB-GROUP C1 | D | | |
| 4.6.1 Inspection | | Duration $t = 30$ min | |
| 4.7 Vibration (see note 3.1) | | Visual examination Mounting: see section "Mounting" of this specification Procedure B4: Frequency range: 10 Hz to 55 Hz Amplitude: 0.75 mm or Acceleration 98 m/s ² (whichever is less severe) Total duration 6 h | No visible damage |
| 4.7.2 Final inspection | | Visual examination | No visible damage |




| GROUP C INSPECTION REQUIREMENTS | | | |
|---|---------|---|---|
| SUB-CLAUSE NUMBER AND TEST | D OR ND | CONDITIONS | PERFORMANCE REQUIREMENTS |
| SUB-GROUP C1B PART OF SAMPLE OF SUB-GROUP C1 | D | | |
| 4.9 Shock (see note 3) | | Mounting: See section "Mounting" for more information Pulse shape: Half sine Acceleration: 490 m/s ² Duration of pulse: 11 ms | |
| 4.9.2 Final measurements | | Visual examination Capacitance Tangent of loss angle Insulation resistance | No visible damage $ \Delta C/C \leq 5\%$ of the value measured initially Increase of $\tan \delta: \leq 0.008$ Compared to values measured initially As specified in section "Insulation Resistance" of this specification |
| SUB-GROUP C1 COMBINED SAMPLE OF SPECIMENS OF SUB-GROUPS C1A AND C1B | D | | |
| 4.11 Climatic sequence | | | |
| 4.11.1 Initial measurements | | Capacitance Measured in 4.4.2 and 4.9.2 Tangent of loss angle: Measured initially in C1A and C1B | |
| 4.11.2 Dry heat | | Temperature: 105 °C Duration: 16 h | |
| 4.11.3 Damp heat cyclic Test Db First cycle | | | |
| 4.11.4 Cold | | Temperature: - 55 °C Duration: 2 h | |
| 4.11.5 Damp heat cyclic Test Db remaining cycles | | | |
| SUB-GROUP C1 COMBINED SAMPLE OF SPECIMENS OF SUB-GROUPS C1A AND C1B | D | | |
| 4.11.6 Final measurements | | Visual examination Capacitance Tangent of loss angle Voltage proof 1200 V _{DC} ; 1 min between term Insulation resistance | No visible damage Legible marking $ \Delta C/C \leq 5\%$ of the value measured in 4.11.1. Increase of $\tan \delta: \leq 0.008$ compared to values measured in 4.11.1 No permanent breakdown or flash-over $\geq 50\%$ of values specified in section "Insulation Resistance" of this specification |



| GROUP C INSPECTION REQUIREMENTS | | | |
|--|----------------|--|--|
| SUB-CLAUSE NUMBER AND TEST | D OR ND | CONDITIONS | PERFORMANCE REQUIREMENTS |
| SUB-GROUP C2 | D | | |
| 4.12 Damp heat steady state | | 56 days, 40 °C, 90 % to 95 % RH, no load capacitance | |
| 4.12.1 Initial measurements | | Tangent of loss angle at 10 kHz | |
| 4.12.3 Final measurements | | Visual examination | No visible damage Legible marking |
| | | Capacitance | $ \Delta C/C \leq 5\%$ of the value measured in 4.12.1. |
| | | Tangent of loss angle | Increase of $\tan \delta$: ≤ 0.008 Compared to values measured in 4.12.1. |
| | | Voltage proof 1200 V _{DC} ; 1 min between term | No permanent breakdown or flash-over |
| | | Insulation resistance | $\geq 50\%$ of values specified in section "Insulation Resistance" of this specification |
| SUB GROUP C3 | D | | |
| 4.13.1 Initial measurements | | Capacitance Tangent of loss angle: For C ≤ 470 nF at 100 kHz For C > 470 nF at 10 kHz | |
| 4.13 Impulse voltage | | 3 successive impulses, full wave, peak voltage: X1: 4 kV Max. 24 pulses | No selfhealing breakdowns or flashover |
| 4.14 Endurance | | Duration: 1000 h 1.25 U _{RAC} at 105 °C Once in every hour the voltage is increased to 1000 V _{RMS} for 0.1 s via resistor of $47\ \Omega \pm 5\%$ | |
| SUB GROUP C3 | D | | |
| 4.14.7 Final measurements | | Visual examination | No visible damage Legible marking |
| | | Capacitance | $ \Delta C/C \leq 10\%$ compared to values measured in 4.13.1. |
| | | Tangent of loss angle | Increase of $\tan \delta$: ≤ 0.008 Compared to values measured in 4.13.1. |
| | | Voltage proof 1200 V _{DC} ; 1 min between terminations 2050 V _{DC} ; 1 min between terminations and case | No permanent breakdown or flash-over |
| | | Insulation resistance | $\geq 50\%$ of values specified in section "Insulation Resistance" of this specification |



| GROUP C INSPECTION REQUIREMENTS | | | |
|--------------------------------------|----------|--|--|
| SUB-CLAUSE NUMBER AND TEST | D OR ND | CONDITIONS | PERFORMANCE REQUIREMENTS |
| SUB-GROUP C 4 | D | | |
| 4.15 Charge and discharge | | 10 000 cycles (50 c/s) charge to U_R half sinewave Duration: 5 ms Discharge resistance: $R = \frac{385 V_{DC}}{1.5 \times C(dU/dt)}$ $R_{min.} = 2.2$ | |
| 4.15.1 Initial measurements | | Capacitance Tangent of loss angle For $C \leq 470$ nF at 100 kHz For $C > 470$ nF at 10 kHz | |
| 4.15.3 Final measurements | | Capacitance Tangent of loss angle Insulation resistance | $ \Delta C/C \leq 10$ % compared to values measured in 4.15.1. Increase of $\tan \delta$: ≤ 0.008 Compared to values measured in 4.15.1 ≥ 50 % of values specified in section "Insulation Resistance" of this specification |
| SUB-GROUP C5 | D | | |
| 4.16 Radio frequency characteristic | | Resonance frequency | As specified in section "Resonant Frequency" of this specification. ± 10 % |
| SUB-GROUP C6 | D | | |
| 4.17 Passive flammability Class B | | Bore of gas jet: $\varnothing 0.5$ mm Fuel: Butane Test duration for actual volume V in mm ³ : $V \leq 250$: 10 s $250 < V \leq 500$: 20 s $500 < V \leq 1750$: 30 s $V > 1750$: 60 s One flame application  | After removing test flame from capacitor, the capacitor must not continue to burn for more than 10 s. No burning particle must drop from the sample. |
| SUB-GROUP C7 | D | | |
| 4.18 Active flammability | | 20 x 4 kV discharges on the test capacitor connected to U_R | The cheese cloth around the capacitors shall not burn with a flame. No electrical measurements are required. |



Disclaimer

ALL PRODUCT, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE TO IMPROVE RELIABILITY, FUNCTION OR DESIGN OR OTHERWISE.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product.

Vishay makes no warranty, representation or guarantee regarding the suitability of the products for any particular purpose or the continuing production of any product. To the maximum extent permitted by applicable law, Vishay disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Statements regarding the suitability of products for certain types of applications are based on Vishay's knowledge of typical requirements that are often placed on Vishay products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. Parameters provided in datasheets and / or specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein.

Hyperlinks included in this datasheet may direct users to third-party websites. These links are provided as a convenience and for informational purposes only. Inclusion of these hyperlinks does not constitute an endorsement or an approval by Vishay of any of the products, services or opinions of the corporation, organization or individual associated with the third-party website. Vishay disclaims any and all liability and bears no responsibility for the accuracy, legality or content of the third-party website or for that of subsequent links.

Except as expressly indicated in writing, Vishay products are not designed for use in medical, life-saving, or life-sustaining applications or for any other application in which the failure of the Vishay product could result in personal injury or death. Customers using or selling Vishay products not expressly indicated for use in such applications do so at their own risk. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay. Product names and markings noted herein may be trademarks of their respective owners.