


## High Pulse Load Carbon Film Leaded Resistors



CBB 0207 leaded resistors with advanced pulse load capability, are the perfect choice for circuitries exposed to high levels of electromagnetic interference or electrostatic discharge. The resistors can also be used to protect the circuitry of signal and mains input lines from surge pulses. Applications are in all fields of automotive, telecommunication and industrial equipment.

### FEATURES

- Pulse load capability up to 6 kV or 140 W
- Specialty product for ESD and EMC sensitive applications
- Special carbon film technology for maximum heat stress capability
- Material categorization:  
for definitions of compliance please see [www.vishay.com/doc?99912](http://www.vishay.com/doc?99912)



**RoHS**  
COMPLIANT  
HALOGEN  
**FREE**  
**GREEN**  
(5-2008)

### APPLICATIONS

- Automotive
- Telecommunication
- Industrial equipment

TECHNICAL SPECIFICATIONS	
DESCRIPTION	CBB 0207
Resistance range	10 $\Omega$ to 1.5 M $\Omega$
Res. Tolerance	$\pm 2 \%$
Temperature coefficient	Refer to temperature coefficient graph
Rated dissipation, $P_{70}$	0.6 W
Operating voltage, $U_{max}$ . AC/DC	350 V
Maximum permissible film temperature	155 $^{\circ}\text{C}$
Max. resistance change at $P_{70}$ for resistance range, $\Delta R/R$ after:	10 $\Omega$ to 100 k $\Omega$
1000 h	$\pm 2 \%$
8000 h	+5 % / -4 %
Permissible voltage against ambient (insulation):	
1 min; $U_{ins}$	500 V
Continuous	75 V
Failure rate: FIT <sub>observed</sub>	$\leq 0.1 \times 10^{-9}/\text{h}$

### APPLICATION INFORMATION

The power dissipation on the resistor generates a temperature rise against the local ambient, depending on the heat flow support of the printed-circuit board (thermal resistance). The rated dissipation applies only if the permitted film temperature is not exceeded. Furthermore, a high level of ambient temperature or of power dissipation may raise the temperature of the solder joint, hence special solder alloys or board materials may be required to maintain the reliability of the assembly.

These resistors do not feature a limited lifetime when operated within the permissible limits. However, resistance value drift increasing over operating time may result in exceeding a limit acceptable to the specific application, thereby establishing a functional lifetime. The designer may estimate the performance of the particular resistor application or set certain load and temperature limits in order to maintain a desired stability.

**MAXIMUM RESISTANCE CHANGE AT RATED DISSIPATION**

OPERATION MODE		STANDARD	POWER
Climatic category		-55 °C / +125 °C / 56 days	-55 °C / +155 °C / 56 days
Rated dissipation, $P_{70}$	CBB 0207	0.4 W	0.6 W
Applied maximum film temperature, $\vartheta_{F \max}$		125 °C	155 °C
		10 $\Omega$ to 100 k $\Omega$	
Max. resistance change at rated dissipation [ $\Delta R/R_{\max}$ ], after:	CBB 0207		
	1000 h	$\leq \pm (1 \% R + 0.05 \Omega)$	$\leq \pm (2 \% R + 0.05 \Omega)$
	8000 h	$\leq + (3 \% R + 0.05 \Omega)$ $- (2 \% R + 0.05 \Omega)$	$\leq + (5 \% R + 0.05 \Omega)$ $- (4 \% R + 0.05 \Omega)$

**TEMPERATURE COEFFICIENT AND RESISTANCE RANGE**

TYPE / SIZE	TCR	TOLERANCE	RESISTANCE	E-SERIES
CBB 0207	-250 ppm/K <sup>(1)</sup>	$\pm 2 \%$	10 $\Omega$ to 1.5 M $\Omega$	E24

**Note**

<sup>(1)</sup> This TCR figure is exhibited by most ohmic values up to 10 k $\Omega$ , for detailed information please see TCR curve on page 6.

**PART NUMBER AND PRODUCT DESCRIPTION**
**Part Number: CBB0207001501G C1 00**

C	B	B	0	2	0	7	0	0	1	5	0	1	G	C	1	0	0
TYPE / SIZE		SPECIAL CHARACTER				TCR			VALUE			TOLERANCE		PACKAGING		SPECIAL	
CBB0207		0 = neutral				0 = standard See TCR graph			3 digit value 1 digit multiplier Multiplier 9 = *10 <sup>-1</sup> 0 = *10 <sup>0</sup> 1 = *10 <sup>1</sup> 2 = *10 <sup>2</sup> 3 = *10 <sup>3</sup> 4 = *10 <sup>4</sup>			G = ± 2 %		CT C1		up to 2 digits 00 = standard	

**Product Description: CBB 0207 2 % C1 1K5**

CBB	0207	2 %	C1	1K5
TYPE	SIZE	TOLERANCE	PACKAGING	RESISTANCE VALUE
CBB	0207	$\pm 2 \%$	CT C1	47K = 47 k $\Omega$ 51R1 = 51.1 $\Omega$

**PACKAGING**

TYPE / SIZE	CODE	QUANTITY	PACKAGING STYLE	WIDTH	PITCH	DIMENSIONS
CBB 0207	CT	5000	Taped acc. to IEC 60286-1 fan-folded in a box	52 mm	5 mm	77 mm x 82 mm x 324 mm
	C1	1000				74 mm x 42 mm x 184 mm



## DESCRIPTION

Production is strictly controlled and follows an extensive set of instructions established for reproducibility. A homogeneous and dense carbon film is deposited on a high grade ceramic body (85 %  $\text{Al}_2\text{O}_3$ ) and conditioned to achieve the desired temperature coefficient. Nickel plated steel termination caps are firmly pressed on the rods. A special laser is used to achieve the target value by smoothly cutting a helical groove in the resistive layer without damaging the ceramics. Connecting wires of electrolytic copper plated with 100 % tin are welded to the termination caps. The resistors are covered by protective coating designed for electrical, mechanical and climatic protection. Five color code rings designate the resistance value and tolerance in accordance with **IEC 60062** <sup>(1)</sup>.

The result of the determined production is verified by an extensive testing procedure performed on 100 % of the individual resistors. Only accepted products are stuck directly on the adhesive tapes in accordance with **IEC 60286-1**.

## ASSEMBLY

The resistors are suitable for processing on automatic insertion equipment and cutting and bending machines. Excellent solderability is proven, even after extended storage. They are suitable for automatic soldering using wave or dipping. The encapsulation is resistant to all cleaning solvents <sup>(3)</sup> commonly used in the electronics industry, including alcohols, esters and aqueous solutions. The suitability of conformal coatings, potting compounds and their processes, if applied, shall be qualified by appropriate means to ensure the long-term stability of the whole system. The resistors are completely lead (Pb)-free, the pure tin plating provides compatibility with lead (Pb)-free and lead-containing soldering processes. The immunity of the plating against tin whisker growth has been proven under extensive testing.

## MATERIALS

Vishay acknowledges the following systems for the regulation of hazardous substances:

- IEC 62474, Material Declaration for Products of and for the Electrotechnical Industry, with the list of declarable substances given therein
- The Global Automotive Declarable Substance List (GADSL) <sup>(2)</sup>
- The REACH regulation (1907/2006/EC) and the related list of substances with very high concern (SVHC) <sup>(3)</sup> for its supply chain

The products do not contain any of the banned substances as per IEC 62474, GADSL, or the SVHC list, see [www.vishay.com/how/leadfree](http://www.vishay.com/how/leadfree).

Hence the products fully comply with the following directives:

- 2000/53/EC End-of-Life Vehicle Directive (ELV) and Annex II (ELV II)
- 2011/65/EU Restriction of the Use of Hazardous Substances Directive (RoHS) with amendment 2015/863/EU
- 2012/19/EU Waste Electrical and Electronic Equipment Directive (WEEE)

Vishay pursues the elimination of conflict minerals from its supply chain, see the Conflict Minerals Policy at [www.vishay.com/doc?49037](http://www.vishay.com/doc?49037).

## APPROVALS

Where applicable, the resistors are tested in accordance with **EN 140101-806 (successor of CECC 40101-806)** which refers to **EN 60115-1** and **EN 140100**.

Vishay Beyschlag has achieved “**Approval of Manufacturer**” in accordance with **IEC QC 001002-3, clause 2**. The release certificate for “**Technology Approval Schedule**” in accordance with **CECC 240001** based on **IEC QC 001002-3, clause 6** is granted for the Vishay Beyschlag manufacturing process.




## Notes

<sup>(1)</sup> The quoted IEC standards are also released as EN standards with the same number and identical contents.


<sup>(2)</sup> Global Automotive Declarable Substance List, see [www.gadsl.org](http://www.gadsl.org). All products comply with the IEC 62474, Material Declaration for Products of and for the Electrotechnical Industry.

CEPIC (European Chemical Industry Council), EECA (European Electronic Component Manufacturers Association), EICTA (European trade organization representing the information and communications technology and consumer electronics), see [www.digitaleurope.org/SearchResults.aspx?Search=eicta](http://www.digitaleurope.org/SearchResults.aspx?Search=eicta).

<sup>(3)</sup> Other cleaning solvents with aggressive chemicals should be evaluated in actual cleaning process for their suitability.


**FUNCTIONAL DESCRIPTION**

**Derating - Power Operation**

**Derating - Standard Operation**

**Temperature Rise**

## FUNCTIONAL DESCRIPTION




Maximum pulse load, single pulse; for permissible resistance change equivalent to 8000 h operation.

### Single Pulse



Maximum pulse load, continuous pulses; for permissible resistance change equivalent to 8000 h operation.


### Continuous Pulse



Maximum pulse voltage, single and continuous pulses; for permissible resistance change equivalent to 8000 h operation.


### Pulse Voltage

# FUNCTIONAL DESCRIPTION




Pulse load rating in accordance with IEC 60115-1, 4.27; 1.2  $\mu$ s/50  $\mu$ s; 5 pulses at 12 s intervals; for permissible resistance change 0.5 %.

## 1.2/50 Pulse




Pulse load rating in accordance with IEC 60115-1, 4.27; 10  $\mu$ s/ 700  $\mu$ s; 10 pulses at 1 minute intervals; for permissible resistance change 0.5 %.

## 10/700 Pulse



## Temperature Coefficient (TCR)

## FUNCTIONAL DESCRIPTION



Current Noise -  $A_1$  in accordance with IEC 60195

## TESTS AND REQUIREMENTS

Essentially all tests are carried out in accordance with the following specifications:

EN 60115-1, generic specification (includes tests)

EN 140100, sectional specification (includes schedule for qualification approval)

EN 140101-806 (successor of CECC 40101-806), detail specification (includes schedule for conformance inspection)

The following table contains the applicable tests selected from the documents listed above.

The tests are carried out in accordance with IEC 60068-2-xx test method and under standard atmospheric conditions in accordance with IEC 60068-1, 5.3. climatic category

LCT / UCT / 56 (rated temperature range: Lower category temperature, upper category temperature; damp heat, long term, 56 days) is valid.

Unless otherwise specified the following values apply:

Temperature: 15 °C to 35 °C

Relative humidity: 45 % to 75 %

Air pressure: 86 kPa to 106 kPa (860 mbar to 1060 mbar).

In the Test Procedures and Requirements table only the tests and requirements are listed with reference to the relevant clauses of IEC 60115-1 and IEC 60068-2-xx test methods. A short description of the test procedure is also given.


TEST PROCEDURES AND REQUIREMENTS				
IEC 60115-1 CLAUSE	IEC 60068-2-xx TEST METHOD	TEST	PROCEDURE	REQUIREMENTS PERMISSIBLE CHANGE ( $\Delta R_{\max.}$ )
			Stability for product types:	
			CBB 0207	10 $\Omega$ to 1.5 M $\Omega$
4.5	-	Resistance	-	$\pm 2 \%$
4.7	-	Voltage proof	$U_{\text{RMS}} = U_{\text{ins}}$ ; 60 s	No flashover or breakdown
4.8	-	Temperature coefficient	At (20 / -55 / 20) °C and (20 / 155 / 20) °C	-
4.13	-	Short time overload	Room temperature; $U = 2.5 \times \sqrt{P_{70} \times R}$ or $U = 2 \times U_{\text{max.}}$ ; 5 s	$\pm (0.5 \% R + 0.1 \Omega)$ no visible damage
4.16	21 (Ua) 21 (Ub) 21 (Uc)	Robustness of terminations	Tensile, bending and torsion	$\pm (0.5 \% R + 0.05 \Omega)$

**TEST PROCEDURES AND REQUIREMENTS**

IEC 60115-1 CLAUSE	IEC 60068-2-xx TEST METHOD	TEST	PROCEDURE	REQUIREMENTS PERMISSIBLE CHANGE ( $\Delta R_{\max.}$ )
			<b>Stability for product types:</b>	
			<b>CBB 0207</b>	<b>10 <math>\Omega</math> to 1.5 M<math>\Omega</math></b>
4.17	20 (Ta)	Solderability	+235 °C; 2 s solder bath method SnPb40  +245 °C; 3 s solder bath method SnAG3Cu0.5	Good tinning ( $\geq 95$ % covered, no visible damage)
4.18.2	20 (Tb)	Resistance to soldering heat	Unmounted components; (260 $\pm$ 3) °C; (10 $\pm$ 1) s	$\pm$ (0.5 % $R$ + 0.05 $\Omega$ ) no visible damage
4.19	14 (Na)	Rapid change of temperature	30 min at LCT = -55 °C and 30 min at UCT = 155 °C; 200 cycles	$\pm$ (0.5 % $R$ + 0.05 $\Omega$ ) no visible damage
4.22	6 (B4)	Vibration	6 h; 10 Hz to 2000 Hz 1.5 mm or 196 m/s <sup>2</sup>	$\pm$ (0.5 % $R$ + 0.05 $\Omega$ )
4.23		Climatic sequence:		
4.23.2	2 (Ba)	dry heat	155 °C; 16 h	
4.23.3	30 (Db)	damp heat, cyclic	55 °C; 24 h; 90 % to 100 % RH; 1 cycle	
4.23.4	1 (Aa)	cold	-55 °C; 2 h	
4.23.5	13 (M)	low air pressure	8.5 kPa; 2 h; 15 °C to 35 °C	
4.23.6	30 (Db)	damp heat, cyclic	55 °C; 5 days; 90 % to 100 % RH; 5 cycles	$\pm$ (1 % $R$ + 0.1 $\Omega$ ) no visible damage
4.23.7		DC load	apply rated power for 1 min	
4.24	78 (Cab)	Damp heat, steady state	(40 $\pm$ 2) °C; 56 days; (93 $\pm$ 3) % RH	$\pm$ (1 % $R$ + 0.1 $\Omega$ )
4.25.1	-	Endurance at 70 °C: standard operation mode	$U = \sqrt{P_{70} \times R}$ or $U = U_{\max.}$ 1.5 h on; 0.5 h off; 70 °C; 1000 h 70 °C; 8000 h	$\pm$ (1 % $R$ + 0.05 $\Omega$ ) +(3 % $R$ + 0.05 $\Omega$ ) -(2 % $R$ + 0.05 $\Omega$ )
	-	Endurance at 70 °C: power operation mode	$U = \sqrt{P_{70} \times R}$ or $U = U_{\max.}$ 1.5 h on; 0.5 h off; 70 °C; 1000 h 70 °C; 8000 h	$\pm$ (2 % $R$ + 0.05 $\Omega$ ) +(5 % $R$ + 0.05 $\Omega$ ) -(4 % $R$ + 0.05 $\Omega$ )
4.25.3	-	Endurance at upper category temperature	125 °C; 1000 h 155 °C; 1000 h	$\pm$ (2 % $R$ + 0.05 $\Omega$ ) $\pm$ (4 % $R$ + 0.1 $\Omega$ )
4.29	45 (XA)	Component solvent resistance	Isopropyl alcohol +23 °C; toothbrush method	Marking legible; no visible damage
4.40	-	Electrostatic discharge (human body model)	IEC 61340-3-1; 3 pos. + 3 neg. 16 kV	$\pm$ (0.5 % $R$ + 0.05 $\Omega$ )



## DIMENSIONS



DIMENSIONS AND MASS						
TYPE	D <sub>max.</sub> (mm)	L <sub>max.</sub> (mm)	d <sub>nom.</sub> (mm)	I <sub>min.</sub> (mm)	M <sub>min.</sub> (mm)	MASS (mg)
CBB 0207	2.5	6.3	0.6	28.0	10.0	220

## HISTORICAL 12NC INFORMATION

- The resistors had a 12-digit numeric code starting with 2312.
- The subsequent 4 digits indicated the resistor type, specification and packaging; see the 12NC table.
- The remaining 4 digits indicated the resistance value:
  - The first 3 digits indicated the resistance value.
  - The last digit indicated the resistance decade in accordance with the Resistance Decade table.

## Resistance Decade

RESISTANCE DECADE	LAST DIGIT
10 $\Omega$ to 99.9 $\Omega$	9
100 $\Omega$ to 999 $\Omega$	1
1 k $\Omega$ to 9.99 k $\Omega$	2
10 k $\Omega$ to 99.9 k $\Omega$	3
100 k $\Omega$ to 999 k $\Omega$	4
1 M $\Omega$ to 9.99 M $\Omega$	5

## 12NC Example

The 12NC of a CBB 0207 resistor, value 47 k $\Omega$  with  $\pm 2\%$  tolerance, supplied on bandoleer in a box of 5000 units was: 2312 955 24703.

HISTORICAL 12NC - Resistor Type and Packaging			
DESCRIPTION		CODE 2312 ... ..	
		BLISTER TAPE ON REEL	
TYPE	TOL.	C1 1000 UNITS	CT 5000 UNITS
CBB 0207	$\pm 2\%$	950 2....	955 2....



## Disclaimer

ALL PRODUCT, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE TO IMPROVE RELIABILITY, FUNCTION OR DESIGN OR OTHERWISE.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product.

Vishay makes no warranty, representation or guarantee regarding the suitability of the products for any particular purpose or the continuing production of any product. To the maximum extent permitted by applicable law, Vishay disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Statements regarding the suitability of products for certain types of applications are based on Vishay's knowledge of typical requirements that are often placed on Vishay products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. Parameters provided in datasheets and / or specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein.

Hyperlinks included in this datasheet may direct users to third-party websites. These links are provided as a convenience and for informational purposes only. Inclusion of these hyperlinks does not constitute an endorsement or an approval by Vishay of any of the products, services or opinions of the corporation, organization or individual associated with the third-party website. Vishay disclaims any and all liability and bears no responsibility for the accuracy, legality or content of the third-party website or for that of subsequent links.

Vishay products are not designed for use in life-saving or life-sustaining applications or any application in which the failure of the Vishay product could result in personal injury or death unless specifically qualified in writing by Vishay. Customers using or selling Vishay products not expressly indicated for use in such applications do so at their own risk. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay. Product names and markings noted herein may be trademarks of their respective owners.