

Power Resistors Cooled by Auxiliary Heatsink (Not Supplied) Thick Film Technology



FEATURES

- Technology: thick film deposited on ceramic
- Cold system without external radiation
- High power / volume ratio
- Non-inductive
- Easy assembly, self calibrated pressure (400 N)
- Possible configuration with 2 or 3 resistors
- Material categorization: for definitions of compliance please see www.vishay.com/doc?99912


RoHS
COMPLIANT

LINKS TO ADDITIONAL RESOURCES



3D Models

STANDARD ELECTRICAL SPECIFICATIONS

MODEL	RESISTANCE RANGE Ω	MAX. RATED POWER $BC_{85^{\circ}C}$ W	TOLERANCE ⁽¹⁾ $\pm \%$	TEMPERATURE COEFFICIENT $\pm \text{ppm}/^{\circ}C$	E-SERIES OHMIC VALUES
RCEC 850	0.47 to 3	850	10, 5	300	E24
	3 to 1M	850	10, 5	100	

Note

⁽¹⁾ $\pm 2 \%$ or $\pm 1 \%$ on special request for limited resistance value and with reduction of maximum power and pulse rating (contact us for details)

MECHANICAL SPECIFICATIONS

UL 94 flame classifications	Material complies with the standard UL 94 V-0
Resistive element	Cermet
Substrate	Alumina
Encapsulation	Resin filled case


TECHNICAL SPECIFICATIONS

PARAMETER	RCEC 850
Operating temperature range	$-55^{\circ}C$ to $+155^{\circ}C$
Maximum operating voltage	5000 V
Dielectric strength V_{RMS} (50 Hz / 1 min)	7000 V (other cases: contact us)
Creepage distance	$> 42 \text{ mm}$
Clearance distance	$> 13 \text{ mm}$
Nominal power at $85^{\circ}C$ bottom case temperature	850 W (single resistor), 2 x 350 W (double resistor)
Capacitance / ground	120 pF (typical) / frequency 10 kHz
Self-inductance	$\leq 40 \text{ nH}$ (typical) / frequency 10 kHz
Partial discharge	$< 20 \text{ pC}$ at 5000 V_{eff} Other cases: consult us
Insulation	$> 100 \text{ G}\Omega$ at 1000 V_{DC}
Weight (max.)	120 g


PERFORMANCES			
TESTS	CONDITIONS	REQUIREMENTS	TYPICAL VALUES
Overload	1200 W / 10 s with $\theta_{\text{bottom case}} = 85^{\circ}\text{C}$	$\pm 2\%$ or $\pm (0.5\% + 0.05\Omega)$	$< 0.2\%$
Damp heat	4 days 40°C 93 % HR	$\pm 2\%$ or $\pm (0.5\% + 0.05\Omega)$	$< 0.2\%$
VRT	$-55^{\circ}\text{C} / +125^{\circ}\text{C}$ 21 cycles	$\pm 2\%$ or $\pm (0.5\% + 0.05\Omega)$	$< 0.1\%$
Shock	18 shocks 3 positive and 3 negative per axis - 100 m/s^2 and 11 ms (IEC 60068-2-27, Ea)	$\pm (0.5\% + 0.05\Omega)$	$< 0.1\%$
Vibrations	10 sweeps/axis - 7.5 mm at 5 Hz to 8 Hz, 20 m/s^2 at 8 Hz to 200 Hz and 40 m/s^2 at 200 Hz to 500 Hz (IEC 60068-2-6, Fc)	$\pm (0.5\% + 0.05\Omega)$	$< 0.1\%$
Terminal strength	200 Ncm/100 N	$\pm 1\%$ or $\pm (0.5\% + 0.05\Omega)$	$< 0.1\%$

Note

- All tests were done in Vishay MCB laboratories conditions



DISSIPATION


Permanent Applicable Power (W) as a Function of Bottom Case Temperature ($^{\circ}\text{C}$)

OVERLOAD







Intermittent Overload (Exceptional Operation) Bottom Case Temperature $+85^{\circ}\text{C}$


ENERGY	
$R < 390\Omega$	$R > 390\Omega$
Repetitive operation = 8 J Pulse $\tau = 50\mu\text{s}$	Repetitive operation = 4 J Pulse $\tau = 50\mu\text{s}$
Accidental operation = 20 J Pulse $\tau = 50\mu\text{s}$ 120 pulses	Other τ values: consult us

DIMENSIONS in millimeters


DIMENSION	MILLIMETER		INCHES	
	MIN.	MAX.	MIN.	MAX.
A	59.2	60.8	2.331	2.394
B	35.8	36.2	1.409	1.425
C	33.8	34.2	1.331	1.346
D	57	58	2.244	2.283
E	59.7	60.3	2.350	2.374
F	67	68	2.638	2.677
G	9.5	10.5	0.374	0.413
H	4.3	4.9	0.169	0.193
I	13.5	14.5	0.531	0.571
J	14	14.6	0.551	0.575
K	23.7	24.7	0.933	0.972
L	25.5	26	1.004	1.024

CONFIGURATIONS

1	2	3	4	5
				

ASSEMBLY


Mounting screws and washers are supplied.
Electrical screws and washers are not supplied.

Tightening torque for mechanical fixation	1.8 Nm to 2 Nm
Tightening torque for electrical connections	1.8 Nm to 2 Nm

TERMINAL OPTIONS

- Electrical terminals M4

COOLING

The temperature of the heatsink may be maintained at the specified values with:

- Forced air ventilation or internal circulation of a liquid cooling
- Heatsink contact surface: < Ra 6.3 μ
- Evenness defect: 0.05 mm max.
- Surface temperature gradient (isotherm): 20 °C max.
- Thermal compound not supplied (resistance < 0.025 °C / W / 0.05 mm preconized)
- Mounting recommendation: www.vishay.com/doc?32558

Note

- The user must select the thermal resistance of the heatsink according to the power applied

**ORDERING INFORMATION**

RCEC	850	S	1	100K	100K	100K	5 %	XXX	BO20
MODEL	STYLE	SINGLE / DOUBLE	CONFIGURATION	RESISTANCE	RESISTANCE	RESISTANCE	TOLERANCE	CUSTOM	PACKAGING
				Value for single / first value for double or triple	Second value for double or triple	Third value for triple	± 5 % ± 10 % Other on request		

GLOBAL PART NUMBER INFORMATION

R	C	E	C	8	5	0	S	1	2	R	7	0	J	B			
1							2		3			4		5	6		
1		2		3		4		5		6							
GLOBAL MODEL		TERMINAL		OHMIC VALUE		TOLERANCE		PACKAGING		INDUSTRIALIZATION NUMBER							
RCEC 850		First digit: S = simple D = double T = triple Second digit: configuration 1, 2, 3, 4, or 5		The first three digits are significant figures and the last specifies the number of zeros to follow, R designates decimal point. 4702 = 47 kΩ 47R0 = 47 Ω In case of double or triple value → value = sum of the 2 or 3 values		J = 5 % K = 10 %		B = box		3 specific digits (if applicable)							



Disclaimer

ALL PRODUCT, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE TO IMPROVE RELIABILITY, FUNCTION OR DESIGN OR OTHERWISE.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product.

Vishay makes no warranty, representation or guarantee regarding the suitability of the products for any particular purpose or the continuing production of any product. To the maximum extent permitted by applicable law, Vishay disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Statements regarding the suitability of products for certain types of applications are based on Vishay's knowledge of typical requirements that are often placed on Vishay products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. Parameters provided in datasheets and / or specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein.

Hyperlinks included in this datasheet may direct users to third-party websites. These links are provided as a convenience and for informational purposes only. Inclusion of these hyperlinks does not constitute an endorsement or an approval by Vishay of any of the products, services or opinions of the corporation, organization or individual associated with the third-party website. Vishay disclaims any and all liability and bears no responsibility for the accuracy, legality or content of the third-party website or for that of subsequent links.

Except as expressly indicated in writing, Vishay products are not designed for use in medical, life-saving, or life-sustaining applications or for any other application in which the failure of the Vishay product could result in personal injury or death. Customers using or selling Vishay products not expressly indicated for use in such applications do so at their own risk. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay. Product names and markings noted herein may be trademarks of their respective owners.