


IHLP® Automotive Inductors, High Temperature (155 °C) Wide Terminal Series



FEATURES

- Wide terminals for improved mounting stability
- 10.8 mm x 10.2 mm x 4.0 mm SMD package
- High temperature, up to 155 °C
- Magnetically shielded construction
- Handles high transient current spikes without saturation
- AEC-Q200 qualified
- Packaging information: [SMD packaging](#)
- Material categorization: for definitions of compliance please see www.vishay.com/doc?99912

AUTOMOTIVE
GRADE

RoHS
COMPLIANT

HALOGEN
FREE
GREEN
(5-2008)

LINKS TO ADDITIONAL RESOURCES



3D Models



Design Tools



Product Page

APPLICATIONS


- Engine and transmission control units
- DC/DC converters for infotainment, navigation systems, lighting
- Noise suppression and filtering
- LED drivers

STANDARD ELECTRICAL SPECIFICATIONS

PART NUMBER	INDUCTANCE ± 20 % (μH) AT 0 A	DCR 25 °C (mΩ)		HEAT RATING CURRENT DC TYP. (A) ⁽¹⁾	SATURATION CURRENT DC TYP. (A) ⁽²⁾		SRF TYP. (MHz)
		TYP.	MAX.		20 % DROP	30 % DROP	
IHLP4W40DZERR47M5A	0.47	1.55	1.66	30	28.5	40	72.1
IHLP4W40DZERR68M5A	0.68	2.17	2.32	35	24	35	42.5
IHLP4W40DZER1R0M5A	1.0	2.87	3.07	23.5	24.0	32.0	37.2
IHLP4W40DZER1R5M5A	1.5	4.2	4.5	22	17.9	26	32
IHLP4W40DZER2R2M5A	2.2	8.15	8.76	15	12	16	30.1
IHLP4W40DZER3R3M5A	3.3	11	11.81	11	12	15	25.5
IHLP4W40DZER4R7M5A	4.7	14.3	15.32	9.8	9.2	14	20.1
IHLP4W40DZER5R6M5A	5.6	16.5	17.6	9.3	9.0	12.2	16.3
IHLP4W40DZER6R8M5A	6.8	20.9	22.36	8.0	9.0	12.2	16.3
IHLP4W40DZER100M5A	10	30.9	33.06	6.5	8.5	10	11.5
IHLP4W40DZER220M5A	22	70.5	75.44	4.1	6.4	9	8.3
IHLP4W40DZER330M5A	33	110	117.7	3.7	4.2	6.5	5.79
IHLP4W40DZER470M5A	47	167	178	3.1	4.1	6.2	5.22
IHLP4W40DZER680M5A	68	240	252	2.4	3.5	4.7	4.02

Notes

- All test data is referenced to 25 °C ambient
 - Test condition: 100 kHz, 0.25 V
 - Operating temperature range -55 °C to +155 °C
 - The part temperature (ambient + temp. rise) should not exceed 155 °C under worst case operating conditions. Circuit design, component placement, PCB trace size and thickness, airflow and other cooling provisions all affect the part temperature. Part temperature should be verified in the end application
 - Rated operating voltage (across inductor) = 75 V
- ⁽¹⁾ DC current (A) that will cause an approximate ΔT of 40 °C
- ⁽²⁾ DC current (A) that will cause L₀ to drop approximately 20 %

DIMENSIONS in inches [millimeters]

DESCRIPTION









IHLP-4W40DZ-5A	4.7 μH	± 20 %	TAPE AND REEL	e3
MODEL	INDUCTANCE VALUE	INDUCTANCE TOLERANCE	PACKAGE CODE	JEDEC® LEAD (Pb)-FREE STANDARD

GLOBAL PART NUMBER

I H L P	4 W 4 0 D Z	E R	4 R 7	M	5 A
PRODUCT FAMILY	SIZE	PACKAGE CODE	IMPEDANCE VALUE	INDUCTANCE TOLERANCE	SERIES
		ER = tape and reel	4R7 = 4.7 μ H	M = ± 20 %	










PERFORMANCE GRAPHS













PERFORMANCE GRAPHS












PERFORMANCE GRAPHS: INDUCTANCE AND Q VS. FREQUENCY





PERFORMANCE GRAPHS: INDUCTANCE AND Q VS. FREQUENCY





Disclaimer

ALL PRODUCT, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE TO IMPROVE RELIABILITY, FUNCTION OR DESIGN OR OTHERWISE.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product.

Vishay makes no warranty, representation or guarantee regarding the suitability of the products for any particular purpose or the continuing production of any product. To the maximum extent permitted by applicable law, Vishay disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Statements regarding the suitability of products for certain types of applications are based on Vishay's knowledge of typical requirements that are often placed on Vishay products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. Parameters provided in datasheets and / or specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein.

Hyperlinks included in this datasheet may direct users to third-party websites. These links are provided as a convenience and for informational purposes only. Inclusion of these hyperlinks does not constitute an endorsement or an approval by Vishay of any of the products, services or opinions of the corporation, organization or individual associated with the third-party website. Vishay disclaims any and all liability and bears no responsibility for the accuracy, legality or content of the third-party website or for that of subsequent links.

Except as expressly indicated in writing, Vishay products are not designed for use in medical, life-saving, or life-sustaining applications or for any other application in which the failure of the Vishay product could result in personal injury or death. Customers using or selling Vishay products not expressly indicated for use in such applications do so at their own risk. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay. Product names and markings noted herein may be trademarks of their respective owners.