



HIGH-VOLTAGE POWER MOSFETs

SiHG22N60S, SiHP22N60S, SiHB22N60S,
SiHF22N60S



New 600-V MOSFETs with Super Junction Technology

Super Junction Technology in TO-220, TO-247, TO-220F,
and TO-263 Packages

KEY BENEFITS

- Dramatic reduction of maximum $R_{DS(on)}$ at $V_{GS} = 10\text{ V}$: $0.190\ \Omega$
- Ultra-low gate charge: $Q_g = 98\text{ nC}$
- Increased efficiency for SMPS
- High E_{AR} capability
- Low figure-of-merit (FOM) $R_{on} \times Q_g$
- 100% avalanche tested
- High peak current capability
- dV/dt ruggedness
- Effective C_{OSS} specified
- Improved transconductance
- High power dissipation capability

APPLICATIONS

- Power factor correction (PFC) and pulse width modulation (PWM) in a wide range of electronics including:
 - LCD TVs
 - PCs
 - Servers
 - Switchmode power supplies (SMPS)
 - Telecom systems

Power MOSFETS

PRODUCT SUMMARY	
V_{DS} at T_J max. (V)	650
$V_{DS(on)}$ (Ω)	$V_{GS} = 10$ V 0.190
C_{Qj} (Max.) (nC)	98
Q_{gs} (nC)	17
Q_{gd} (nC)	25
Configuration	Single

FEATURES

- High E_{AS} Capability
- Lower Figure-of-Merit $R_{\theta(jc)} \times Q_g$
- 100 % Avalanche Tested
- High Peak Current Capability
- dV/dt Ruggedness
- Effective C_{oss} Specified
- Improved Transconductance
- Improved t_{rr}/Q_{rr}
- Improved Gate Charge
- High Power Dissipation Capability
- Compliant to RoHS Directive 2002/95/EC



ORDERING INFORMATION

Package	TO-220
Lead (Pb)-free	SiHF22N60S-E3

ORDERING INFORMATION

Package	TO-247
Lead (Pb)-free	SiHG22N60S-E3

ORDERING INFORMATION

Package	TO-220 FULLPAK
Lead (Pb)-free	SiHF22N60S-E3

ORDERING INFORMATION

Package	D ² PAK (TO-263)
Lead (Pb)-free	SiHB22N60S-E3

PARAMETER	SYMBOL	LIMIT	UNIT
Drain-Source Voltage	V_{DS}	600	V
Gate-Source Voltage	V_{GS}	± 20	
Continuous Drain Current ^a	I_D	22	A
	I_{DM}	13	
Pulsed Drain Current ^b		65	
Linear Derating Factor		2	W/°C
Single Pulse Avalanche Energy ^c	E_{AS}	680	mJ
Repetitive Avalanche Energy ^b	E_{AR}	25	
Maximum Power Dissipation	P_D	250	W
Peak Diode Recovery dV/dt ^d	dV/dt	7.3	V/ns
Operating Junction and Storage Temperature Range	T_J, T_{stg}	-55 to +150	°C
Soldering Recommendations (Peak Temperature) ^e		300	

- Notes**
- Limited by maximum junction temperature.
 - Repetitive rating; pulse width limited by maximum junction temperature.
 - $V_{DS} = 50$ V, starting $T_J = 25$ °C, $L = 13.8$ mH, $R_{\theta(jc)} = 25$ °C/W, $I_{AS} = 10$ A.
 - $I_{sp} \leq 22$ A, $dI/dt \leq 340$ A/μs, $V_{DD} \leq V_{DS}$, $T_J \leq 150$ °C.
 - 1.6 mm from case.

Revision 10-Dec-09

* Pb containing terminations are not RoHS compliant, exemptions may apply

DISCLAIMER All product specifications and data are subject to change without notice. Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or omissions contained herein or in any other disclosure relating to any product. Vishay disclaims any and all liability arising out of the use or application of any product described herein or of any information provided herein to the maximum extent permitted by law. The product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein, which apply to these products. No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay. The products shown herein are not designed for use in medical, life-saving, or life-sustaining applications unless otherwise expressly indicated. Customers using or selling Vishay products not expressly indicated for use in such applications do so entirely at their own risk and agree to fully indemnify Vishay for any damages arising or resulting from such use or sale. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications. Product names and markings noted herein may be trademarks of their respective owners.

For technical questions, contact hvm@vishay.com