


Thin Film Center-Tapped Resistor Divider Network



Product may not be to scale

The CTT series resistor chips offer a combination of low shunt capacitance and excellent stability. The CTT offers the designer flexibility in use as either a single value resistor or as two resistor with a center tap feature.

The CTTs six bonding pads allows the user increased layout flexibility. The CTTs tantalum nitride resistor material offers excellent resistance to high moisture environments.


The CTTs are manufactured using Vishay Electro-Films (EFI) sophisticated thin film equipment and manufacturing technology. The CTTs are 100 % electrically tested and visually inspected to MIL-STD-883, method 2032 class H or K.

FEATURES

- Wire bondable
- Center tap feature
- Chip size: 0.030" x 0.030"
- Case: 0303
- Resistance range R_T : 10 Ω to 35 k Ω
- Alumina substrate, low shunt capacitance: < 0.2 pF
- Resistor material: Tantalum nitride
- Moisture resistant
- Material categorization: For definitions of compliance please see www.vishay.com/doc?99912



RoHS
COMPLIANT
GREEN
(5-2008)




APPLICATIONS

The CTT center-tapped resistor chips are used mainly in feedback circuits of amplifiers where ratio matching, tracking, low shunt capacitance and better frequency response are necessary.

Vishay EFI measures low-value resistors by the four-wire kelvin technique.

TEMPERATURE COEFFICIENT OF RESISTANCE, VALUES, AND TOLERANCES

PARAMETER	VALUE	UNIT
Total Resistance Range	10 to 35K	Ω
Standard Tolerances	± 0.5	%
TCR	$\pm 25, \pm 50, \pm 100, \pm 250$	ppm/ $^{\circ}\text{C}$




STANDARD ELECTRICAL SPECIFICATIONS


PARAMETER	VALUE	UNIT
TCR Tracking Between Halves (R_A/R_B) ⁽¹⁾	± 2	ppm/ $^{\circ}\text{C}$
Center Tap Ratio, R_A/R_B : Tolerance	1 ± 1	%
Noise, MIL-STD-202, Method 308	- 35 typ.	dB
Moisture Resistance, MIL-STD-202, Method 106	± 0.5 max. $\Delta R/R$	%
Stability, 1000 h, + 125 $^{\circ}\text{C}$, 62 mW	± 0.25 max. $\Delta R/R$	%
Operating Temperature Range	- 55 to + 125	$^{\circ}\text{C}$
Thermal Shock, MIL-STD-202, Method 107, Test Condition F	± 0.1 max. $\Delta R/R$	%
High Temperature Exposure, + 150 $^{\circ}\text{C}$, 100 h	± 0.2 max. $\Delta R/R$	%
Insulation Resistance	10^{12} min.	Ω
Operating Voltage	100 max.	V
DC Power Rating at 70 $^{\circ}\text{C}$ (derated to zero at + 150 $^{\circ}\text{C}$)	0.125 max.	W
5 x Rated Power Short-Time Overload, + 25 $^{\circ}\text{C}$, 5 s	± 0.25 max. $\Delta R/R$	%

Note

⁽¹⁾ 10 ppm/ $^{\circ}\text{C}$ for $R < 100$

DIMENSIONS in inches


STANDARD CONFIGURATION
 *Six locations. All pads 0.005" x 0.005"

SCHEMATIC


MECHANICAL SPECIFICATIONS	
PARAMETER	VALUE
Chip Size	0.030" x 0.030" ± 0.002" (0.762 mm x 0.762 mm ± 0.050 mm)
Chip Thickness	0.010" ± 0.002" (0.254 mm ± 0.05 mm)
Chip Substrate Material	99.6 % alumina
Resistor Material	Tantalum nitride
Bonding Pad Size	0.005" x 0.005" (0.127 mm x 0.127 mm)
Number of Pads	6
Pad Material	25 kÅ minimum gold (Al optional)
Backing	None

Options: Alphanumeric part marking, up to six characters.

GLOBAL PART NUMBER INFORMATION																
Global Part Number: CTT50000KFKKGNHWS																
Global Part Number Description: CTT 5K 10 % RT 1 % ± 100 ppm/°C ± 10 ppm/°C Au None H WS																
C	T	T	5	0	0	0	0	K	F	K	K	G	N	H	W	S
MODEL	RESISTANCE (R TOTAL)	RESISTANCE MULTIPLIER CODE	TOL. CODE (%)	RATIO TOL. (%)	TCR (ppm/°C)	TCR TRACK (ppm/°C)	TERMINATION		BACK METAL	VISUAL CLASS	PACKAGING CODE					
CTT	First 4 digits are significant figures of resistance	B = 0.01 A = 0.1 0 = 1 1 = 10	D = 0.5 F = 1.0 G = 2.0 J = 5.0 K = 10.0	F = 1.0 G = 2.0 U = User N = No	E = ± 25 C = ± 50 K = ± 100 M = ± 250	G = ± 2 J = ± 5 K = ± 10 N = No	G = Au A = Al		G = Au N = None	H = Class H K = Class K	WS = Waffle pack 100 min., 1 mult					



Disclaimer

ALL PRODUCT, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE TO IMPROVE RELIABILITY, FUNCTION OR DESIGN OR OTHERWISE.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product.

Vishay makes no warranty, representation or guarantee regarding the suitability of the products for any particular purpose or the continuing production of any product. To the maximum extent permitted by applicable law, Vishay disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Statements regarding the suitability of products for certain types of applications are based on Vishay's knowledge of typical requirements that are often placed on Vishay products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. Parameters provided in datasheets and / or specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein.

Hyperlinks included in this datasheet may direct users to third-party websites. These links are provided as a convenience and for informational purposes only. Inclusion of these hyperlinks does not constitute an endorsement or an approval by Vishay of any of the products, services or opinions of the corporation, organization or individual associated with the third-party website. Vishay disclaims any and all liability and bears no responsibility for the accuracy, legality or content of the third-party website or for that of subsequent links.

Except as expressly indicated in writing, Vishay products are not designed for use in medical, life-saving, or life-sustaining applications or for any other application in which the failure of the Vishay product could result in personal injury or death. Customers using or selling Vishay products not expressly indicated for use in such applications do so at their own risk. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay. Product names and markings noted herein may be trademarks of their respective owners.