P-Channel 20 V (D-S) MOSFET

PRODUCT SUMMARY			
V_{DS} (V)	$R_{DS(on)}$ (Ω)	I_D (A) [e]	Q_g (TYP.)
-20	0.032 at V_{GS} = -4.5 V	-16	14.5 nC
	0.046 at V_{GS} = -2.5 V	-14.3	
	0.065 at V_{GS} = -2.0 V	-12	
	0.120 at V_{GS} = -1.8 V	-2.5	

FEATURES


- TrenchFET® power MOSFET
- Ultra-small 1.5 mm x 1 mm maximum outline
- Ultra-thin 0.59 mm maximum height
- Material categorization: for definitions of compliance please see www.vishay.com/doc?99912

Pb-free

RoHS COMPLIANT

HALOGEN FREE

MICRO FOOT® 1.5 x 1



Backside View


Bump Side View

Marking Code: xxxx = 8499
xxx = Date / lot traceability code

Ordering Information:
Si8499DB-T2-E1 (Lead (Pb)-free and halogen-free)

APPLICATIONS

- Low on-resistance load switch, charger switch and battery switch for portable devices
  - Low power consumption
  - Increased battery life



P-Channel MOSFET

ABSOLUTE MAXIMUM RATINGS (T_A = 25 °C, unless otherwise noted)				
PARAMETER		SYMBOL	LIMIT	UNIT
Drain-Source Voltage		V_{DS}	-20	V
Gate-Source Voltage		V_{GS}	± 12	
Continuous Drain Current (T_J = 150 °C)	T_C = 25 °C	I_D	-16	A
	T_C = 70 °C		-13.7	
	T_A = 25 °C		-7.8 [a, b]	
	T_A = 70 °C		-6.3 [a, b]	
Pulsed Drain Current		I_{DM}	-20	
Continuous Source-Drain Diode Current	T_C = 25 °C	I_S	-10.8	
	T_A = 25 °C		-2.3 [a, b]	
Maximum Power Dissipation	T_C = 25 °C	P_D	13	W
	T_C = 70 °C		8.4	
	T_A = 25 °C		2.77 [a, b]	
	T_A = 70 °C		1.77 [a, b]	
Operating Junction and Storage Temperature Range		T_J, T_{stg}	-55 to +150	°C
Package Reflow Conditions [c]	IR/Convection		260	

THERMAL RESISTANCE RATINGS					
PARAMETER		SYMBOL	TYPICAL	MAXIMUM	UNIT
Maximum Junction-to-Ambient [a, f]		R_{thJA}	37	45	°C/W
Maximum Junction-to-Case (Drain)	Steady State	R_{thJC}	7	9.5	

Notes

a. Surface mounted on 1" x 1" FR4 board.
b. t = 10 s.
c. Refer to IPC/JEDEC® (J-STD-020), no manual or hand soldering.
d. Case is defined as the top surface of the package.
e. Based on T_C = 25 °C.
f. Maximum under steady state conditions is 85 °C/W.

For technical questions, contact: pmostechsupport@vishay.com

THIS DOCUMENT IS SUBJECT TO CHANGE WITHOUT NOTICE. THE PRODUCTS DESCRIBED HEREIN AND THIS DOCUMENT ARE SUBJECT TO SPECIFIC DISCLAIMERS, SET FORTH AT www.vishay.com/doc?91000

SPECIFICATIONS (T_J = 25 °C, unless otherwise noted)						
PARAMETER	**SYMBOL**	**TEST CONDITIONS**	**MIN.**	**TYP.**	**MAX.**	**UNIT**
Static						
Drain-Source Breakdown Voltage	V_{DS}	V_{GS} = 0, I_D = -250 µA	-20	-	-	V
V_{DS} Temperature Coefficient	$\Delta V_{DS}/T_J$	I_D = -250 µA	-	-20	-	mV/°C
$V_{GS(th)}$ Temperature Coefficient	$\Delta V_{GS(th)}/T_J$		-	2.2	-	
Gate-Source Threshold Voltage	$V_{GS(th)}$	V_{DS} = V_{GS}, I_D = -250 µA	-0.5	-	-1.3	V
Gate-Source Leakage	I_{GSS}	V_{DS} = 0 V, V_{GS} = ± 12 V	-	-	± 100	nA
Zero Gate Voltage Drain Current	I_{DSS}	V_{DS} = -20 V, V_{GS} = 0 V	-	-	-1	µA
		V_{DS} = -20 V, V_{GS} = 0 V, T_J = 70 °C	-	-	-10	
On-State Drain Current [a]	$I_{D(on)}$	$V_{DS} \leq$ -5 V, V_{GS} = -4.5 V	-5	-	-	A
Drain-Source On-State Resistance [a]	$R_{DS(on)}$	V_{GS} = -4.5 V, I_D = -1.5 A	-	0.026	0.032	Ω
		V_{GS} = -2.5 V, I_D = -1.5 A	-	0.036	0.046	
		V_{GS} = -2 V, I_D = -1 A	-	0.048	0.065	
		V_{GS} = -1.8 V, I_D = -0.5 A	-	0.060	0.120	
Forward Transconductance [a]	g_{fs}	V_{DS} = -10 V, I_D = -1.5 A	-	10	-	S
Dynamic [b]						
Input Capacitance	C_{iss}	V_{DS} = -10 V, V_{GS} = 0 V, f = 1 MHz	-	1300	-	pF
Output Capacitance	C_{oss}		-	250	-	
Reverse Transfer Capacitance	C_{rss}		-	200	-	
Total Gate Charge	Q_g	V_{DS} = -10 V, V_{GS} = -5 V, I_D = -1.5 A	-	20	30	nC
		V_{DS} = -10 V, V_{GS} = -4.5 V, I_D = -1.5 A	-	14.5	22	
Gate-Source Charge	Q_{gs}		-	2	-	
Gate-Drain Charge	Q_{gd}		-	4.1	-	
Gate Resistance	R_g	V_{GS} = -0.1 V, f = 1 MHz	-	7	-	Ω
Turn-On Delay Time	$t_{d(on)}$	V_{DD} = -10 V, R_L = 6.7 Ω $I_D \cong$ -1.5 A, V_{GEN} = -4.5 V, R_g = 1 Ω	-	20	40	ns
Rise Time	t_r		-	25	50	
Turn-Off Delay Time	$t_{d(off)}$		-	50	100	
Fall Time	t_f		-	30	60	
Turn-On Delay Time	$t_{d(on)}$	V_{DD} = -10 V, R_L = 6.7 Ω $I_D \cong$ -1.5 A, V_{GEN} = -10 V, R_g = 1 Ω	-	7	15	
Rise Time	t_r		-	10	20	
Turn-Off Delay Time	$t_{d(off)}$		-	55	110	
Fall Time	t_f		-	30	60	
Drain-Source Body Diode Characteristics						
Continuous Source-Drain Diode Current	I_S	T_C = 25 °C	-	-	-10.8	A
Pulse Diode Forward Current	I_{SM}		-	-	-20	
Body Diode Voltage	V_{SD}	I_S = -1.5 A, V_{GS} = 0	-	-0.8	-1.2	V
Body Diode Reverse Recovery Time	t_{rr}	I_F = -1.5 A, dI/dt = 100 A/µs, T_J = 25 °C	-	40	80	ns
Body Diode Reverse Recovery Charge	Q_{rr}		-	22	45	nC
Reverse Recovery Fall Time	t_a		-	15	-	ns
Reverse Recovery Rise Time	t_b		-	25	-	

Notes


a. Pulse test; pulse width ≤ 300 µs, duty cycle ≤ 2 %.

b. Guaranteed by design, not subject to production testing.


Stresses beyond those listed under "Absolute Maximum Ratings" may cause permanent damage to the device. These are stress ratings only, and functional operation of the device at these or any other conditions beyond those indicated in the operational sections of the specifications is not implied. Exposure to absolute maximum rating conditions for extended periods may affect device reliability.

For technical questions, contact: pmostechsupport@vishay.com
THIS DOCUMENT IS SUBJECT TO CHANGE WITHOUT NOTICE. THE PRODUCTS DESCRIBED HEREIN AND THIS DOCUMENT ARE SUBJECT TO SPECIFIC DISCLAIMERS, SET FORTH AT www.vishay.com/doc?91000


TYPICAL CHARACTERISTICS (25 °C, unless otherwise noted)




Output Characteristics




Transfer Characteristics




On-Resistance vs. Drain Current and Gate Voltage



Capacitance




Gate Charge




On-Resistance vs. Junction Temperature

For technical questions, contact: pmostechsupport@vishay.com
THIS DOCUMENT IS SUBJECT TO CHANGE WITHOUT NOTICE. THE PRODUCTS DESCRIBED HEREIN AND THIS DOCUMENT ARE SUBJECT TO SPECIFIC DISCLAIMERS, SET FORTH AT www.vishay.com/doc?91000


TYPICAL CHARACTERISTICS (25 °C, unless otherwise noted)




Source-Drain Diode Forward Voltage




On-Resistance vs. Gate-to-Source Voltage



Threshold Voltage




Single Pulse Power, Junction-to-Ambient




Safe Operating Area, Junction-to-Ambient

For technical questions, contact: pmostechsupport@vishay.com
THIS DOCUMENT IS SUBJECT TO CHANGE WITHOUT NOTICE. THE PRODUCTS DESCRIBED HEREIN AND THIS DOCUMENT ARE SUBJECT TO SPECIFIC DISCLAIMERS, SET FORTH AT www.vishay.com/doc?91000

TYPICAL CHARACTERISTICS (25 °C, unless otherwise noted)



Current Derating*




Power Derating


* The power dissipation P_D is based on T_J (max.) = 150 °C, using junction-to-case thermal resistance, and is more useful in settling the upper dissipation limit for cases where additional heatsinking is used. It is used to determine the current rating, when this rating falls below the package limit.

For technical questions, contact: pmostechsupport@vishay.com
THIS DOCUMENT IS SUBJECT TO CHANGE WITHOUT NOTICE. THE PRODUCTS DESCRIBED HEREIN AND THIS DOCUMENT ARE SUBJECT TO SPECIFIC DISCLAIMERS, SET FORTH AT www.vishay.com/doc?91000

TYPICAL CHARACTERISTICS (25 °C, unless otherwise noted)



Normalized Thermal Transient Impedance, Junction-to-Ambient




Normalized Thermal Transient Impedance, Junction-to-Case


Vishay Siliconix maintains worldwide manufacturing capability. Products may be manufactured at one of several qualified locations. Reliability data for Silicon Technology and Package Reliability represent a composite of all qualified locations. For related documents such as package/tape drawings, part marking, and reliability data, see www.vishay.com/ppg?65906.


For technical questions, contact: pmostechsupport@vishay.com
THIS DOCUMENT IS SUBJECT TO CHANGE WITHOUT NOTICE. THE PRODUCTS DESCRIBED HEREIN AND THIS DOCUMENT ARE SUBJECT TO SPECIFIC DISCLAIMERS, SET FORTH AT www.vishay.com/doc?91000

MICRO FOOT®: 6-Bump
(1.5 mm x 1 mm, 0.5 mm Pitch, 0.250 mm Bump Height)





Mark on Backside of Die





NOTE 5





Recommended Land Pattern

Notes

(unless otherwise specified)

1. Six (6) solder bumps are 95.5/3.8/0.7 Sn/Ag/Cu.
2. Backside surface is coated with a Ti/Ni/Ag layer.
3. Non-solder mask defined copper landing pad.
4. Laser marks on the silicon die back.
5. “b1” is the diameter of the solderable substrate surface, defined by an opening in the solder resist layer solder mask defined.
6. • is the location of pin 1

DIM.	MILLIMETERS			INCHES		
	MIN.	NOM.	MAX.	MIN.	NOM.	MAX.
A	0.510	0.575	0.590	0.0201	0.0226	0.0232
A_1	0.220	0.250	0.280	0.0087	0.0098	0.0110
A_2	0.290	0.300	0.310	0.0114	0.0118	0.0122
b	0.297	0.330	0.363	0.0116	0.0129	0.0143
b1		0.250			0.0098	
e		0.500			0.0197	
s	0.210	0.230	0.250	0.0082	0.0090	0.0098
D	0.920	0.960	1.000	0.0362	0.0378	0.0394
E	1.420	1.460	1.500	0.0559	0.0575	0.0591
K	0.028	0.065	0.102	0.0011	0.0025	0.0040

Note

- Use millimeters as the primary measurement.

ECN: T15-0140-Rev. A, 20-Apr-15
DWG: 6035

For technical questions, contact: pmostechsupport@vishay.com

THIS DOCUMENT IS SUBJECT TO CHANGE WITHOUT NOTICE. THE PRODUCTS DESCRIBED HEREIN AND THIS DOCUMENT ARE SUBJECT TO SPECIFIC DISCLAIMERS, SET FORTH AT www.vishay.com/doc?91000

Disclaimer

ALL PRODUCT, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE TO IMPROVE RELIABILITY, FUNCTION OR DESIGN OR OTHERWISE.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, “Vishay”), disclaim any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product.

Vishay makes no warranty, representation or guarantee regarding the suitability of the products for any particular purpose or the continuing production of any product. To the maximum extent permitted by applicable law, Vishay disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Statements regarding the suitability of products for certain types of applications are based on Vishay's knowledge of typical requirements that are often placed on Vishay products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. Parameters provided in datasheets and / or specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein.

Hyperlinks included in this datasheet may direct users to third-party websites. These links are provided as a convenience and for informational purposes only. Inclusion of these hyperlinks does not constitute an endorsement or an approval by Vishay of any of the products, services or opinions of the corporation, organization or individual associated with the third-party website. Vishay disclaims any and all liability and bears no responsibility for the accuracy, legality or content of the third-party website or for that of subsequent links.

Except as expressly indicated in writing, Vishay products are not designed for use in medical, life-saving, or life-sustaining applications or for any other application in which the failure of the Vishay product could result in personal injury or death. Customers using or selling Vishay products not expressly indicated for use in such applications do so at their own risk. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay. Product names and markings noted herein may be trademarks of their respective owners.

© 2024 VISHAY INTERTECHNOLOGY, INC. ALL RIGHTS RESERVED