

Low Capacitance, 2-Line ESD Protection Diode



20904


20903 1

FEATURES

- Compact LLP75-4L package
- Low package height < 0.6 mm
- 2-line ESD protection
- Low leakage current < 0.1 µA
- Low load capacitance C_D = 1.5 pF
- ESD immunity acc. IEC 61000-4-2
  ± 15 kV contact discharge
  ± 15 kV air discharge
- High surge current acc. IEC 61000-4-5 I_{PP} > 3 A
- Soldering can be checked by standard vision inspection. no X-ray necessary
- e4 - precious metal (e.g. Ag, Au, NiPd, NiPdAu) (no Sn)
- Material categorization: for definitions of compliance please see www.vishay.com/doc?99912


Pb-free

e4

RoHS COMPLIANT

HALOGEN FREE GREEN (5-2008)

MARKING (example only)



21001

Dot = pin 1 marking
YY = type code (see table below)
XX = date code

DESIGN SUPPORT TOOLS

click logo to get started

3D Models Available

ORDERING INFORMATION

DEVICE NAME	ORDERING CODE	TAPED UNITS PER REEL (8 mm TAPE ON 7" REEL)	MINIMUM ORDER QUANTITY
VBUS052BD-HTF	VBUS052BD-HTF-GS08	3000	15 000

PACKAGE DATA

DEVICE NAME	PACKAGE NAME	TYPE CODE	WEIGHT	MOLDING COMPOUND FLAMMABILITY RATING	MOISTURE SENSITIVITY LEVEL	SOLDERING CONDITIONS
VBUS052BD-HTF	LLP75-4L	U7	4.2 mg	UL 94 V-0	MSL level 1 (according J-STD-020)	Peak temperature max. 260 °C

ABSOLUTE MAXIMUM RATINGS VBUS052BD-HTF

RATING	TEST CONDITIONS	SYMBOL	VALUE	UNIT
Peak pulse current	Acc. IEC 61000-4-5, t_p = 8/20 µs/single shot	I_{PPM}	3	A
Peak pulse power	Acc. IEC 61000-4-5, t_P = 8/20 µs/single shot	P_{PP}	45	W
ESD immunity	Contact discharge acc. IEC 61000-4-2; 10 pulses	V_{ESD}	± 15	kV
	Air discharge acc. IEC 61000-4-2; 10 pulses		± 15	kV
Operating temperature	Junction temperature	T_J	-40 to +125	°C
Storage temperature		T_{STG}	-40 to +150	°C

For technical questions, contact: ESDprotection@vishay.com

THIS DOCUMENT IS SUBJECT TO CHANGE WITHOUT NOTICE. THE PRODUCTS DESCRIBED HEREIN AND THIS DOCUMENT ARE SUBJECT TO SPECIFIC DISCLAIMERS, SET FORTH AT www.vishay.com/doc?91000

APPLICATION NOTE

The VBUS052BD-HTF is a two-line ESD protection device with the characteristic of a Z-diode with a high ESD immunity and a very low capacitance which makes it usable for high frequency applications like USB2.0 or HDMI.
With the VBUS052BD-HTF two high speed data lines can be protected against transient voltage signals like ESD (electro static discharge). Connected to the data line (pin 1 and 2) and to ground (pin 3) negative transients will be clamped close below the ground level while positive transients will be clamped close above the 5 V working range. The clamping behavior of the VBUS052BD-HTF is bidirectional but asymmetrical (BiAs) and so it offers the best protection for applications running up to 5 V.

ELECTRICAL CHARACTERISTICS VBUS052BD-HTF						
PARAMETER	**TEST CONDITIONS/REMARKS**	**SYMBOL**	**MIN.**	**TYP.**	**MAX.**	**UNIT**
Protection paths	Number of lines which can be protected	$N_{channel}$	-	-	2	lines
Reverse stand-off voltage	at I_R = 0.1 µA; pin 1 or pin 2 to pin 3	V_{RWM}	-	-	5	V
Reverse current	at $V_R = V_{RWM}$ = 5 V; pin 1 or pin 2 to pin 3	I_R	-	< 0.01	0.1	µA
Reverse breakdown voltage	at I_R = 1 mA; pin 1 or pin 2 to pin 3	V_{BR}	6.9	7.9	8.7	V
Reverse clamping voltage	at I_{PP} = 3 A, acc. IEC 61000-4-5; pin 1 or pin 2 to pin 3	V_C	-	-	16	V
Forward clamping voltage	at I_F = 3 A, acc. IEC 61000-4-5; pin 3 to pin 1 or pin 2	V_F	-	4.8	6	V
Capacitance	at V_R = 0 V; f = 1 MHz; pin 1 or pin 2 to pin 3	C_D	-	1.5	2.5	pF

Note

- Ratings at 25 °C, ambient temperature unless otherwise specified

TYPICAL CHARACTERISTICS T_{amb} = 25 °C, unless otherwise specified




Fig. 1 - ESD Discharge Current Wave Form acc. IEC 61000-4-2 (330 Ω/150 pF)




Fig. 3 - Typical Capacitance C_D vs. Reverse Voltage V_R




Fig. 2 - 8/20 µs Peak Pulse Current Wave Form acc. IEC 61000-4-5




Fig. 4 - Typical Forward Current I_F vs. Forward Voltage V_F

For technical questions, contact: ESDprotection@vishay.com

THIS DOCUMENT IS SUBJECT TO CHANGE WITHOUT NOTICE. THE PRODUCTS DESCRIBED HEREIN AND THIS DOCUMENT ARE SUBJECT TO SPECIFIC DISCLAIMERS, SET FORTH AT www.vishay.com/doc?91000




Fig. 5 - Typical Reverse Voltage V_R vs. Reverse Current I_R




Fig. 8 - Typical Clamping Performance at - 8 kV Contact Discharge (acc. IEC 61000-4-2)




Fig. 6 - Typical Clamping Voltage vs. Peak Pulse Current I_{PP}




Fig. 9 - Typical Peak Clamping Voltage at ± ESD Contact Discharge (acc. IEC 61000-4-2)





Fig. 7 - Typical Clamping Performance at + 8 kV Contact Discharge (acc. IEC 61000-4-2)

For technical questions, contact: ESDprotection@vishay.com
THIS DOCUMENT IS SUBJECT TO CHANGE WITHOUT NOTICE. THE PRODUCTS DESCRIBED HEREIN AND THIS DOCUMENT ARE SUBJECT TO SPECIFIC DISCLAIMERS, SET FORTH AT www.vishay.com/doc?91000

PACKAGE DIMENSIONS in millimeters (inches): **LLP75-4L**




Foot print recommendation:

Document no.:S8-V-3906.02-015 (4)
Created - Date: 04. September 2007
Rev. 2 - Date: 09. Sep. 2008
20906

For technical questions, contact: ESDprotection@vishay.com

THIS DOCUMENT IS SUBJECT TO CHANGE WITHOUT NOTICE. THE PRODUCTS DESCRIBED HEREIN AND THIS DOCUMENT ARE SUBJECT TO SPECIFIC DISCLAIMERS, SET FORTH AT www.vishay.com/doc?91000



For technical questions, contact: ESDprotection@vishay.com
THIS DOCUMENT IS SUBJECT TO CHANGE WITHOUT NOTICE. THE PRODUCTS DESCRIBED HEREIN AND THIS DOCUMENT ARE SUBJECT TO SPECIFIC DISCLAIMERS, SET FORTH AT www.vishay.com/doc?91000

Disclaimer

ALL PRODUCT, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE TO IMPROVE RELIABILITY, FUNCTION OR DESIGN OR OTHERWISE.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, “Vishay”), disclaim any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product.

Vishay makes no warranty, representation or guarantee regarding the suitability of the products for any particular purpose or the continuing production of any product. To the maximum extent permitted by applicable law, Vishay disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Statements regarding the suitability of products for certain types of applications are based on Vishay's knowledge of typical requirements that are often placed on Vishay products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. Parameters provided in datasheets and / or specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein.

Hyperlinks included in this datasheet may direct users to third-party websites. These links are provided as a convenience and for informational purposes only. Inclusion of these hyperlinks does not constitute an endorsement or an approval by Vishay of any of the products, services or opinions of the corporation, organization or individual associated with the third-party website. Vishay disclaims any and all liability and bears no responsibility for the accuracy, legality or content of the third-party website or for that of subsequent links.

Except as expressly indicated in writing, Vishay products are not designed for use in medical, life-saving, or life-sustaining applications or for any other application in which the failure of the Vishay product could result in personal injury or death. Customers using or selling Vishay products not expressly indicated for use in such applications do so at their own risk. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay. Product names and markings noted herein may be trademarks of their respective owners.

© 2024 VISHAY INTERTECHNOLOGY, INC. ALL RIGHTS RESERVED