
# Silicon PIN Photodiode, RoHS Compliant



94 8480

## FEATURES

- Package type: leaded
- Package form: side view
- Dimensions (L x W x H in mm): 5 x 4 x 6.8
- Radiant sensitive area (in $mm^2$): 7.5
- High radiant sensitivity
- Daylight blocking filter matched with 870 nm to 950 nm emitters
- Fast response times
- Angle of half sensitivity: $\varphi = \pm 65°$
- Lead (Pb)-free component in accordance with RoHS 2002/95/EC and WEEE 2002/96/EC

Pb-free

e4

RoHS COMPLIANT

## DESCRIPTION

BPW82 is a PIN photodiode with high speed and high radiant sensitivity in a black, side view plastic package with daylight blocking filter. Filter bandwidth is matched with 870 nm to 950 nm IR emitters.

## APPLICATIONS

- High speed detector for infrared radiation
- Infrared remote control and free air data transmission systems, e.g. in combination with TSFFxxxx series IR emitters

## PRODUCT SUMMARY

| COMPONENT | $I_{ra}$ (µA) | $\varphi$ (deg) | $\lambda_{0.5}$ (nm) |
|---|---|---|---|
| BPW82 | 45 | ± 65 | 790 to 1050 |

**Note**

Test condition see table “Basic Characteristics”

## ORDERING INFORMATION

| ORDERING CODE | PACKAGING | REMARKS | PACKAGE FORM |
|---|---|---|---|
| BPW82 | Bulk | MOQ: 4000 pcs, 4000 pcs/bulk | Side view |

**Note**

MOQ: minimum order quantity

## ABSOLUTE MAXIMUM RATINGS

| PARAMETER | TEST CONDITION | SYMBOL | VALUE | UNIT |
|---|---|---|---|---|
| Reverse voltage | | $V_R$ | 60 | V |
| Power dissipation | $T_{amb} \leq 25$ °C | $P_V$ | 215 | mW |
| Junction temperature | | $T_j$ | 100 | °C |
| Operating temperature range | | $T_{amb}$ | - 40 to + 100 | °C |
| Storage temperature range | | $T_{stg}$ | - 40 to + 100 | °C |
| Soldering temperature | $t \leq 5$ s | $T_{sd}$ | 260 | °C |
| Thermal resistance junction/ambient | Connected with Cu wire, 0.14 $mm^2$ | $R_{thJA}$ | 350 | K/W |

**Note**

$T_{amb}$ = 25 °C, unless otherwise specified

| BASIC CHARACTERISTICS | | | | | | |
|---|---|---|---|---|---|---|
| **PARAMETER** | **TEST CONDITION** | **SYMBOL** | **MIN.** | **TYP.** | **MAX.** | **UNIT** |
| Breakdown voltage | $I_R$ = 100 µA, E = 0 | $V_{(BR)}$ | 60 | | | V |
| Reverse dark current | $V_R$ = 10 V, E = 0 | $I_{ro}$ | | 2 | 30 | nA |
| Diode capacitance | $V_R$ = 0 V, f = 1 MHz, E = 0 | $C_D$ | | 70 | | pF |
| | $V_R$ = 3 V, f = 1 MHz, E = 0 | $C_D$ | | 25 | 40 | pF |
| Open circuit voltage | $E_e$ = 1 mW/cm², λ = 870 nm | $V_o$ | | 350 | | mV |
| Short circuit current | $E_e$ = 1 mW/cm², λ = 870 nm | $I_k$ | | 38 | | µA |
| Reverse light current | $E_e$ = 1 mW/cm², λ = 870 nm, $V_R$ = 5 V | $I_{ra}$ | 43 | 45 | | µA |
| Angle of half sensitivity | | φ | | ± 65 | | deg |
| Wavelength of peak sensitivity | | $\lambda_p$ | | 950 | | nm |
| Range of spectral bandwidth | | $\lambda_{0.5}$ | | 790 to 1050 | | nm |
| Noise equivalent power | $V_R$ = 10 V, λ = 870 nm | NEP | | $4 \times 10^{-14}$ | | W/√Hz |
| Rise time | $V_R$ = 10 V, $R_L$ = 1 kΩ, λ = 820 nm | $t_r$ | | 100 | | ns |
| Fall time | $V_R$ = 10 V, $R_L$ = 1 kΩ, λ = 820 nm | $t_f$ | | 100 | | ns |

**Note**

$T_{amb}$ = 25 °C, unless otherwise specified

## BASIC CHARACTERISTICS

$T_{amb}$ = 25 °C, unless otherwise specified





Fig. 1 - Reverse Dark Current vs. Ambient Temperature





Fig. 2 - Relative Reverse Light Current vs. Ambient Temperature





Fig. 3 - Reverse Light Current vs. Irradiance





Fig. 6 - Relative Spectral Sensitivity vs. Wavelength





Fig. 4 - Reverse Light Current vs. Reverse Voltage





Fig. 7 - Relative Radiant Sensitivity vs. Angular Displacement






Fig. 5 - Diode Capacitance vs. Reverse Voltage

**PACKAGE DIMENSIONS** in millimeters




Drawing-No.: 6.544-5108.01-4
Issue:1; 01.07.96
96 12195

# Disclaimer

ALL PRODUCT, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE TO IMPROVE RELIABILITY, FUNCTION OR DESIGN OR OTHERWISE.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, “Vishay”), disclaim any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product.

Vishay makes no warranty, representation or guarantee regarding the suitability of the products for any particular purpose or the continuing production of any product. To the maximum extent permitted by applicable law, Vishay disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Statements regarding the suitability of products for certain types of applications are based on Vishay's knowledge of typical requirements that are often placed on Vishay products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. Parameters provided in datasheets and / or specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein.

Hyperlinks included in this datasheet may direct users to third-party websites. These links are provided as a convenience and for informational purposes only. Inclusion of these hyperlinks does not constitute an endorsement or an approval by Vishay of any of the products, services or opinions of the corporation, organization or individual associated with the third-party website. Vishay disclaims any and all liability and bears no responsibility for the accuracy, legality or content of the third-party website or for that of subsequent links.

Except as expressly indicated in writing, Vishay products are not designed for use in medical, life-saving, or life-sustaining applications or for any other application in which the failure of the Vishay product could result in personal injury or death. Customers using or selling Vishay products not expressly indicated for use in such applications do so at their own risk. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay. Product names and markings noted herein may be trademarks of their respective owners.

*© 2024 VISHAY INTERTECHNOLOGY, INC. ALL RIGHTS RESERVED*