

Optocoupler, Power Phototriac





PIN	FUNCTION
2	LED anode
3	LED cathode
4	No connection
5	No connection
6	No connection
7	No connection
9, 13	Triac T2
11	Triac T1
15	Triac gate

FEATURES

- Maximum trigger current (I_{FT}): 10 mA
- Isolation test voltage 5300 V_{RMS}
- Peak off-state voltage 600 V
- Load current 1 A
- dV/dt of 500 V/µs
- Pure tin leads

Pb-free

e3

RoHS COMPLIANT

APPLICATIONSFIE

- Triac driver
- Programable controllers
- AC-output module

AGENCY APPROVALS

- UL - E52744 system code H
- CUL - E52744 system code H
- VDE - DIN EN 60747-5-5 (VDE 0884-5)


DESCRIPTION

The VO3526 is an optically couple phototriac driving a power triac in a DIP-10 (16) package.

ORDERING INFORMATION

V	O	3	5	2	6	-	X	0	0	#

PART NUMBER — PACKAGE OPTION



AGENCY CERTIFIED / PACKAGE	TRIGGER, CURRENT I_{FT} (mA)
VDE, UL, cUL	**10**
DIP-10, tubes	VO3526

Note

- For additional information on the possible lead bend and VDE options refer to option information.

ABSOLUTE MAXIMUM RATINGS (T_{amb} = 25 °C, unless otherwise specified)

PARAMETER	TEST CONDITION	SYMBOL	VALUE	UNIT
INPUT				
LED continuous forward current		I_F	50	mA
LED reverse voltage		V_R	5.0	V
OUTPUT				
Repetitive peak off-state voltage	Sine wave, 50 to 60 Hz, gate open	V_{DRM}	600	V
On-state RMS current		$I_{T(RMS)}$	1.0	A
Peak nonrepetitive surge current (50 Hz, peak)		I_{TSM}	10	A

For technical questions, contact: optocoupleranswers@vishay.com

THIS DOCUMENT IS SUBJECT TO CHANGE WITHOUT NOTICE. THE PRODUCTS DESCRIBED HEREIN AND THIS DOCUMENT ARE SUBJECT TO SPECIFIC DISCLAIMERS, SET FORTH AT www.vishay.com/doc?91000

ABSOLUTE MAXIMUM RATINGS (T_{amb} = 25 °C, unless otherwise specified)				
PARAMETER	**TEST CONDITION**	**SYMBOL**	**VALUE**	**UNIT**
COUPLER				
Total power dissipation		P_{diss}	1.2	W
Ambient temperature range		T_{amb}	-40 to +85	°C
Storage temperature range		T_{stg}	-40 to +125	°C
Soldering temperature (1)	t ≤ 10 s max.	T_{sld}	260	°C
Isolation test voltage	for 1.0 s	V_{ISO}	5300	V_{RMS}

Notes

- Stresses in excess of the absolute maximum ratings can cause permanent damage to the device. Functional operation of the device is not implied at these or any other conditions in excess of those given in the operational sections of this document. Exposure to absolute maximum ratings for extended periods of the time can adversely affect reliability

(1) Refer to wave profile for soldering conditions for through hole devices

(2) Total power dissipation value is based on 2S2P PCB. Refer to power phototriac application note for PCB design tips

ABSOLUTE MAXIMUM RATING CURVES




Fig. 1 - Power Dissipation vs. Temperature




Fig. 2 - Allowable Load Current vs. Ambient Temperature

Note

- The allowable load current was calculated out under a given operating conditions and only for reference:
  LED power: Q_E = 0.015 W, θ_{BA} (4-layer) = 30 °C/W


THERMAL CHARACTERISTICS			
PARAMETER	**SYMBOL**	**VALUE**	**UNIT**
Maximum LED junction temperature	$T_{jmax.}$	105	°C
Maximum NOT junction temperature	$T_{jmax.}$	105	°C
Thermal resistance, junction NOT to bord	θ_{NOT-B}	75	°C/W
Thermal resistance, junction NOT to case	θ_{NOT-C}	150	°C/W
Thermal resistance, junction OT to board	θ_{OT-B}	158	°C/W
Thermal resistance, junction OT to case	θ_{OT-C}	157	°C/W
Thermal resistance, junction emitter to board	θ_{E-B}	149	°C/W
Thermal resistance, junction emitter to case	θ_{E-C}	161	°C/W
Thermal resistance, junction NOT to junction OT	θ_{NOT-OT}	243	°C/W
Thermal resistance, junction emitter to junction NOT	θ_{E-NOT}	420	°C/W
Thermal resistance, junction emitter to junction OT	θ_{E-OT}	235	°C/W
Thermal resistance, case to ambient	θ_{CA}	130	°C/W

Note

- The thermal model is represented in the thermal network below. Each resistance value given in this model can be used to calculate the temperatures at each node for a given operating condition. The thermal resistance from board to ambient will be dependent on the type of PCB, layout and thickness of copper traces. For a detailed explanation of the thermal model, please reference Vishay's Thermal Characteristics of Power Phototriac application note

For technical questions, contact: optocoupleranswers@vishay.com

THIS DOCUMENT IS SUBJECT TO CHANGE WITHOUT NOTICE. THE PRODUCTS DESCRIBED HEREIN AND THIS DOCUMENT ARE SUBJECT TO SPECIFIC DISCLAIMERS, SET FORTH AT www.vishay.com/doc?91000



Thermal Model

NOT: Non-opto-triac
OT: Opto-triac
T_B: Board temperature
T_{CASE}: Case temperature
T_A: Ambient temperature
θ_{BA}: Thermal resistance, board to ambient
Q_E: LED power dissipation
Q_{OT}: OT power dissipation
Q_{NOT}: NOT power dissipation

ELECTRICAL CHARACTERISTICS (T_{amb} = 25 °C, unless otherwise specified)						
PARAMETER	**TEST CONDITION**	**SYMBOL**	**MIN.**	**TYP.**	**MAX.**	**UNIT**
INPUT						
LED trigger current	V_T = 6 V	I_{FT}	-	-	10	mA
Input reverse current	V_R = 5 V	I_R	-	-	10	µA
LED forward voltage	I_F = 10 mA	V_F	0.9	-	1.4	V
OUTPUT						
Peak on-state voltage	I_{TM} = 1.5 A	V_{TM}	-	-	1.7	V
Repetitive peak off-state current	V_{DRM} = 600 V, T_A = 110 °C, 60 Hz	I_{DRM}	-	-	100	µA
Holding current	R_L = 100 Ω	I_H	-	-	25	mA
Critical rate of rise of off-state voltage	V_{IN} = 400 V (Fig. 3)	dV/dt_{cr}	-	210	-	V/µs
Critical rate of rise of commutating voltage	V_{IN} = 240 V_{RMS}, I_T = 1 A_{RMS} (Fig. 3)	dV/dt_{crq}	-	0.9	-	V/µs

Note

- Minimum and maximum values are testing requirements. Typical values are characteristics of the device and are the result of engineering evaluations. Typical values are for information only and are not part of the testing requirements




Fig. 3 - dV/dt Test Circuit

For technical questions, contact: optocoupleranswers@vishay.com
THIS DOCUMENT IS SUBJECT TO CHANGE WITHOUT NOTICE. THE PRODUCTS DESCRIBED HEREIN AND THIS DOCUMENT ARE SUBJECT TO SPECIFIC DISCLAIMERS, SET FORTH AT www.vishay.com/doc?91000

RECOMMENDED OPERATING CONDITIONS

PARAMETER			TEST CONDITION	SYMBOL	MIN.	MAX.	UNIT
Forward current at on-state		Input		$I_{F(ON)}$	10	20	mA
Forward current at off-state				$I_{F(OFF)}$	0	0.1	mA
Load supply voltage		Output	With snubber (0.022 µF, 47 Ω)	$V_{OUT(RMS)}$	-	240	V
On-state RMS current	T_A = 40 °C		On 4-layer PCB (R_{BA} = 30 °C/W)	$I_{OUT(RMS)}$	-	0.8	A
	T_A = 60 °C				-	0.6	A
Frequency				f	50	60	Hz
Operating temperature					- 40	85	°C

SAFETY AND INSULATION RATINGS

PARAMETER		TEST CONDITION	SYMBOL	MIN.	TYP.	MAX.	UNIT
Climatic classification		IEC 68 part 1		-	40 / 85 / 21	-	
Pollution degree		DIN VDE 0109		-	2	-	
Tracking resistance (comparative tracking index)		Insulation group IIIa	CTI	175	-	-	
Highest allowable overvoltage		Transient overvoltage	V_{IOTM}	8000	-	-	V_{peak}
Maximum working insulation voltage		Recurring peak voltage	V_{IORM}	890	-	-	V_{peak}
Insulation resistance at 25 °C		V_{IO} = 500 V	R_{IS}	-	-	$\geq 10^{12}$	Ω
Insulation resistance at T_S		V_{IO} = 500 V	R_{IS}	-	-	$\geq 10^{9}$	Ω
Insulation resistance at 100 °C		V_{IO} = 500 V	R_{IS}	-	-	$\geq 10^{11}$	Ω
Partial discharge test voltage		Method b, $V_{pd} = V_{IORM}$ x 1.6	V_{pd}	-	-	1424	V_{peak}
Safety limiting values - maximum values allowed in the event of a failure	Output power		P_{SO}	-	-	2	W
	Input current		I_{SI}	-	-	150	mA
	Case temperature		T_{SI}	-	-	165	°C
Minimum external air gap (clearance)		Measured from input terminals to output terminals, shortest distance through air		≥ 7	-	-	mm
Minimum external tracking (creepage)		Measured from input terminals to output terminals, shortest distance path along body		≥ 7	-	-	mm

Note

- This phototriac coupler is suitable for 'safe electrical insulation' only within the safety ratings. Compliance with safety ratings shall be ensured by means of protective circuits

For technical questions, contact: optocoupleranswers@vishay.com

THIS DOCUMENT IS SUBJECT TO CHANGE WITHOUT NOTICE. THE PRODUCTS DESCRIBED HEREIN AND THIS DOCUMENT ARE SUBJECT TO SPECIFIC DISCLAIMERS, SET FORTH AT www.vishay.com/doc?91000

TYPICAL CHARACERISTICS (T_{amb} = 25 °C, unless otherwise specified)




Fig. 4 - Forward Current vs. Forward Voltage




Fig. 7 - Off-State Leakage Current vs. Voltage




Fig. 5 - Diode Reverse Voltage vs. Temperature




Fig. 8 - Normalized Trigger Input Current vs. Temperature




Fig. 6 - On-State Current vs. On State Voltage




Fig. 9 - Trigger Input Current vs. Turn-on Time

For technical questions, contact: optocoupleranswers@vishay.com
THIS DOCUMENT IS SUBJECT TO CHANGE WITHOUT NOTICE. THE PRODUCTS DESCRIBED HEREIN AND THIS DOCUMENT ARE SUBJECT TO SPECIFIC DISCLAIMERS, SET FORTH AT www.vishay.com/doc?91000




Fig. 10 - Normalized Holding Current vs. Temperature




Fig. 11 - Trigger Current vs. Trigger Pulse Width





Fig. 12 - Trigger Current vs. V_{load}


For technical questions, contact: optocoupleranswers@vishay.com

THIS DOCUMENT IS SUBJECT TO CHANGE WITHOUT NOTICE. THE PRODUCTS DESCRIBED HEREIN AND THIS DOCUMENT ARE SUBJECT TO SPECIFIC DISCLAIMERS, SET FORTH AT www.vishay.com/doc?91000

PACKAGE DIMENSIONS in inches (millimeters)



PACKAGE MARKING



For technical questions, contact: optocoupleranswers@vishay.com

THIS DOCUMENT IS SUBJECT TO CHANGE WITHOUT NOTICE. THE PRODUCTS DESCRIBED HEREIN AND THIS DOCUMENT ARE SUBJECT TO SPECIFIC DISCLAIMERS, SET FORTH AT www.vishay.com/doc?91000

Disclaimer

ALL PRODUCT, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE TO IMPROVE RELIABILITY, FUNCTION OR DESIGN OR OTHERWISE.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, “Vishay”), disclaim any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product.

Vishay makes no warranty, representation or guarantee regarding the suitability of the products for any particular purpose or the continuing production of any product. To the maximum extent permitted by applicable law, Vishay disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Statements regarding the suitability of products for certain types of applications are based on Vishay's knowledge of typical requirements that are often placed on Vishay products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. Parameters provided in datasheets and / or specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein.

Hyperlinks included in this datasheet may direct users to third-party websites. These links are provided as a convenience and for informational purposes only. Inclusion of these hyperlinks does not constitute an endorsement or an approval by Vishay of any of the products, services or opinions of the corporation, organization or individual associated with the third-party website. Vishay disclaims any and all liability and bears no responsibility for the accuracy, legality or content of the third-party website or for that of subsequent links.

Except as expressly indicated in writing, Vishay products are not designed for use in medical, life-saving, or life-sustaining applications or for any other application in which the failure of the Vishay product could result in personal injury or death. Customers using or selling Vishay products not expressly indicated for use in such applications do so at their own risk. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay. Product names and markings noted herein may be trademarks of their respective owners.

© 2024 VISHAY INTERTECHNOLOGY, INC. ALL RIGHTS RESERVED