


Bicolor LED in Ø 5 mm Untinted Diffused Package



19230

PRODUCT GROUP AND PACKAGE DATA

- Product group: LED
- Package: 5 mm
- Product series: bicolor
- Angle of half intensity: $\pm 30^\circ$

FEATURES

- Even luminance of the emitting surface
- Ideal as flush mounted panel indicators
- For DC and pulse operation
- Color mixing possible due to separate anode terminals
- Luminous intensity selected into groups
- Categorized for green color
- Wide viewing angle
- Common cathode
- Material categorization: For definitions of compliance please see www.vishay.com/doc?99912



RoHS
 COMPLIANT
 HALOGEN
FREE
GREEN
 (5-2008)

APPLICATIONS

- Indicating and illumination purposes

PARTS TABLE

PART	COLOR	LUMINOUS INTENSITY (mcd)			at I _F (mA)	WAVELENGTH (nm)			at I _F (mA)	FORWARD VOLTAGE (V)			at I _F (mA)	TECHNOLOGY
		MIN.	TYP.	MAX.		MIN.	TYP.	MAX.		MIN.	TYP.	MAX.		
TLUV5300	Red	1	2.5	-	10	612	-	625	10	-	2	3	20	GaAsP on GaP
TLUV5300	Green	1	2.5	-	10	552	-	575	10	-	2.4	3	20	GaAsP on GaP

ABSOLUTE MAXIMUM RATINGS (T_{amb} = 25 °C, unless otherwise specified)

TLUV5300

PARAMETER	TEST CONDITION	SYMBOL	VALUE	UNIT
Reverse voltage per diode		V _R	6	V
DC forward current per diode		I _F	30	mA
Surge forward current per diode	t _p ≤ 10 μs	I _{FSM}	1	A
Power dissipation per diode	T _{amb} ≤ 55 °C	P _V	100	mW
Total power dissipation	T _{amb} ≤ 55 °C	P _{tot}	150	mW
Junction temperature		T _j	100	°C
Operating temperature range		T _{amb}	- 40 to + 100	°C
Storage temperature range		T _{stg}	- 55 to + 100	°C
Soldering temperature	t ≤ 5 s, 2 mm from body	T _{sd}	260	°C
Thermal resistance junction/ambient per diode		R _{thJA}	450	K/W
Thermal resistance junction/ambient total		R _{thJA}	300	K/W



OPTICAL AND ELECTRICAL CHARACTERISTICS (T _{amb} = 25 °C, unless otherwise specified) TLUV5300, RED						
PARAMETER	TEST CONDITION	SYMBOL	MIN.	TYP.	MAX.	UNIT
Per diode						
Luminous intensity ⁽¹⁾	I _F = 10 mA	I _V	1	2.5	-	mcd
Dominant wavelength	I _F = 10 mA	λ _d	612	-	625	nm
Peak wavelength	I _F = 10 mA	λ _p	-	630	-	nm
Angle of half intensity	I _F = 10 mA	φ	-	± 30	-	deg
Forward voltage	I _F = 20 mA	V _F	-	2	3	V
Reverse voltage	I _R = 10 μA	V _R	6	15	-	V
Junction capacitance	V _R = 0 V, f = 1 MHz	C _j	-	50	-	pF

Note

(1) In one packing unit I_{Vmin}/I_{Vmax} ≤ 0.5

OPTICAL AND ELECTRICAL CHARACTERISTICS (T _{amb} = 25 °C, unless otherwise specified) TLUV5300, GREEN						
PARAMETER	TEST CONDITION	SYMBOL	MIN.	TYP.	MAX.	UNIT
Per diode						
Luminous intensity ⁽¹⁾	I _F = 10 mA	I _V	1	2.5	-	mcd
Dominant wavelength	I _F = 10 mA	λ _d	552	-	575	nm
Peak wavelength	I _F = 10 mA	λ _p	-	565	-	nm
Angle of half intensity	I _F = 10 mA	φ	-	±30	-	deg
Forward voltage	I _F = 20 mA	V _F	-	2.4	3	V
Reverse voltage	I _R = 10 μA	V _R	6	15	-	V
Junction capacitance	V _R = 0 V, f = 1 MHz	C _j	-	50	-	pF

Note

(1) In one packing unit I_{Vmin}/I_{Vmax} ≤ 0.5

TYPICAL CHARACTERISTICS (T_{amb} = 25 °C, unless otherwise specified)




Fig. 1 - Power Dissipation vs. Ambient Temperature




Fig. 2 - Forward Current vs. Ambient Temperature for InGaN




Fig. 3 - Forward Current vs. Pulse Length




Fig. 6 - Relative Luminous Intensity vs. Ambient Temperature




Fig. 4 - Relative Luminous Intensity vs. Angular Displacement




Fig. 7 - Relative Luminous Intensity vs. Forward Current/Duty Cycle




Fig. 5 - Forward Current vs. Forward Voltage




Fig. 8 - Relative Luminous Intensity vs. Forward Current




Fig. 9 - Relative Intensity vs. Wavelength




Fig. 12 - Specific Luminous Intensity vs. Forward Current




Fig. 10 - Forward Current vs. Forward Voltage




Fig. 13 - Relative Luminous Intensity vs. Forward Current




Fig. 11 - Relative Luminous Intensity vs. Ambient Temperature





Fig. 14 - Relative Intensity vs. Wavelength



PACKAGE DIMENSIONS in millimeters



95 11271



Disclaimer

ALL PRODUCT, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE TO IMPROVE RELIABILITY, FUNCTION OR DESIGN OR OTHERWISE.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product.

Vishay makes no warranty, representation or guarantee regarding the suitability of the products for any particular purpose or the continuing production of any product. To the maximum extent permitted by applicable law, Vishay disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Statements regarding the suitability of products for certain types of applications are based on Vishay's knowledge of typical requirements that are often placed on Vishay products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. Parameters provided in datasheets and / or specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein.

Hyperlinks included in this datasheet may direct users to third-party websites. These links are provided as a convenience and for informational purposes only. Inclusion of these hyperlinks does not constitute an endorsement or an approval by Vishay of any of the products, services or opinions of the corporation, organization or individual associated with the third-party website. Vishay disclaims any and all liability and bears no responsibility for the accuracy, legality or content of the third-party website or for that of subsequent links.

Vishay products are not designed for use in life-saving or life-sustaining applications or any application in which the failure of the Vishay product could result in personal injury or death unless specifically qualified in writing by Vishay. Customers using or selling Vishay products not expressly indicated for use in such applications do so at their own risk. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay. Product names and markings noted herein may be trademarks of their respective owners.