





Dual-Line Unidirectional ESD Protection Diode in SOT-23




20456



20512

1

MARKING (example only)



20357

YYY = type code (see table below)

XX = date code

FEATURES

- Small SOT-23 package
- AEC-Q101 qualified available
- 2-line unidirectional ESD protection
- Working range 33 V
- Low leakage current $I_R < 0.05 \mu A$
- Low load capacitance $C_D < 18 \text{ pF}$
- ESD immunity acc. IEC 61000-4-2
± 15 kV contact discharge
± 15 kV air discharge
- e3 - pins plated with tin (Sn)
- Material categorization: for definitions of compliance please see www.vishay.com/doc?99912



RoHS
COMPLIANT
HALOGEN
FREE
GREEN
(5-2008)

LINKS TO ADDITIONAL RESOURCES



3D Models

ORDERING INFORMATION

PART NUMBER (EXAMPLE)	ENVIRONMENTAL AND QUALITY CODE				PACKAGING CODE		ORDERING CODE (EXAMPLE)
	AEC-Q101 QUALIFIED	RoHS-COMPLIANT + LEAD (Pb)-FREE TERMINATIONS		TIN PLATED	3K PER 7" REEL (8 mm TAPE) 15K/BOX = MOQ	10K PER 13" REEL (8 mm TAPE) 10K/BOX = MOQ	
		STANDARD	GREEN				
VESD33A2-03S	-	G	-	3	-08	-	VESD33A2-03S-G3-08
VESD33A2-03S	H	G	-	3	-08	-	VESD33A2-03SHG3-08
VESD33A2-03S	-	G	-	3	-	-18	VESD33A2-03S-G3-18
VESD33A2-03S	H	G	-	3	-	-18	VESD33A2-03SHG3-18

PACKAGE DATA

DEVICE NAME	PACKAGE NAME	TYPE CODE	WEIGHT	MOLDING COMPOUND FLAMMABILITY RATING	MOISTURE SENSITIVITY LEVEL	SOLDERING CONDITIONS
VESD33A2-03S	SOT-23	D33	8.1 mg	UL 94 V-0	MSL level 1 (according J-STD-020)	Peak temperature max. 260 °C

ABSOLUTE MAXIMUM RATINGS ($T_{amb} = 25 \text{ }^{\circ}\text{C}$, between pin 1 - 3 or 2 - 3, unless otherwise specified)

PARAMETER	TEST CONDITIONS	SYMBOL	VALUE	UNIT
Peak pulse current	Acc. IEC 61000-4-5, 8/20 μs /single shot	I_{PPM}	1.6	A
Peak pulse power	Acc. IEC 61000-4-5, 8/20 μs /single shot	P_{PP}	100	W
ESD immunity	Contact discharge acc. IEC 61000-4-2; 10 pulses	V_{ESD}	15	kV
	Air discharge acc. IEC 61000-4-2; 10 pulses		15	kV
Operating temperature	Junction temperature	T_J	-55 to +150	°C
Storage temperature		T_{stg}	-55 to +150	°C

**ELECTRICAL CHARACTERISTICS** ($T_{amb} = 25\text{ }^{\circ}\text{C}$, between pin 1 - 3 or 2 - 3, unless otherwise specified)

PARAMETER	TEST CONDITIONS/REMARKS	SYMBOL	MIN.	TYP.	MAX.	UNIT
Protection paths	Number of lines which can be protected	$N_{channel}$	-	-	1	lines
Reverse stand off voltage	Max. reverse working voltage	V_{RWM}	-	-	33	V
Reverse voltage	at $I_R = 0.1\text{ }\mu\text{A}$	V_R	33	-	-	V
Reverse current	at $V_R = 33\text{ V}$	I_R	-	< 0.01	0.1	μA
Reverse breakdown voltage	at $I_R = 1\text{ mA}$	V_{BR}	35.5	37.4	39.3	V
Reverse clamping voltage	at $I_{PP} = I_{PPM} = 1.6\text{ A}$, $t_p = 8/20\text{ }\mu\text{s}$	V_C	-	56	62.5	V
Forward clamping voltage	at $I_{PP} = 1\text{ A}$, $t_p = 300\text{ }\mu\text{s}$	V_F	0.9	1.1	1.2	V
	at $I_{PP} = I_{PPM} = 1.6\text{ A}$, $t_p = 8/20\text{ }\mu\text{s}$	V_F	-	1.22	1.32	V
Dynamic resistance	$t_p = 100\text{ ns}$ (TLP; 1 A to 12 A)	r_{dyn}	-	3.6	-	Ω
Capacitance	at $V_R = 0\text{ V}$; $f = 1\text{ MHz}$	C_D	12	15	18	pF



TYPICAL CHARACTERISTICS ($T_{amb} = 25\text{ }^{\circ}\text{C}$, unless otherwise specified)Fig. 1 - ESD Discharge Current Wave Form
acc. IEC 61000-4-2 (330 Ω / 150 pF)

Fig. 3 - Typical Peak Clamping Voltage vs. Peak Pulse Current



Fig. 2 - 8/20 μs Peak Pulse Current Wave Form
acc. IEC 61000-4-5

Fig. 4 - Typical Capacitance vs. Reverse Voltage




Fig. 5 - Typical Reverse Voltage vs. Reverse Current




Fig. 7 - Typical Forward Voltage vs. Forward Current




Fig. 6 - Typical Clamping Voltage vs. Peak Pulse Current








Fig. 8 - Typical Forward Voltage vs. Forward Current



PACKAGE DIMENSIONS in millimeters (inches) **SOT-23**




Foot print recommendation:



Document no.: 6.541-5014.01-4
Rev. 8 - Date: 23. Sep. 2009
17418

ORIENTATION IN CARRIER TAPE SOT-23




Orientation in carrier tape
SOT-23
S8-V-3929.01-006 (4)
04.02.2010
22607




CARRIER TAPE SOT-23

A-A Section



B-B Section



Carrier tape SOT-23
Document no.: S8-V-3929.01-005 (4)
Created - Date: 04. Feb. 2010
22856



Disclaimer

ALL PRODUCT, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE TO IMPROVE RELIABILITY, FUNCTION OR DESIGN OR OTHERWISE.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product.

Vishay makes no warranty, representation or guarantee regarding the suitability of the products for any particular purpose or the continuing production of any product. To the maximum extent permitted by applicable law, Vishay disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Statements regarding the suitability of products for certain types of applications are based on Vishay's knowledge of typical requirements that are often placed on Vishay products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. Parameters provided in datasheets and / or specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein.

Hyperlinks included in this datasheet may direct users to third-party websites. These links are provided as a convenience and for informational purposes only. Inclusion of these hyperlinks does not constitute an endorsement or an approval by Vishay of any of the products, services or opinions of the corporation, organization or individual associated with the third-party website. Vishay disclaims any and all liability and bears no responsibility for the accuracy, legality or content of the third-party website or for that of subsequent links.

Except as expressly indicated in writing, Vishay products are not designed for use in medical, life-saving, or life-sustaining applications or for any other application in which the failure of the Vishay product could result in personal injury or death. Customers using or selling Vishay products not expressly indicated for use in such applications do so at their own risk. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay. Product names and markings noted herein may be trademarks of their respective owners.