



# Thyristor High Voltage, Phase Control SCR, 50 A


**TO-247AD 3L**


## FEATURES

- Designed and qualified according to JEDEC®-JESD 47
- Low  $I_{GT}$  designed
- 150 °C maximum operating junction temperature
- Material categorization: for definitions of compliance please see [www.vishay.com/doc?99912](http://www.vishay.com/doc?99912)



**RoHS**  
COMPLIANT  
**HALOGEN**  
**FREE**

## APPLICATIONS

Typical usage is in input rectification crowbar (soft start) and AC switch motor control, UPS, welding, and battery charge.

## DESCRIPTION

The VS-50TPS12 high voltage series of silicon controlled rectifiers are specifically designed for medium power switching, and phase control applications. The glass passivation technology used, has reliable operation up to 150 °C junction temperature.

## PRIMARY CHARACTERISTICS

$I_{T(AV)}$	50 A
$V_{DRM}/V_{RRM}$	1200 V
$V_{TM}$ (typ.)	1.1 V
$I_{GT}$ (typ.)	35 mA
$T_J$	-40 °C to +150 °C
Package	TO-247AD 3L
Circuit configuration	Single SCR

## MAJOR RATINGS AND CHARACTERISTICS

PARAMETER	TEST CONDITIONS	VALUES	UNITS
$V_{RRM}/V_{DRM}$		1200	V
$V_T$	50 A, $T_J = 125$ °C	1.1	
$I_{T(AV)}$		50	A
$I_{RMS}$		79	
$I_{TSM}$		630	
$dV/dt$		500	V/μs
$T_J, T_{Stg}$		-40 to +150	°C

## VOLTAGE RATINGS

PART NUMBER	$V_{RRM}/V_{DRM}$ , MAXIMUM REPETITIVE PEAK AND OFF-STATE VOLTAGE V	$V_{RSM}$ , MAXIMUM NON-REPETITIVE PEAK REVERSE VOLTAGE V	$I_{RRM}/I_{DRM}$ AT 125 °C mA
VS-50TPS12AL-M3	1200	1300	10

**ABSOLUTE MAXIMUM RATINGS**

PARAMETER	SYMBOL	TEST CONDITIONS	VALUES		UNITS
			TYP.	MAX.	
Maximum average on-state current	$I_{T(AV)}$	$T_C = 112\text{ }^{\circ}\text{C}$ , 180° conduction half sine wave	-	50	A
Maximum continuous RMS on-state current as AC switch	$I_{T(RMS)}$		-	79	
Peak, one-cycle non-repetitive surge current	$I_{TSM}$	10 ms sine pulse, rated $V_{RRM}$ applied	-	530	
		10 ms sine pulse, no voltage reapplied	-	630	A <sup>2</sup> s
$I^2t$ for fusing	$I^2t$	10 ms sine pulse, rated $V_{RRM}$ applied	-	1405	
		10 ms sine pulse, no voltage reapplied	-	1986	
$I^2\sqrt{t}$ for fusing	$I^2\sqrt{t}$	$t = 0.1\text{ ms to }10\text{ ms}$ , no voltage reapplied, $T_J = 125\text{ }^{\circ}\text{C}$	-	19 850	A <sup>2</sup> √s
Low level value of threshold voltage	$V_{T(TO)1}$	$T_J = 125\text{ }^{\circ}\text{C}$	-	0.89	V
High level value of threshold voltage	$V_{T(TO)2}$		-	0.97	
Low level value of on-state slope resistance	$r_{t1}$		-	6.77	mΩ
High level value of on-state slope resistance	$r_{t2}$		-	6.32	
On-state voltage	$V_T$	50 A, $T_J = 25\text{ }^{\circ}\text{C}$	1.2	1.32	V
		100 A, $T_J = 25\text{ }^{\circ}\text{C}$	1.4	1.6	
Rate of rise of turned-on current	$di/dt$	$T_J = 25\text{ }^{\circ}\text{C}$	-	150	A/μs
Holding current	$I_H$	Anode supply = 6 V, resistive load, $T_J = 25\text{ }^{\circ}\text{C}$	-	300	mA
Latching current	$I_L$		-	350	
Reverse and direct leakage current	$I_{RRM}/I_{DRM}$	$T_J = 25\text{ }^{\circ}\text{C}$	-	0.05	
		$T_J = 125\text{ }^{\circ}\text{C}$	-	10	
Rate of rise of off-state voltage	$dV/dt$	$T_J = T_J\text{ maximum}$ , linear to 80 % $V_{DRM}$ , $R_g\text{-k} = 100\text{ }^{\circ}\Omega$	-	500	V/μs

**TRIGGERING**

PARAMETER	SYMBOL	TEST CONDITIONS	TYP.	MAX.	UNITS
Peak gate power	$P_{GM}$	10 ms sine pulse, no voltage reapplied	-	10	W
Average gate power	$P_{G(AV)}$		-	2.5	
Peak gate current	$I_{GM}$		-	2.5	A
Peak negative gate voltage	$-V_{GM}$		-	10	V
Required DC gate voltage to trigger	$V_{GT}$	$T_J = -40\text{ }^{\circ}\text{C}$	-	1.6	
		$T_J = 25\text{ }^{\circ}\text{C}$	-	1.5	
		$T_J = 150\text{ }^{\circ}\text{C}$	-	1	
Required DC gate to trigger	$I_{GT}$	$T_J = -40\text{ }^{\circ}\text{C}$	-	100	mA
		$T_J = 25\text{ }^{\circ}\text{C}$	35	60	
		$T_J = 150\text{ }^{\circ}\text{C}$	-	40	
DC gate voltage not to trigger	$V_{GD}$	$T_J = 150\text{ }^{\circ}\text{C}$ , $V_{DRM} = \text{rated value}$	-	0.15	V
DC gate current not to trigger	$I_{GD}$		-	2.5	mA

**SWITCHING**

PARAMETER	SYMBOL	TEST CONDITIONS	VALUES	UNITS
Turn-on time	$t_{gt}$	$I_T = 50\text{ A}$ , $V_D = 50\text{ \% }V_{DRM}$ , $I_{gt} = 300\text{ mA}$ , $T_J = 25\text{ }^{\circ}\text{C}$	1.5	μs
Turn-off time	$t_q$	$I_T = 50\text{ A}$ , $V_D = 80\text{ \% }V_{DRM}$ , $dV/dt = 20\text{ V/}\mu\text{s}$ , $t_p = 200\text{ }\mu\text{s}$ , $I_{gt} = 100\text{ mA}$ , $dI/dt = 10\text{ A/}\mu\text{s}$ , $V_R = 100\text{ V}$ , $T_J = 150\text{ }^{\circ}\text{C}$	92	

**THERMAL AND MECHANICAL SPECIFICATIONS**

PARAMETER	SYMBOL	TEST CONDITIONS	TYP.	MAX.	UNITS
Maximum junction and storage temperature range	T <sub>J</sub> , T <sub>Stg</sub>		-40	150	°C
Maximum thermal resistance, junction to case	R <sub>thJC</sub>		-	0.35	°C/W
Maximum thermal resistance, junction to ambient	R <sub>thJA</sub>		-	40	
Typical thermal resistance, case to heatsink	R <sub>thCS</sub>	Mounting surface, smooth, and greased	0.2	-	
Mounting torque	minimum		6 (5)		kgf · cm (lbf · in)
	maximum		12 (10)		
Marking device		Case style Super TO-247AD 3L	50TPS12AL		

 **$\Delta R_{thJ-HS}$  CONDUCTION PER JUNCTION**

DEVICE	SINE HALF-WAVE CONDUCTION					RECTANGULAR WAVE CONDUCTION					UNITS
	180°	120°	90°	60°	30°	180°	120°	90°	60°	30°	
VS-50TPS12L-M3	0.143	0.166	0.208	0.299	0.490	0.099	0.168	0.223	0.311	0.494	°C/W




Fig. 1 - Current Rating Characteristics




Fig. 3 - On-State Power Loss Characteristics




Fig. 2 - Current Rating Characteristics




Fig. 4 - On-State Power Loss Characteristics




Fig. 5 - Maximum Non-Repetitive Surge Current




Fig. 6 - Maximum Non-Repetitive Surge Current




Fig. 7 - On-State Voltage Drop Characteristics





Fig. 8 - Gate Characteristics


Fig. 9 - Thermal Impedance  $Z_{thJC}$  Characteristics

## ORDERING INFORMATION TABLE

Device code	<b>VS-</b>	<b>50</b>	<b>T</b>	<b>P</b>	<b>S</b>	<b>12</b>	<b>A</b>	<b>L</b>	<b>-M3</b>
	①	②	③	④	⑤	⑥	⑦	⑧	⑨

- 1** - Vishay Semiconductors product
- 2** - Current code (50 = 50 A)
- 3** - Circuit configuration:  
T = thyristor
- 4** - P = TO-247AD 3L package
- 5** - Type of silicon:  
S = standard recovery rectifier
- 6** - Voltage code (12 = 1200 V)
- 7** - A = Low  $I_{GT}$  selection
- 8** - Package L = long lead
- 9** - -M3 = halogen-free, RoHS-compliant, and terminations lead (Pb)-free


ORDERING INFORMATION (example)			
PREFERRED P/N	QUANTITY PER TUBE	MINIMUM ORDER QUANTITY	PACKAGING DESCRIPTION
VS-50TPS12AL-M3	25	500	Antistatic plastic tubes

LINKS TO RELATED DOCUMENTS	
Dimensions	<a href="http://www.vishay.com/doc?95626">www.vishay.com/doc?95626</a>
Part marking information	<a href="http://www.vishay.com/doc?95007">www.vishay.com/doc?95007</a>



### TO-247AD 3L

**DIMENSIONS** in millimeters and inches



SYMBOL	MILLIMETERS		INCHES		NOTES
	MIN.	MAX.	MIN.	MAX.	
A	4.65	5.31	0.183	0.209	
A1	2.21	2.59	0.087	0.102	
A2	1.50	2.49	0.059	0.098	
b	0.99	1.40	0.039	0.055	
b1	0.99	1.35	0.039	0.053	
b2	1.65	2.39	0.065	0.094	
b3	1.65	2.34	0.065	0.092	
b4	2.59	3.43	0.102	0.135	
b5	2.59	3.38	0.102	0.133	
c	0.38	0.89	0.015	0.035	
c1	0.38	0.84	0.015	0.033	
D	19.71	20.70	0.776	0.815	3
D1	13.08	-	0.515	-	4

SYMBOL	MILLIMETERS		INCHES		NOTES
	MIN.	MAX.	MIN.	MAX.	
D2	0.51	1.30	0.020	0.051	
E	15.29	15.87	0.602	0.625	3
E1	13.46	-	0.53	-	
e	5.46 BSC		0.215 BSC		
$\Phi K$	0.254		0.010		
L	19.81	20.32	0.780	0.800	
L1	3.71	4.29	0.146	0.169	
$\Phi P$	3.56	3.66	0.14	0.144	
$\Phi P1$	-	6.98	-	0.275	
Q	5.31	5.69	0.209	0.224	
R	4.52	5.49	0.178	0.216	
S	5.51 BSC		0.217 BSC		

#### Notes

- (1) Dimensioning and tolerancing per ASME Y14.5M-1994
- (2) Contour of slot optional
- (3) Dimension D and E do not include mold flash. These dimensions are measured at the outermost extremes of the plastic body
- (4) Thermal pad contour optional with dimensions D1 and E1
- (5) Lead finish uncontrolled in L1
- (6)  $\Phi P$  to have a maximum draft angle of 1.5 to the top of the part with a maximum hole diameter of 3.91 mm (0.154")
- (7) Outline conforms to JEDEC® outline TO-247 with exception of dimension A min., D, E min., Q min., S, and note 4



## Disclaimer

ALL PRODUCT, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE TO IMPROVE RELIABILITY, FUNCTION OR DESIGN OR OTHERWISE.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product.

Vishay makes no warranty, representation or guarantee regarding the suitability of the products for any particular purpose or the continuing production of any product. To the maximum extent permitted by applicable law, Vishay disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Statements regarding the suitability of products for certain types of applications are based on Vishay's knowledge of typical requirements that are often placed on Vishay products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. Parameters provided in datasheets and / or specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein.

Hyperlinks included in this datasheet may direct users to third-party websites. These links are provided as a convenience and for informational purposes only. Inclusion of these hyperlinks does not constitute an endorsement or an approval by Vishay of any of the products, services or opinions of the corporation, organization or individual associated with the third-party website. Vishay disclaims any and all liability and bears no responsibility for the accuracy, legality or content of the third-party website or for that of subsequent links.

Vishay products are not designed for use in life-saving or life-sustaining applications or any application in which the failure of the Vishay product could result in personal injury or death unless specifically qualified in writing by Vishay. Customers using or selling Vishay products not expressly indicated for use in such applications do so at their own risk. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay. Product names and markings noted herein may be trademarks of their respective owners.