

## High Voltage Power Capacitors

### FORM OF CONSTRUCTION



In the case of single phase capacitor units with dead casings, both polarities are led out through the casing in an insulated condition by means of porcelain bushings (fig. 1).



In the case of single phase capacitor units with one bushing only, the second polarity is connected to the casing (fig. 2).



Three-phase capacitors are provided with three bushings for connection to the phases and have dead casings with grounding connection point (fig. 3). They are connected either in star or in delta.



In cases where protection against an accidental touch is required, the capacitors can be supplied as IP55 version (fig. 4).



## CAPACITOR - DIMENSION AND WEIGHT

- Three-phase capacitor up to 7.2 kV, 50 Hz, IP00

OUTPUT QN kvar	WEIGHT kg	CASING DIMENSIONS L x l x H
50	21	345 mm x 110 mm x 300 mm
75	21	345 mm x 110 mm x 300 mm
100	22	345 mm x 110 mm x 300 mm
133	24	345 mm x 110 mm x 350 mm
150	27	345 mm x 110 mm x 410 mm
167	29	345 mm x 110 mm x 430 mm
200	32	345 mm x 135 mm x 430 mm
250	37	345 mm x 135 mm x 500 mm
300	41	345 mm x 175 mm x 450 mm
350	47	345 mm x 175 mm x 520 mm
400	53	345 mm x 175 mm x 600 mm
450	56	345 mm x 175 mm x 640 mm
500	62	345 mm x 175 mm x 710 mm
550	67	345 mm x 175 mm x 770 mm
600	71	345 mm x 175 mm x 820 mm
650	78	345 mm x 175 mm x 910 mm
700	81	345 mm x 175 mm x 950 mm
750	101	345 mm x 270 mm x 810 mm
800	106	345 mm x 270 mm x 850 mm

- Three-phase capacitor up to 12 kV, 50 Hz, IP55

OUTPUT QN kvar	WEIGHT kg	CASING DIMENSIONS L x l x H
50	24	345 mm x 135 mm x 300 mm
75	24	345 mm x 135 mm x 300 mm
100	24	345 mm x 135 mm x 300 mm
133	29	345 mm x 135 mm x 330 mm
150	30	345 mm x 135 mm x 360 mm
167	29	345 mm x 135 mm x 380 mm
200	32	345 mm x 135 mm x 430 mm
250	37	345 mm x 175 mm x 400 mm
300	43	345 mm x 175 mm x 480 mm
350	48	345 mm x 175 mm x 540 mm
400	52	345 mm x 175 mm x 590 mm
450	57	345 mm x 175 mm x 650 mm
500	61	345 mm x 175 mm x 700 mm
550	69	345 mm x 175 mm x 810 mm
600	74	345 mm x 175 mm x 870 mm
650	78	345 mm x 175 mm x 920 mm
700	83	345 mm x 175 mm x 980 mm
750	105	345 mm x 270 mm x 840 mm
800	109	345 mm x 270 mm x 880 mm

- Three-phase capacitor up to 12 kV, 50 Hz, IP00

OUTPUT QN kvar	WEIGHT kg	CASING DIMENSIONS L x l x H
50	25	450 mm x 110 mm x 300 mm
75	25	450 mm x 110 mm x 300 mm
100	27	450 mm x 110 mm x 320 mm
133	30	450 mm x 110 mm x 400 mm
150	35	450 mm x 110 mm x 430 mm
167	37	450 mm x 110 mm x 470 mm
200	43	450 mm x 110 mm x 540 mm
250	49	450 mm x 110 mm x 620 mm
300	58	450 mm x 110 mm x 750 mm

- Single-phase capacitor up to 7.2 kV, 50 Hz

OUTPUT QN kvar	WEIGHT kg	CASING DIMENSIONS L x l x H
200	31	345 mm x 110 mm x 490 mm
300	41	345 mm x 175 mm x 450 mm
400	50	345 mm x 175 mm x 575 mm
500	60	345 mm x 175 mm x 698 mm
600	70	345 mm x 175 mm x 820 mm
700	80	345 mm x 175 mm x 950 mm
800	90	345 mm x 175 mm x 1090 mm
900	99	345 mm x 270 mm x 810 mm
1000	108	345 mm x 270 mm x 950 mm

- Single-phase capacitor up to 12 kV, 50 Hz

OUTPUT QN kvar	WEIGHT kg	CASING DIMENSIONS L x l x H
200	31	345 mm x 175 mm x 325 mm
300	40	345 mm x 175 mm x 450 mm
400	50	345 mm x 175 mm x 570 mm
500	60	345 mm x 175 mm x 705 mm
600	70	345 mm x 175 mm x 830 mm
700	80	345 mm x 175 mm x 950 mm
800	90	345 mm x 175 mm x 1090 mm
900	99	345 mm x 270 mm x 810 mm
1000	109	345 mm x 270 mm x 895 mm



## Disclaimer

ALL PRODUCT, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE TO IMPROVE RELIABILITY, FUNCTION OR DESIGN OR OTHERWISE.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product.

Vishay makes no warranty, representation or guarantee regarding the suitability of the products for any particular purpose or the continuing production of any product. To the maximum extent permitted by applicable law, Vishay disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Statements regarding the suitability of products for certain types of applications are based on Vishay's knowledge of typical requirements that are often placed on Vishay products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. Parameters provided in datasheets and/or specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein.

Except as expressly indicated in writing, Vishay products are not designed for use in medical, life-saving, or life-sustaining applications or for any other application in which the failure of the Vishay product could result in personal injury or death. Customers using or selling Vishay products not expressly indicated for use in such applications do so at their own risk and agree to fully indemnify and hold Vishay and its distributors harmless from and against any and all claims, liabilities, expenses and damages arising or resulting in connection with such use or sale, including attorneys fees, even if such claim alleges that Vishay or its distributor was negligent regarding the design or manufacture of the part. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay. Product names and markings noted herein may be trademarks of their respective owners.

## Material Category Policy

**Vishay Intertechnology, Inc. hereby certifies that all its products that are identified as RoHS-Compliant fulfill the definitions and restrictions defined under Directive 2011/65/EU of The European Parliament and of the Council of June 8, 2011 on the restriction of the use of certain hazardous substances in electrical and electronic equipment (EEE) - recast, unless otherwise specified as non-compliant.**

**Please note that some Vishay documentation may still make reference to RoHS Directive 2002/95/EC. We confirm that all the products identified as being compliant to Directive 2002/95/EC conform to Directive 2011/65/EU.**