


## Lead (Pb)-bearing Thick Film, Rectangular, Trimmable Chip Resistors



### FEATURES

- Can be trimmed to the required value after insertion
- For applications in precision circuitry where relative tolerances can be compensated by trimming
- SnPb contacts on Ni barrier layer
- Metal glaze on high quality ceramic
- Protective overglaze

### STANDARD ELECTRICAL SPECIFICATIONS

MODEL	SIZE		POWER RATING $P_{70\text{ }^\circ\text{C}}$ W	LIMITING ELEMENT VOLTAGE MAX $V_{\Xi}$	TEMPERATURE COEFFICIENT ppm/K	TOLERANCE %	RESISTANCE RANGE $\Omega$	E-SERIES
	INCH	METRIC						
D10/CRCW0402-TR	0402	1005	0.063	50	$\pm 100$ $\pm 200$	$\pm 10$ $\pm 15$ $\pm 20$ $+ 0/- 10$ $+ 0/- 20$ $+ 0/- 30$	10R - 10M R47 - 10M	24
D11/CRCW0603-TR	0603	1608	0.10	75	$\pm 100$ $\pm 200$		10R - 10M R47 - 10M	24
D12/CRCW0805-TR	0805	2012	0.125	150	$\pm 100$ $\pm 200$		10R - 10M R47 - 10M	24
D25/CRCW1206-TR	1206	3216	0.25	200	$\pm 100$ $\pm 200$		10R - 10M R47 - 10M	24
CRCW1210-TR	1210	3225	0.33	200	$\pm 200$		10R - 4M7	24
CRCW2010-TR	2010	5025	0.50	200	$\pm 400$		10R - 4M7	24
CRCW2512-TR	2512	6332	1.0	200	$\pm 500$		10R - 4M7	24

### Notes

- These resistors do not feature a limited lifetime when operated within the permissible limits. However, resistance value drift increasing over operating time may result in exceeding a limit acceptable to the specific application, thereby establishing a functional lifetime.
- Marking: No marking on device, on the label only
- Packaging: See appropriate catalog or web pages
- Power rating depends on the max. temperature at the solder point, the component placement density and the substrate material

### TECHNICAL SPECIFICATIONS

PARAMETER	UNIT	D10/ CRCW0402-TR	D11/ CRCW0603-TR	D12/ CRCW0805-TR	D25/ CRCW1206-TR	CRCW1210-TR	CRCW2010-TR	CRCW2512-TR
Rated Dissipation at 70 °C <sup>(3)</sup>	W	0.063	0.1	0.125	0.25	0.33	0.5	1.0
Limiting Element Voltage <sup>(2)</sup>	$V_{\Xi}$	50	75	150	200	200	400	500
Insulation Voltage (1 min)	$V_{\text{peak}}$	> 75	> 100	> 200	> 300	> 300	> 300	> 300
Thermal Resistance <sup>(1)</sup>	K/W	$\leq 870$	$\leq 550$	$\leq 440$	$\leq 220$	$\leq 140$	$\leq 88$	$\leq 65$
Insulation Resistance	$\Omega$	$> 10^9$						
Category Temperature Range	°C	- 55 to + 155						
Failure Rate	$\text{h}^{-1}$	$0.3 \times 10^{-9}$						
Weight/1000 pieces	g	0.65	2	5.5	10	16	25.5	40.5

### Notes

- <sup>(1)</sup> For size 0402 until 1206 the measuring conditions are in acc. to EN 140401-802. For all other sizes the result depends on the solder pad dimensions.
- <sup>(2)</sup> Rated voltage:  $\sqrt{P \times R}$
- <sup>(3)</sup> The power dissipation on the resistor generates a temperature rise against the local ambient, depending on the heat flow support of the printed-circuit board (thermal resistance). The rated dissipation applies only if the permitted film temperature of 155 °C is not exceeded.



Lead (Pb)-bearing Thick Film, Rectangular,  
Trimmable Chip Resistors

PART NUMBER AND PRODUCT DESCRIPTION																	
PART NUMBER: CRCW080525R0KKTATR <sup>(1)</sup>																	
C	R	C	W	0	8	0	5	2	5	R	0	K	K	T	A	T	R
MODEL	VALUE	TOLERANCE		TCR		PACKAGING <sup>(2)</sup>		SPECIAL									
CRCW0402 CRCW0603 CRCW0805 CRCW1206 CRCW1210 CRCW2010 CRCW2512	R = Decimal K = Thousand M = Million	K = ± 10 % L = ± 15 % M = ± 20 % U = + 0 %/- 10 % V = + 0 %/- 20 % W = + 0 %/- 30 %		K = ± 100 ppm/K N = ± 200 ppm/K		TA, TB, TC, TD, TE, TF, TG, TH, TI, TL		up to 2 digits TR = Customer Trimmable									
PRODUCT DESCRIPTION: CRCW0805-TR 250 K 100 RT1																	
CRCW0805-TR	250	K		100		RT1											
MODEL	RESISTANCE VALUE	TOLERANCE		TCR		PACKAGING <sup>(2)</sup>											
CRCW0402-TR CRCW0603-TR CRCW0805-TR CRCW1206-TR CRCW1210-TR CRCW2010-TR CRCW2512-TR	250 = 25R 392 = 3K9 105 = 1M0	K = ± 10 % L = ± 15 % M = ± 20 % U = + 0 %/- 10 % V = + 0 %/- 20 % W = + 0 %/- 30 %		± 100 ppm/K ± 200 ppm/K		RT1, RT5, RT6, RT7, RF4, R02, R67, R82, RG1, R20											


Notes

(1) Preferred way for ordering products is by use of the PART NUMBER

(2) Please refer to table PACKAGING, see below


PACKAGING								
MODEL	REEL							
	TAPE WIDTH	DIAMETER	PITCH	PIECES/REEL	PACKING CODE			
					PART NUMBER		PRODUCT DESC.	
					PAPER	BLISTER	PAPER	BLISTER
D10/CRCW0402-TR	8 mm	180 mm/7"	2 mm	10 000	TD		RT7	
		330 mm/13"	2 mm	50 000	TE		RF4	
D11/CRCW0603-TR	8 mm	180 mm/7"	4 mm	5000	TA	TI	RT1	RG1
		285 mm/11.25"	4 mm	10 000	TB		RT5	
		330 mm/13"	4 mm	20 000	TC	TL	RT6	RG20
D12/CRCW0805-TR	8 mm	180 mm/7"	4 mm	5000	TA	TI	RT1	RG1
		285 mm/11.25"	4 mm	10 000	TB		RT5	
		330 mm/13"	4 mm	20 000	TC	TL	RT6	RG20
D25/CRCW1206TR	8 mm	180 mm/7"	4 mm	5000	TA	TI	RT1	RG1
		285 mm/11.25"	4 mm	10 000	TB		RT5	
		330 mm/13"	4 mm	20 000	TC	TL	RT6	RG20
CRCW1210TR	12 mm	180 mm/7"	4 mm	5000	TA		RT1	
		330 mm/13"	4 mm	20 000	TC		RT6	
CRCW2010TR	12 mm	180 mm/7"	4 mm	4000		TF		R02
CRCW2512TR	12 mm	180 mm/7"	8 mm	2000		TG		R67
			4 mm	4000		TH		R82

**DIMENSIONS**



SIZE		DIMENSIONS [in millimeters]					SOLDER PAD DIMENSIONS [in millimeters]					
							REFLOW SOLDERING			WAVE SOLDERING		
INCH	METRIC	L	W	H	T1	T2	a	b	l	a	b	l
0402	1005	1.0 ± 0.05	0.5 ± 0.05	0.35 ± 0.05	0.25 ± 0.05	0.2 ± 0.1	0.4	0.6	0.5			
0603	1608	1.55 <sup>+0.10</sup> <sub>-0.05</sub>	0.85 ± 0.1	0.45 ± 0.05	0.3 ± 0.2	0.3 ± 0.2	0.5	0.9	1.0	0.9	0.9	1.0
0805	2012	2.0 <sup>+0.20</sup> <sub>-0.10</sub>	1.25 ± 0.15	0.45 ± 0.05	0.3 <sup>+0.20</sup> <sub>-0.10</sub>	0.3 ± 0.2	0.7	1.3	1.2	0.9	1.3	1.3
1206	3216	3.2 <sup>+0.10</sup> <sub>-0.20</sub>	1.6 ± 0.15	0.55 <sup>+0.05</sup> <sub>-0.10</sub>	0.45 ± 0.2	0.4 ± 0.2	0.9	1.7	2.0	1.1	1.7	2.3
1210	3225	3.2 ± 0.2	2.5 ± 0.2	0.55 ± 0.05	0.45 ± 0.2	0.4 ± 0.2	0.9	2.5	2.0	1.1	2.5	2.2
2010	5025	5.0 ± 0.15	2.5 ± 0.15	0.6 ± 0.1	0.6 ± 0.2	0.6 ± 0.2	1.0	2.5	3.9	1.2	2.5	3.9
2512	6332	6.3 ± 0.2	3.15 ± 0.15	0.6 ± 0.1	0.6 ± 0.2	0.6 ± 0.2	1.0	3.2	5.2	1.2	3.2	5.2

**TRIMMING INSTRUCTIONS**




YAG-Laser:  
Maximum trimming factor =  
1.6 for an I-cut and 1.8 for a L-cut

Double cut:  
Distance between two cuts = 0.5 mm min

The laser-cut should be protected with epoxy resins

**PERMISSIBLE TRIMMING AREA**





DIMENSIONS OF THE PERMISSIBLE					
MODEL	L	W	L <sub>trim</sub>	W <sub>trim</sub>	D
D10/CRCW0402-TR <sup>(1)</sup>	1.0	0.5	≤ 0.25	0.27	≥ 0.25
D11/CRCW0603-TR <sup>(1)</sup>	1.55	0.85	≤ 0.425	0.5	≥ 0.425
D12/CRCW0805-TR	2.0	1.25	≤ 0.625	0.85	≥ 0.625
D25/CRCW1206-TR	3.2	1.6	≤ 0.8	1.0	≥ 0.8
CRCW1210-TR	3.2	2.5	≤ 1.25	1.6	≥ 1.25
CRCW2010-TR	5.0	2.5	≤ 1.25	1.9	≥ 1.25
CRCW2512-TR	6.3	3.15	≤ 1.575	2.4	≥ 1.575

**Note**  
<sup>(1)</sup> Single cut only



Lead (Pb)-bearing Thick Film, Rectangular, Trimmable Chip Resistors



TEST PROCEDURES AND REQUIREMENTS			
EN 60115-1			
TEST (clause)	CONDITIONS OF TEST	REQUIREMENTS PERMISSIBLE CHANGE ( $\Delta R/R$ ) <sup>(1)</sup>	
		STABILITY CLASS 1 OR BETTER	STABILITY CLASS 2 OR BETTER
	Stability for product types: <b>D../CRCW....-TR e3</b>	10R - 10M	R47 - 10M
Resistance (4.5)	-	$\pm 10; \pm 15; \pm 20; + 0/- 30 \%$	
Temperature coefficient (4.8.4.2)	20/- 55/20 °C and 20/125/20 °C	$\pm 100$ ppm/K	$\pm 200$ ppm/K
Overload (4.13)	$U = 2.5 \times (P_{70} \times R)^{1/2} \leq 2 \times U_{max.}$ ; Duration: according the style	$\pm (0.25 \% R + 0.05 \Omega)$	$\pm (0.5 \% R + 0.05 \Omega)$
Solderability (4.17.5)	Aging 4 h at 155 °C, dryheat Solder bath method; 235 °C; 2 s Visual examination	Good tinning ( $\geq 95 \%$ covered) no visible damage	
Resistance to soldering heat (4.18.2)	Solder bath method; (260 $\pm$ 5) °C; (10 $\pm$ 1) s	$\pm (0.25 \% R + 0.05 \Omega)$	$\pm (0.5 \% R + 0.05 \Omega)$
Rapid change of temperature (4.19)	30 min at LCT = - 55 °C; 30 min at UCT = 125 °C; 5 cycles	$\pm (0.25 \% R + 0.05 \Omega)$	$\pm (0.5 \% R + 0.05 \Omega)$
Damp heat, steady state (4.24)	(40 $\pm$ 2) °C; 56 days; (93 $\pm$ 3) % RH	$\pm (1 \% R + 0.05 \Omega)$	$\pm (2 \% R + 0.1 \Omega)$
Climatic sequence (4.23)	16 h at UCT = 125 °C; 1 cycle at 55 °C; 2 h at LCT = - 55 °C; 1 h/1 kPa at 15 °C to 35 °C; 5 cycles at 55 °C $U = (P_{70} \times R)^{1/2}$ $U = U_{max.}$ ; whichever is less severe	$\pm (1 \% R + 0.05 \Omega)$	$\pm (2 \% R + 0.1 \Omega)$
Endurance at 70 °C (4.25.1)	$U = (P_{70} \times R)^{1/2}$ $U = U_{max.}$ ; whichever is less severe 1.5 h on; 0.5 h off; 70 °C; 1000 h	$\pm (1 \% R + 0.05 \Omega)$	$\pm (2 \% R + 0.1 \Omega)$
Extended endurance (4.25.1.8)	Duration extended to 8000 h	$\pm (2 \% R + 0.1 \Omega)$	$\pm (4 \% R + 0.1 \Omega)$
Endurance at upper category temperature (4.25.3)	UCT = 125 °C; 1000 h	$\pm (1 \% R + 0.05 \Omega)$	$\pm (2 \% R + 0.1 \Omega)$

Note

<sup>(1)</sup> Data is valid for non trimmed resistors only. Depending on the trimming process some properties can change.

APPLICABLE SPECIFICATIONS	
• EN 60115-1	Generic Specification
• EN 140400	Sectional Specification
• EN 140401-802	Detail Specification
• IEC 60068-2-X	Variety of environmental test procedures
• IEC 60286-3	Packaging of SMD components



## Disclaimer

ALL PRODUCT, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE TO IMPROVE RELIABILITY, FUNCTION OR DESIGN OR OTHERWISE.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product.

Vishay makes no warranty, representation or guarantee regarding the suitability of the products for any particular purpose or the continuing production of any product. To the maximum extent permitted by applicable law, Vishay disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Statements regarding the suitability of products for certain types of applications are based on Vishay's knowledge of typical requirements that are often placed on Vishay products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. Parameters provided in datasheets and/or specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein.

Except as expressly indicated in writing, Vishay products are not designed for use in medical, life-saving, or life-sustaining applications or for any other application in which the failure of the Vishay product could result in personal injury or death. Customers using or selling Vishay products not expressly indicated for use in such applications do so at their own risk and agree to fully indemnify and hold Vishay and its distributors harmless from and against any and all claims, liabilities, expenses and damages arising or resulting in connection with such use or sale, including attorneys fees, even if such claim alleges that Vishay or its distributor was negligent regarding the design or manufacture of the part. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay. Product names and markings noted herein may be trademarks of their respective owners.