


Wirewound Resistors, Commercial Power, Radial Terminals



FEATURES


- Direct mounting on printed circuit board
- Circuit board lock-in mounting tabs
- High performance for low cost



RoHS*
COMPLIANT

Please reference the Vishay Dale CPR as an alternative option (for CPR datasheet please visit our website: <http://www.vishay.com/doc?30219>).

STANDARD ELECTRICAL SPECIFICATIONS			
GLOBAL MODEL	POWER RATING $P_{70^\circ\text{C}}$ W	RESISTANCE RANGE Ω	
		$\pm 5\%, \pm 10\%$	
		TCR $\pm 600 \text{ ppm}/^\circ\text{C}$	TCR $\pm 300 \text{ ppm}/^\circ\text{C}$
CPS04	4	R10 - R99	1R0 - 1K0
CPS05	5	R10 - R99	1R0 - 2K0
CPS07	6.5	R10 - R99	1R0 - 2K7



TECHNICAL SPECIFICATIONS		
PARAMETER	UNIT	CPS CHARACTERISTICS
Operating Temperature Range	$^\circ\text{C}$	- 65 to + 350
Short Time Overload	-	5 x rated power for 5 s
Terminal Strength	lb	10 minimum
Maximum Working Voltage	V	$(P \times R)^{1/2}$


PERFORMANCE		
TEST	CONDITIONS OF TEST	TEST LIMITS
Load Life	1000 h at rated power, 1.5 h "ON", 0.5 h "OFF"	$\pm 3.0\% \Delta R$ average
Climatic Sequence	1000 cycles, - 55 $^\circ\text{C}$ to + 125 $^\circ\text{C}$	$\pm 2.0\% \Delta R$
Damp Heat, Steady State	+ 40 $^\circ\text{C}$, 93 % RH, 56 days	$\pm 2.0\% \Delta R$
Resistance to Solder Heat	+ 260 $^\circ\text{C}$, 10 s	$\pm 0.2\% \Delta R$ typical
Low Temperature Operation	- 65 $^\circ\text{C}$, full rated working voltage for 45 min	$\pm 3.0\% \Delta R$

GLOBAL PART NUMBER INFORMATION														
Global Part Numbering Example: CPS05P100R0KE14														
C	P	S	0	5	P	1	0	0	R	0	K	E	1	4
GLOBAL MODEL	TERMINAL	VALUE		TOLERANCE		PACKAGING			SPECIAL					
CPS04 CPS05 CPS07	P = /2	R = Decimal K = Thousand R1500 = 0.15 Ω 1K000 = 1000 Ω		J = $\pm 5.0\%$ K = $\pm 10.0\%$		E14 = Lead (Pb)-free bulk E31 = Lead (Pb)-free four layer bulk B14 = Tin/lead bulk B31 = Tin/lead four layer bulk			(Dash Number) (up to 3 digits) From 1 - 999 as applicable					

* Pb containing terminations are not RoHS compliant, exemptions may apply





DIMENSIONS in inches [millimeters]




MODEL	DIMENSIONS in inches [millimeters]	
	L	RM
CPS04	0.945 ± 0.055 [24 ± 1.4]	0.598 [15.2]
CPS05	1.350 ± 0.055 [34.3 ± 1.4]	1.000 [25.4]
CPS07	1.752 ± 0.055 [44.5 ± 1.4]	1.398 [35.5]

SURFACE TEMPERATURE



CPS Terminal Temperature



CPS Body Hot Spot Temperature Rise



Disclaimer

ALL PRODUCT, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE TO IMPROVE RELIABILITY, FUNCTION OR DESIGN OR OTHERWISE.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product.

Vishay makes no warranty, representation or guarantee regarding the suitability of the products for any particular purpose or the continuing production of any product. To the maximum extent permitted by applicable law, Vishay disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Statements regarding the suitability of products for certain types of applications are based on Vishay's knowledge of typical requirements that are often placed on Vishay products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. Parameters provided in datasheets and / or specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein.

Hyperlinks included in this datasheet may direct users to third-party websites. These links are provided as a convenience and for informational purposes only. Inclusion of these hyperlinks does not constitute an endorsement or an approval by Vishay of any of the products, services or opinions of the corporation, organization or individual associated with the third-party website. Vishay disclaims any and all liability and bears no responsibility for the accuracy, legality or content of the third-party website or for that of subsequent links.

Vishay products are not designed for use in life-saving or life-sustaining applications or any application in which the failure of the Vishay product could result in personal injury or death unless specifically qualified in writing by Vishay. Customers using or selling Vishay products not expressly indicated for use in such applications do so at their own risk. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay. Product names and markings noted herein may be trademarks of their respective owners.