


Lead (Pb)-bearing Thick Film, Rectangular High Value Chip Resistor



FEATURES

- High resistance values (up to 470M)
- Suitable for voltage dividers and hybrids
- SnPb contacts on Ni barrier layer
- Metal glaze on high quality ceramic
- Protective overglaze

STANDARD ELECTRICAL SPECIFICATIONS

MODEL	SIZE		POWER RATING $P_{70\text{ }^\circ\text{C}}$ W	LIMITING ELEMENT VOLTAGE MAX. V_{\equiv}	TEMP. COEFF. ppm/K	TOLERANCE %	RESISTANCE RANGE Ω	E-SERIES
	INCH	METRIC						
D11/CRCW0603-HR	0603	1608	0.10	75	± 500	± 5	11M - 470M	24
D12/CRCW0805-HR	0805	2012	0.125	150	± 500	± 5	11M - 470M	24
D25/CRCW1206-HR	1206	3216	0.25	200	± 500	± 5	11M - 470M	24

Notes

- These resistors do not feature a limited lifetime when operated within the permissible limits. However, resistance value drift increasing over operating time may result in exceeding a limit acceptable to the specific application, thereby establishing a functional lifetime.
- Marking and packaging: See appropriate catalog or web pages
- Power rating depends on the max. temperature at the solder point, the component placement density and the substrate material

TECHNICAL SPECIFICATIONS


PARAMETER	UNIT	D11 CRCW0603-HR	D12 CRCW0805-HR	D25 CRCW1206-HR
Rated Dissipation at 70 °C (2)	W	0.1	0.125	0.25
Limiting Element Voltage	V_{\equiv}	75	150	200
Voltage Coefficient	%/V	< 100M: < 0.1/> 100M: < 0.3		
Insulation Voltage (1 min)	V_{peak}	> 100	> 200	> 300
Thermal Resistance (1)	K/W	≤ 550	≤ 440	≤ 220
Insulation Resistance	Ω	$> 10^9$		
Category Temperature Range	$^\circ\text{C}$	- 55 to + 155		
Weight/1000 pieces	g	2	5.5	10

Notes

- (1) Measuring conditions in acc. to EN 140401-802
 (2) The power dissipation on the resistor generates a temperature rise against the local ambient, depending on the heat flow support of the printed-circuit board (thermal resistance). The rated dissipation applies only if the permitted film temperature of 155 °C is not exceeded.

PART NUMBER AND PRODUCT DESCRIPTION

PART NUMBER: CRCW060314M0JPTBHR (3)



MODEL/SIZE	VALUE	TOLERANCE	TCR	PACKAGING (4)	SPECIAL
CRCW0603 CRCW0805 CRCW1206	M = Million	J = $\pm 5\%$	P = ± 500 ppm/K	TA, TB TC, TI TL	up to 2 digits HR = High Value


Product Description: CRCW0603 146 J 500 RT5

CRCW0603	146	J	500	RT5
MODEL	RESISTANCE VALUE	TOLERANCE	TCR	PACKAGING (4)
CRCW0603 CRCW0805 CRCW1206	686 = 68 M Ω 227 = 220 M Ω $\pm 5\% = 2$ sig. digits plus multiplier	J = $\pm 5\%$	± 500 ppm/K	RT1, RT5 RT6, RG1 R20



Notes

- (3) Preferred way for ordering products is by use of the PART NUMBER
 (4) Please refer to table PACKAGING, see next page

PACKAGING								
MODEL	REEL							
	TAPE WIDTH	DIAMETER	PITCH	PIECES/REEL	PACKING CODE			
					PART NUMBER		PRODUCT DESC.	
					PAPER	BLISTER	PAPER	BLISTER
D11/CRCW0603-HR	8 mm	180 mm/7"	4 mm	5000	TA	TI	RT1	RG1
		285 mm/11.25"		10 000	TB		RT5	
		330 mm/13"		20 000	TC	TL	RT6	R20
D12/CRCW0805-HR	8 mm	180 mm/7"	4 mm	5000	TA	TI	RT1	RG1
		285 mm/11.25"		10 000	TB		RT5	
		330 mm/13"		20 000	TC	TL	RT6	R20
D25/CRCW1206-HR	8 mm	180 mm/7"	4 mm	5000	TA	TI	RT1	RG1
		285 mm/11.25"		10 000	TB		RT5	
		330 mm/13"		20 000	TC	TL	RT6	R20

DIMENSIONS


SIZE		DIMENSIONS [in millimeters]					SOLDER PAD DIMENSIONS [in millimeters]					
							REFLOW SOLDERING			WAVE SOLDERING		
INCH	METRIC	L	W	H	T1	T2	a	b	l	a	b	l
0603	1608	1.55 ^{+0.10} _{-0.05}	0.85 ± 0.1	0.45 ± 0.05	0.3 ± 0.2	0.3 ± 0.2	0.5	0.9	1.0	0.9	0.9	1.0
0805	2012	2.0 ^{+0.20} _{-0.10}	1.25 ± 0.15	0.45 ± 0.05	0.3 ^{+0.20} _{-0.10}	0.3 ± 0.2	0.7	1.3	1.2	0.9	1.3	1.3
1206	3216	3.2 ^{+0.10} _{-0.20}	1.6 ± 0.15	0.55 ± 0.05	0.45 ± 0.2	0.4 ± 0.2	0.9	1.7	2.0	1.1	1.7	2.3


Temperature Rise

Derating

TEST PROCEDURES AND REQUIREMENTS		
EN 60115-1		
TEST (clause)	CONDITIONS OF TEST	REQUIREMENTS PERMISSIBLE CHANGE ($\Delta R/R$)
		STABILITY CLASS 2 OR BETTER
	Stability for product types: D../CRCW....-HR	11 M Ω to 470 M Ω
Resistance (4.5)	-	$\pm 5 \%$
Temperature coefficient (4.8.4.2)	20/- 55/20 °C and 20/125/20 °C	± 500 ppm/K
Overload (4.13)	$U = 2.5 \times (P_{70} \times R)^{1/2}$ $\leq 2 \times U_{max}$; Duration: according the style	$\pm (0.5 \% R + 0.05 \Omega)$
Solderability (4.17.5)	Aging 4 h at 155 °C, dryheat solder bath method; 235 °C; 2 s visual examination	Good tinning ($\geq 95 \%$ covered) no visible damage
Resistance to soldering heat (4.18.2)	Solder bath method; (260 \pm 5) °C; (10 \pm 1) s	$\pm (0.5 \% R + 0.05 \Omega)$
Rapid change of temperature (4.19)	30 min at LCT = - 55 °C; 30 min at UCT = 125 °C; 5 cycles	$\pm (0.5 \% R + 0.05 \Omega)$
Damp heat, steady state (4.24)	(40 \pm 2) °C; 56 days; (93 \pm 3) % RH	$\pm (2 \% R + 0.1 \Omega)$
Climatic sequence (4.23)	16 h at UCT = 125 °C; 1 cycle at 55 °C; 2 h at LCT = - 55 °C; 1 h/1 kPa at 15 °C to 35 °C; 5 cycles at 55 °C $U = (P_{70} \times R)^{1/2}$ $U = U_{max}$; whichever is less severe	$\pm (2 \% R + 0.1 \Omega)$
Endurance at 70 °C (4.25.1)	$U = (P_{70} \times R)^{1/2}$ $U = U_{max}$; whichever is less severe 1.5 h ON; 0.5 h OFF; 70 °C; 1000 h	$\pm (2 \% R + 0.1 \Omega)$
Extended endurance (4.25.1.8)	Duration extended to 8000 h	$\pm (4 \% R + 0.1 \Omega)$
Endurance at upper category temperature (4.25.3)	UCT = 125 °C; 1000 h	$\pm (2 \% R + 0.1 \Omega)$

APPLICABLE SPECIFICATIONS	
• EN 60115-1	Generic Specifications
• EN 140400	Sectional Specification
• EN 140401-802	Detail Specifications
• IEC 60068-2-x	Variety of environmental test procedures
• IEC 60286-3	Packaging of SMD components



Disclaimer

All product specifications and data are subject to change without notice.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained herein or in any other disclosure relating to any product.

Vishay disclaims any and all liability arising out of the use or application of any product described herein or of any information provided herein to the maximum extent permitted by law. The product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein, which apply to these products.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay.

The products shown herein are not designed for use in medical, life-saving, or life-sustaining applications unless otherwise expressly indicated. Customers using or selling Vishay products not expressly indicated for use in such applications do so entirely at their own risk and agree to fully indemnify Vishay for any damages arising or resulting from such use or sale. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

Product names and markings noted herein may be trademarks of their respective owners.