

Carbon Film Resistors, Fusible Type



FEATURES


- Fusible resistor for constant voltage designed for over load protection
- Special construction opens the resistor at a specified overload
- Non inflammable coating
- Lead (Pb)-free solder contacts
- Pure tin plating provides compatibility with lead (Pb)-free and lead containing soldering processes
- Compatible with "Restriction of the use of Hazardous Substances" (RoHS) directive 2002/95/EC (issue 2004)
- Defined switch-off behaviour



STANDARD ELECTRICAL SPECIFICATIONS				
MODEL	SIZE	POWER RATING $P_{70\text{ }^\circ\text{C}}$ W	TOLERANCE %	RESISTANCE RANGE Ω
SKS2	0207	0.30	$\pm 5, \pm 10$	1R0 - 5K1
SKS4	0414	0.50	$\pm 5, \pm 10$	1R0 - 5K1



- $R_i \geq 6 \Omega$ for $R_N < 10R$
- $R_i \geq 1 \Omega$ for $R_N \geq 10R$
- Coating: red brown
- Marking: 5th band yellow

TECHNICAL SPECIFICATIONS			
PARAMETER	UNIT	SKS2	SKS4
Rated Dissipation at 70 °C	W	0.30	0.50
Overload to Fuse	W	3.5	7.0
Time to Fuse (max)	s	40	70
Max. Permissible Voltage	V	See Diagram	
Voltage Coefficient	1/V	$< 10^{-7}$	$< 10^{-7}$
Current Noise	$\mu\text{V/V}$	< 0.1	< 0.1
Thermal Resistance (max)	K/W	220	130
Thermal Time Constant	s	8	20
Category Temperature Range	$^\circ\text{C}$	- 55 to + 125	
Failure Rate	$10^{-9}/\text{h}$	< 30	
Weight	g	0.2	0.7


DIMENSIONS


MODEL	DIMENSIONS [in millimeters]					
	D	L	L1 _{max}	B	d	e
SKS2	2.5 - 0.5	6.0 - 0.5	7.5	53 ± 1 ¹⁾	0.6	7.5
SKS4	4.1 - 0.5	12.0 - 1.5	15.0	73 ± 1	0.8	15

- Taping in acc. with IEC60286-1
 - D and L measured in acc. with IEC60294
 - d according to IEC60301
1. Also available in 26 mm tape spacing


PART NUMBER AND PRODUCT DESCRIPTION
PART NUMBER: SKS2207001000JD500

PRODUCT DESCRIPTION: SKS2 100R 5 % R5

¹⁾ Please refer to table PACKAGING, page 3.

Note: The PART NUMBER shown above is to facilitate the unified part numbering system for ordering products.




DERATING

FUSING TIME (AT U = CONSTANT)





OPENING POWER P [W]
Calculated with rated resistance




OPENING POWER P [W]
Calculated with rated resistance

APPROXIMATE VALUES FOR \hat{U} MAX IN CASE OF FAILURE AND MAX PULSE VOLTAGE







PULSE LOAD $\bar{P} \leq P40$ $R \geq 10 \Omega$



PULSE LOAD $\bar{P} \leq P40$ $R < 10 \Omega$



PULSE LOAD $\bar{P} \rightarrow 0$ $R \geq 10 \Omega$



PULSE LOAD $\bar{P} \rightarrow 0$ $R < 10 \Omega$

PACKAGING				
MODEL	REEL		BOX	
	PIECES/REEL	CODE	PIECES/BOX	CODE
SKS2	5000	R5	2000	A2
SKS4	2500	RE	1000	A1

PERFORMANCE		
TEST	CONDITIONS	RESULTS
Voltage Coefficient	1/V	$< 10^{-7}$
Ohmic Value after Fusing	Ω	$> 10 \times R_N$
Temperature Coefficient	$10^{-6}/K$	$R < 10 \Omega: +200; R \geq 10 \Omega: -300.. -500$
Non-Linearity	dB	SKS2, SKS4 = 100
Damp Heat steady state	56 days, 40 °C, (90 - 95) % humidity	$\leq 1\%$



Disclaimer

All product specifications and data are subject to change without notice.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained herein or in any other disclosure relating to any product.

Vishay disclaims any and all liability arising out of the use or application of any product described herein or of any information provided herein to the maximum extent permitted by law. The product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein, which apply to these products.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay.

The products shown herein are not designed for use in medical, life-saving, or life-sustaining applications unless otherwise expressly indicated. Customers using or selling Vishay products not expressly indicated for use in such applications do so entirely at their own risk and agree to fully indemnify Vishay for any damages arising or resulting from such use or sale. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

Product names and markings noted herein may be trademarks of their respective owners.