

High Pulse Wirewound Resistor, Noise Suppressor



FEATURES

- High grade alumina ceramic core
- AEC-Q200 qualified
- High ignition pulse, 25 kV, withstanding resistive winding element
- Non-flammable silicone cement coating
- Material categorization:
for definitions of compliance please see www.vishay.com/doc?99912



RoHS
COMPLIANT
HALOGEN
FREE
GREEN
(5-2008)

APPLICATIONS

- EMI / RFI noise suppression in automotive ignition


STANDARD ELECTRICAL SPECIFICATIONS			
TYPE	RATED DISSIPATION P_{40}	RESISTANCE RANGE	RESISTANCE TOLERANCE
HPR 1/2 (HPR0500)	0.50 W	1 k Ω to 5 k Ω	$\pm 10\%$, $\pm 20\%$
HPR 1 (HPR1000)	1 W	1 k Ω to 5 k Ω	$\pm 10\%$, $\pm 20\%$

Note

- Customer specific resistance values are available on request

TECHNICAL SPECIFICATIONS		
DESCRIPTION	HPR 1/2 (HPR0500)	HPR 1 (HPR1000)
Imperial size	0411	0519
Typical inductance	22 μ H at 1 MHz, 1 V	
Basic specifications	IEC 60115-1	
Climatic category	-55 ° C / +200 ° C / 56 days	
Termination	Stainless steel caps	
Lacquer coating	Non-flammable silicone cement meets IEC 60115-1, 4.26 active flammability test and IEC 60115-1, 4.35 passive flammability needle flame test	

DIMENSIONS



Notes

- Top surface of the product will be covered by silicone cement lacquer
- There will be no lacquer on the edges and on the side surface of the product



DIMENSIONS - HPR types, mass and relevant physical dimensions			
TYPE	Ø D _{MAX.} (mm)	Ø L _{MAX.} (mm)	MASS (mg)
HPR 1/2 (HPR0500)	3.9	11.0	360
HPR 1 (HPR1000)	5.2	18.7	993

PART NUMBER AND PRODUCT DESCRIPTION

Part Number: HPR0500005001KLX00

H	P	R	0	5	0	0	0	0	5	0	0	1	K	L	X	0	0
---	---	---	---	---	---	---	---	---	---	---	---	---	---	---	---	---	---

MODEL HPR0500 HPR1000	VARIANT 0 = neutral	TCR / MATERIAL 0 = neutral	RESISTANCE 3 digit value 1 digit multiplier Multiplier 1 = *10 ¹	TOLERANCE K = ± 10 % M = ± 20 %	PACKAGING LX
-----------------------------	------------------------	-------------------------------	---	---------------------------------------	-----------------

Product Description: HPR0500 5K 10% LX CD xxxx

HPR0500	5K	10 %	LX	CD xxxx
TYPE HPR1000	RESISTANCE 5K = 5 kΩ	TOLERANCE K = ± 10 % M = ± 20 %	PACKAGING	SPECIAL CODE

PACKAGING			
PRODUCT TYPE	CODE	QUANTITY	DESCRIPTION
HPR 1/2 (HPR0500)	LX	1000	Loose in box
HPR 1 (HPR1000)			



DESCRIPTION

Stainless steel caps (terminations) are firmly pressed onto a high grade alumina ceramic core. The resistor element is a resistive wire, which is wound on this ceramic core. Resistor is coated with silicone cement protective coating designed for electrical, mechanical and climatic protection.

MATERIALS

Vishay acknowledges the following systems for the regulation of hazardous substances:

- IEC 62474, Material Declaration for Products of and for the Electrotechnical Industry, with the list of declarable substances given therein (1)
• The Global Automotive Declarable Substance List (GADSL) (2)
• The REACH regulation (1907/2006/EC) and the related list of substances with very high concern (SVHC) (3) for its supply chain

The products do not contain any of the banned substances as per IEC 62474, GADSL, or the SVHC list, see www.vishay.com/how/leadfree.

Hence the products fully comply with the following directives:

- 2000/53/EC End-of-Life Vehicle Directive (ELV) and Annex II (ELV II)
• 2011/65/EU Restriction of the Use of Hazardous Substances Directive (RoHS) with amendment 2015/863/EU
• 2012/19/EU Waste Electrical and Electronic Equipment Directive (WEEE)

Vishay pursues the elimination of conflict minerals from its supply chain, see the Conflict Minerals Policy at www.vishay.com/doc?49037.

ASSEMBLY

The resistor is mounted inside noise suppressor spark plug cap. Connections are taken mechanically through a spring and through a screw electrode. The suitability of conformal coatings, if applied, shall be qualified by appropriate means to ensure the long-term stability of the whole system.

Notes

- (1) The IEC 62474 list of declarable substances is maintained in a dedicated database, which is available at http://std.iec.ch/iec62474
(2) The Global Automotive Declarable Substance List (GADSL) is maintained by the American Chemistry Council and available at www.gadsl.org
(3) The SVHC list is maintained by the European Chemical Agency (ECHA) and available at http://echa.europa.eu/candidate-list-table

Table with 5 columns: IEC 60115-1 CLAUSE, IEC 60068-2 TEST METHOD, TEST, PROCEDURE, REQUIREMENTS PERMISSIBLE CHANGE (ΔR). Rows include test conditions like short time overload, rapid change of temperature, climatic sequence (dry heat, damp heat, cold, low air pressure), damp heat (steady state), and endurance tests.



Disclaimer

ALL PRODUCT, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE TO IMPROVE RELIABILITY, FUNCTION OR DESIGN OR OTHERWISE.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product.

Vishay makes no warranty, representation or guarantee regarding the suitability of the products for any particular purpose or the continuing production of any product. To the maximum extent permitted by applicable law, Vishay disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Statements regarding the suitability of products for certain types of applications are based on Vishay's knowledge of typical requirements that are often placed on Vishay products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. Parameters provided in datasheets and / or specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein.

Hyperlinks included in this datasheet may direct users to third-party websites. These links are provided as a convenience and for informational purposes only. Inclusion of these hyperlinks does not constitute an endorsement or an approval by Vishay of any of the products, services or opinions of the corporation, organization or individual associated with the third-party website. Vishay disclaims any and all liability and bears no responsibility for the accuracy, legality or content of the third-party website or for that of subsequent links.

Vishay products are not designed for use in life-saving or life-sustaining applications or any application in which the failure of the Vishay product could result in personal injury or death unless specifically qualified in writing by Vishay. Customers using or selling Vishay products not expressly indicated for use in such applications do so at their own risk. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay. Product names and markings noted herein may be trademarks of their respective owners.