

Lower Voltage Ceramic Disc Capacitors 1000 VDC Precision Capacitors

Fig. 1





Fig. 2



LEAD OFFSET 'LO' (NOMINAL)	
1000 VDC	0.050" (1.3 mm)

INSULATION RESISTANCE

Min. 1000 Ω F or 50 000 M Ω

TOLERANCE ON CAPACITANCE

$\pm 5\%$

DISSIPATION FACTOR

0.1 % max. at 1 MHz; 1 V

CATEGORY TEMPERATURE RANGE

(- 55 to + 125) °C

CLIMATIC CATEGORY ACC. TO EN60068-1

55/125/21

OPERATING TEMPERATURE RANGE

(- 55 to + 105) °C

FEATURES

- Ultra stable over temperature and voltage
- Used when the ultimate in stability is required
- Radial leads



RoHS
COMPLIANT

APPLICATIONS

- Temperature compensating
- Resonant circuit

DESIGN

The capacitors consist of a ceramic disc of which both sides are silver-plated. Connection leads are made of tinned copper or tinned copper clad steel having diameters of 0.020" (0.51 mm) or 0.025" (0.64 mm).

The capacitors may be supplied with radial kinked or straight leads having lead spacing of 0.250" (6.35 mm) or 0.375" (9.5 mm).

Coating is made of flame retardant epoxy resin in accordance with "UL 94 V-0".

CAPACITANCE RANGE

1.0 pF to 680 pF

RATED VOLTAGE

1000 VDC

DIELECTRIC STRENGTH BETWEEN LEADS

Component test:
2500 VDC, 2 s

CERAMIC DIELECTRIC

C0K, C0G, U2J, M3K, S3N (Class 1)



ORDERING INFORMATION, CERAMIC 1000 VDC PRECISION CAPACITORS								
C (pF)	TOL. (%)	D DIAMETER INCH (mm)	T THICKNESS INCH (mm)	LS LEAD SPACE	WIRE SIZE		FIG.	ORDERING CODE
					AWG	INCH (mm)		
C0K								
1.0	± 0.5 pF	0.250 (6.4)	0.156 (4.0)	0.250 (6.4)	24	0.020 (0.51)	2	561R10TCCV10
2.2								561R10TCCV22
2.7								561R10TCCV27
COG (NPO)								
3.0	± 0.5 pF	0.250 (6.4)	0.156 (4.0)	0.250 (6.4)	24	0.020 (0.51)	2	561R10TCCV30
3.3								561R10TCCV33
3.9								561R10TCCV39
4.7								561R10TCCV47
5.0								561R10TCCV50
5.6								561R10TCCV56
6.8								561R10TCCV68
8.2								561R10TCCV82
10								561R10TCCQ10
12								561R10TCCQ12
15	± 5 %	0.290 (7.4)	0.156 (4.0)	0.250 (6.4)	22	0.025 (0.64)	1	561R10TCCQ15
18								561R10TCCQ18
20								561R10TCCQ20
22								561R10TCCQ22
25								561R10TCCQ25
27								561R10TCCQ27
30								561R10TCCQ30
33								561R10TCCQ33
39								561R10TCCQ39
47								561R10TCCQ47
50	± 5 %	0.370 (9.4)	0.156 (4.0)	0.250 (6.4)	22	0.025 (0.64)	1	561R10TCCQ50
56								561R10TCCQ56
68								561R10TCCQ68
100								561R10TCCT10
120								561R10TCCT12
220								561R10TCCT22
U2J (N750)								
33	± 5 %	0.290 (7.4)	0.156 (4.0)	0.250 (6.4)	24	0.020 (0.51)	2	561R10TCUQ33
68		0.370 (9.4)	0.156 (4.0)	0.250 (6.4)	22	0.025 (0.64)		561R10TCUQ68
M3K (N1000)								
560	± 5 %	0.560 (14.2)	0.156 (4.0)	0.375 (9.5)	22	0.025 (0.64)	1	561R10TCUT56
S3N (N3300)								
680	± 5 %	0.630 (16.0)	0.156 (4.0)	0.375 (9.5)	22	0.025 (0.64)	1	561R10TCUT68



Disclaimer

All product specifications and data are subject to change without notice.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained herein or in any other disclosure relating to any product.

Vishay disclaims any and all liability arising out of the use or application of any product described herein or of any information provided herein to the maximum extent permitted by law. The product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein, which apply to these products.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay.

The products shown herein are not designed for use in medical, life-saving, or life-sustaining applications unless otherwise expressly indicated. Customers using or selling Vishay products not expressly indicated for use in such applications do so entirely at their own risk and agree to fully indemnify Vishay for any damages arising or resulting from such use or sale. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

Product names and markings noted herein may be trademarks of their respective owners.