



Pot Capacitors for Coupling Purposes

TDFZ 170229 40 KV_p



TDFZ 170311 32 KV_p



• Dimensions in millimeters (inches)
 * Metric threads available on request

MODEL:

The ceramic capacitor element is housed in a rugged silver plated copper can. This construction allows additional "Belt-contacting" of the outer electrode terminal over the copper can shaft. The results are short conduction paths with low impedance and low inductance as well as protection of the outer noble metal electrode.

FINISH:

Insulating rim protected with silicone rubber.

MATERIAL:

Capacitor elements made from Class 1 ceramic dielectric with noble metal electrodes. Connection terminals of the inner electrode and outer electrode's covering can made from copper/brass, silver plated.

MARKING:


Type designator, Capacitance value and tolerance, Rated voltage (peak value), Production date code, Ceramic material code, DRALORIC Logo, Serial number.

ORDERING INFORMATION				
TDFZ 170311	32 KV _p	4000 pF	± 10 %	R 85
MODEL	RATED VOLTAGE	CAPACITANCE VALUE	TOLERANCE	CERAMIC




DERATING DIAGRAMS


TDFZ 170229				
CERAMIC	CAPACITANCE VALUE [pF]	RATED VOLTAGE [KV _p]	RATED POWER [KVA _r]	RATED CURRENT [A _{RMS}]
R 85	2000	40	120	max. 100



TDFZ 170311				
CERAMIC	CAPACITANCE VALUE [pF]	RATED VOLTAGE [KV _p]	RATED POWER [KVA _r]	RATED CURRENT [A _{RMS}]
R 85	3000	32	230	max. 120



TDFZ 170311				
CERAMIC	CAPACITANCE VALUE [pF]	RATED VOLTAGE [KV _p]	RATED POWER [KVA _r]	RATED CURRENT [A _{RMS}]
R 85	4000	32	230	max. 170



CAPACITANCE TOLERANCE: $\pm 10\%$

Other capacitance values and tolerances are available on request.



Disclaimer

ALL PRODUCT, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE TO IMPROVE RELIABILITY, FUNCTION OR DESIGN OR OTHERWISE.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product.

Vishay makes no warranty, representation or guarantee regarding the suitability of the products for any particular purpose or the continuing production of any product. To the maximum extent permitted by applicable law, Vishay disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Statements regarding the suitability of products for certain types of applications are based on Vishay's knowledge of typical requirements that are often placed on Vishay products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. Parameters provided in datasheets and/or specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein.

Except as expressly indicated in writing, Vishay products are not designed for use in medical, life-saving, or life-sustaining applications or for any other application in which the failure of the Vishay product could result in personal injury or death. Customers using or selling Vishay products not expressly indicated for use in such applications do so at their own risk and agree to fully indemnify and hold Vishay and its distributors harmless from and against any and all claims, liabilities, expenses and damages arising or resulting in connection with such use or sale, including attorneys fees, even if such claim alleges that Vishay or its distributor was negligent regarding the design or manufacture of the part. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay. Product names and markings noted herein may be trademarks of their respective owners.

Material Category Policy

Vishay Intertechnology, Inc. hereby certifies that all its products that are identified as RoHS-Compliant fulfill the definitions and restrictions defined under Directive 2011/65/EU of The European Parliament and of the Council of June 8, 2011 on the restriction of the use of certain hazardous substances in electrical and electronic equipment (EEE) - recast, unless otherwise specified as non-compliant.

Please note that some Vishay documentation may still make reference to RoHS Directive 2002/95/EC. We confirm that all the products identified as being compliant to Directive 2002/95/EC conform to Directive 2011/65/EU.