



	<p>Ref. Certif. No. DE1-63498/M1</p>
<p>IEC SYSTEM FOR MUTUAL RECOGNITION OF TEST CERTIFICATES FOR ELECTRICAL EQUIPMENT (IECEE) CB SCHEME</p>	
<p>CB TEST CERTIFICATE</p>	
<p>Product</p> <p>Name and address of the applicant</p> <p>Name and address of the manufacturer</p> <p>Name and address of the factory</p> <p><i>Note: When more than one factory, please report on page 2</i></p> <p>Ratings and principal characteristics</p> <p>Trademark (if any)</p> <p>Customer's Testing Facility (CTF) Stage used</p> <p>Model / Type Ref.</p> <p>Additional information (if necessary may also be reported on page 2)</p> <p>A sample of the product was tested and found to be in conformity with</p> <p>As shown in the Test Report Ref. No. which forms part of this Certificate</p>	<p>Fixed capacitor for electromagnetic interference suppression and connection to the supply mains</p> <p>VISHAY Electronic GmbH Dr.-Felix-Zandman-Platz 1, 95100 Selb GERMANY</p> <p>VISHAY Electronic GmbH Dr.-Felix-Zandman-Platz 1, 95100 Selb GERMANY</p> <p>VISHAY Electronic Spol. s.r.o. zavod Sokolov Geschäftsbereich Draloric Bergmannova 392, 356 04 DOLNI RYCHNOV CZECH REPUBLIC</p> <p><input type="checkbox"/> Additional Information on page 2 1000 pF to 8000 pF; X1/Y2; ±20% (M); X1: AC 400 V; Y2: AC 250/300 V; 40/125/21/C; Ceramic: Y5S</p> <p>CM</p> <p>25Y</p> <p><input checked="" type="checkbox"/> Additional Information on page 2 IEC 60384-14:2013 IEC 60384-14:2013/AMD1:2016</p> <p>280991-TL3-1</p>
<p>This CB Test Certificate is issued by the National Certification Body</p>	
<p>VDE Prüf- und Zertifizierungsinstitut GmbH VDE Testing and Certification Institute Zertifizierungsstelle und internat. Angelegenheiten Certification Body and internat. Affairs</p> <p>Date: 2021-05-31</p> <p>Signature:  R. Nickel</p>	

Issued 2018-06-05

1/2