



Aluminum Capacitors



RoHS
COMPLIANT

FEATURES

- Load life: 2000 h at 105 °C
- Extra low impedance, high ripple current
- Polarized SMD aluminum electrolytic capacitors, non solid electrolyte
- Material categorization: for definitions of compliance please see www.vishay.com/doc?99912

APPLICATIONS

- SMD technology, for high mounting density
- Industrial and professional applications
- General industrial, consumer
- Smoothing, filtering, buffering

PACKAGING

Supplied in blister tape.

QUICK REFERENCE DATA

DESCRIPTION	VALUE
Nominal case size (\varnothing D x L in mm)	6 x 5.8 to 12.5 x 13.5
Rated capacitance range C_R	10 μ F to 1500 μ F
Capacitance tolerance	\pm 20 %
Rated voltage range	6.3 V to 50 V
Category temperature range	-40 °C to 105 °C
Load life	2000 h
Based on sectional specification	IEC 60384-4 / EN 130300
Climatic category IEC 60068	40 / 105 / 56

SELECTION CHART FOR C_R , U_R , AND RELEVANT NOMINAL CASE SIZES (\varnothing D x L in mm)

C_R (μ F)	RATED VOLTAGE (V)					
	6.3	10	16	25	35	50
10	→	→	→	→	→	6.3 x 5.8
22	→	→	→	→	→	6.3 x 5.8
33	→	→	→	→	6.3 x 5.8	8 x 6.2
47	→	→	→	→	6.3 x 5.8	8 x 6.2
68	→	→	→	6.3 x 5.8	8 x 6.2	8 x 10
100	→	→	6.3 x 5.8	8 x 6.2	8 x 10	10 x 10
220	6.3 x 5.8	6.3 x 7.7	8 x 6.2	8 x 10	10 x 10	-
330	8 x 6.2	→	8 x 10	-	-	-
470	→	8 x 10	10 x 10	-	-	-
680	→	10 x 10	-	-	-	-
1000	10 x 10	-	-	-	-	-
1500	10 x 10	-	-	-	-	-



DIMENSIONS in millimeters									
CASE SIZE CODE	D ± α	L ± α	A ± α	B ± α	C ± α	E ± α	R	N	P
AD	6.3 ± 0.5	5.8 ± 0.3	2.4 ± 0.2	6.6 ± 0.2	6.6 ± 0.2	2.2 ± 0.2	0.5 to 0.8	0.3	0.5
BM	6.3 ± 0.5	7.7 ± 0.4	2.4 ± 0.2	6.6 ± 0.2	6.6 ± 0.2	2.2 ± 0.2	0.5 to 0.8	0.3	0.5
AE	8 ± 0.5	6.2 ± 0.4	3.3 ± 0.2	8.3 ± 0.2	8.3 ± 0.2	2.3 ± 0.2	0.5 to 0.8	0.3	0.5
AF	8 ± 0.5	10 ± 0.5	2.9 ± 0.2	8.3 ± 0.2	8.3 ± 0.2	3.1 ± 0.2	0.8 to 1.1	0.3	0.5
AG	10 ± 0.5	10 ± 0.5	3.2 ± 0.2	10.3 ± 0.2	10.3 ± 0.2	4.5 ± 0.2	0.8 to 1.1	0.3	0.5
AH	12.5 ± 0.5	13.5 ± 0.5	4.6 ± 0.2	12.8 ± 0.2	12.8 ± 0.2	4.5 ± 0.2	1.1 to 1.4	0.3	0.5

The technical drawings include:

- Top View:** Shows an octagonal case with a central square area. Labels include 'Capacitance' (⊕), 'Lot no.', '22 μF', '50', and 'Voltage' (⊖).
- Side View:** Shows the profile of the capacitor with labels for 'Plastic platform', 'N max.', 'Ø D ± α', and 'L ± α'.
- Cross-sectional View:** Shows the internal structure with labels for 'C ± α', '⊕ Positive P max.', 'A ± α', 'E ± α', 'B ± α', 'R', and '⊖ Negative'.

ELECTRICAL DATA	
SYMBOL	DESCRIPTION
U _R	Rated voltage
C _R	Rated capacitance at 120 Hz
tan δ	Max. dissipation factor at 120 Hz
R _{ESR}	Max. equivalent series resistance at 120 Hz
I _R	Rated alternating current at 120 Hz and upper category temperature
Z	Max. impedance at 100 kHz

Note

- Unless otherwise specified, all electrical values apply at T_{amb} = 20 °C, P = 86 to 100 kPa, RH = 45 to 75 %.

ORDERING EXAMPLE

ECL 22 μF / 50 V, ± 20 %, size 6.3 x 5.8 mm

Ordering code: MALSECL00AD222HARK


For Standard Packaging Quantity (SPQ) and Minimum Order Quantity (MOQ) please refer to our price list or contact customer service.

ELECTRICAL DATA AND ORDERING INFORMATION							
U _R (V)	C _R 120 Hz (μF)	DIMENSIONS D x L (mm)	tan δ 120 Hz	Z 100 kHz / 20 °C (Ω)	I _R 100 kHz / 105 °C (mA)	WEIGHT (g)	CATALOG NUMBER
6.3	220	6.3 x 5.8	0.24	0.44	230	0.30	MALSECL00AD322BARK
	330	8 x 6.2	0.24	0.26	300	0.55	MALSECL00AE333BARK
	1000	10 x 10	0.24	0.09	670	1.21	MALSECL00AG410BARK
	1500	10 x 10	0.24	0.09	670	1.21	MALSECL00AG415BARK
10	220	6.3 x 7.7	0.19	0.34	280	0.40	MALSECL00BM322CARK
	470	8 x 10	0.19	0.17	450	1.00	MALSECL00AF347CARK
	680	10 x 10	0.19	0.09	670	1.21	MALSECL00AG368CARK
16	100	6.3 x 5.8	0.16	0.44	230	0.30	MALSECL00AD310DARK
	220	8 x 6.2	0.16	0.26	300	0.55	MALSECL00AE322DARK
	330	8 x 10	0.16	0.17	450	1.00	MALSECL00AF333DARK
	470	10 x 10	0.16	0.09	670	1.21	MALSECL00AG347DARK



ELECTRICAL DATA AND ORDERING INFORMATION							
U_R (V)	C_R 120 Hz (μ F)	DIMENSIONS D x L (mm)	$\tan \delta$ 120 Hz	Z 100 kHz / 20 °C (Ω)	I_R 100 kHz / 105 °C (mA)	WEIGHT (g)	CATALOG NUMBER
25	68	6.3 x 5.8	0.14	0.44	230	0.30	MALSECL00AD268EARK
	100	8 x 6.2	0.14	0.26	300	0.55	MALSECL00AE310EARK
	220	8 x 10	0.14	0.17	450	1.00	MALSECL00AF322EARK
35	33	6.3 x 5.8	0.12	0.44	230	0.30	MALSECL00AD233FARK
	47	6.3 x 5.8	0.12	0.44	230	0.30	MALSECL00AD247FARK
	68	8 x 6.2	0.12	0.26	300	0.55	MALSECL00AE268FARK
	100	8 x 10	0.12	0.17	450	1.00	MALSECL00AF310FARK
	220	10 x 10	0.12	0.09	670	1.21	MALSECL00AG322FARK
50	10	6.3 x 5.8	0.12	0.88	165	0.30	MALSECL00AD210HARK
	22	6.3 x 5.8	0.12	0.88	165	0.30	MALSECL00AD222HARK
	33	8 x 6.2	0.12	0.63	300	0.55	MALSECL00AE233HARK
	47	8 x 6.2	0.12	0.63	300	0.55	MALSECL00AE247HARK
	68	8 x 10	0.12	0.34	450	1.00	MALSECL00AF268HARK
	100	10 x 10	0.12	0.18	670	1.21	MALSECL00AG310HARK

REFLOW SOLDERING CONDITIONS FOR SMD ALUMINUM ELECTROLYTIC CAPACITORS



PROFILE FEATURE	SOLDERING CONDITION		
	Ø 4 TO Ø 10	Ø 12.5	Ø 16
Average ramp-up rate (T_L to T_P)	3 °C/s max.	3 °C/s max.	
Preheat			
Temperature min. (T_s min.)	150 °C	150 °C	
Temperature max. (T_s max.)	200 °C	200 °C	
Time (T_s min. to T_s max.)	60 s to 150 s	40 s to 120 s	40 s to 100 s
T_s max. to T_L			
Ramp-up rate	3 °C/s max.	3 °C/s max.	
Time maintained above			
Temperature (T_L)	217 °C	217 °C	
Time (t_L)	60 s to 90 s	40 s to 60 s	
Peak / classification temperature (T_P)	250 °C	240 °C	230 °C
Time within 5 °C of actual peak temperature (T_P)	10 s max.	10 s max.	
Ramp-down rate	3 °C/s max.	3 °C/s max.	
Time 25 °C to peak temperature	8 min max.	8 min max.	



RESISTANCE TO SOLDERING HEAT	
Leakage current	Less than specified value
Capacitance value	Within $\pm 10\%$ of initial value
$\tan \delta$	Less than specified value

LOW TEMPERATURE BEHAVIOR (at 120 Hz)								
IMPEDANCE RATIO (Z) T2/(Z) T1	RATED VOLTAGE (V)							
T2/T1	6.3	10	16	25	35	50	63	100
-25 °C / +20 °C	2	2	2	2	2	2	3	3
-40 °C / +20 °C	3	3	3	3	3	3	4	4

MULTIPLIER OF RIPPLE CURRENT (I_R) AS A FUNCTION OF FREQUENCY	
FREQUENCY (Hz)	I_R MULTIPLIER
50	0.41
120	0.59
300	0.69
1000	0.80
10 000	0.88
100 000	1.00

ADDITIONAL ELECTRICAL DATA		
PARAMETER	CONDITIONS	VALUE
Current		
Leakage current (test conditions: U_R , 20 °C)	After 2 min at U_R	$I_{L2} \leq 0.01 \times C_R \times U_R$ or 3 μ A for $U_R \leq 100$ V (whichever is greater)
Resistance		
Equivalent series resistance (ESR)	Calculated from $\tan \delta_{max}$.	$ESR = \tan \delta / 2 \pi f C_R$

TEST PROCEDURES AND REQUIREMENTS		
TEST	PROCEDURE (quick reference)	REQUIREMENTS
Load life	$T_{amb} = 105$ °C U_R and I_R applied After 2000 h	$\Delta C/C: \pm 25\%$ of initial value $I_L \leq$ spec. limit $\tan \delta \leq 2 \times$ spec. limit
Shelf life	No voltage applied After 1000 h After test: U_R to be applied for 30 min 24 h to 48 h before measurement	$\Delta C/C: \pm 25\%$ of initial value $I_L \leq$ spec. limit $\tan \delta \leq 2 \times$ spec. limit

Statements about product lifetime are based on calculations and internal testing. They should only be interpreted as estimations. Also due to external factors, the lifetime in the field application may deviate from the calculated lifetime. In general, nothing stated herein shall be construed as a guarantee of durability.



Disclaimer

ALL PRODUCT, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE TO IMPROVE RELIABILITY, FUNCTION OR DESIGN OR OTHERWISE.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product.

Vishay makes no warranty, representation or guarantee regarding the suitability of the products for any particular purpose or the continuing production of any product. To the maximum extent permitted by applicable law, Vishay disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Statements regarding the suitability of products for certain types of applications are based on Vishay's knowledge of typical requirements that are often placed on Vishay products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. Parameters provided in datasheets and / or specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein.

Hyperlinks included in this datasheet may direct users to third-party websites. These links are provided as a convenience and for informational purposes only. Inclusion of these hyperlinks does not constitute an endorsement or an approval by Vishay of any of the products, services or opinions of the corporation, organization or individual associated with the third-party website. Vishay disclaims any and all liability and bears no responsibility for the accuracy, legality or content of the third-party website or for that of subsequent links.

Vishay products are not designed for use in life-saving or life-sustaining applications or any application in which the failure of the Vishay product could result in personal injury or death unless specifically qualified in writing by Vishay. Customers using or selling Vishay products not expressly indicated for use in such applications do so at their own risk. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay. Product names and markings noted herein may be trademarks of their respective owners.