




## AC and Pulse Metallized Polypropylene Film Capacitors KP/MMKP Radial Potted Type



Dimensions in mm

### APPLICATIONS

Where high currents and steep pulses occur.  
Power supplies.

### MARKING

C-value; tolerance; rated voltage; manufacturer's type designation; code for dielectric material; manufacturer's emblem; code for factory of origin; year and week of manufacture

### DIELECTRIC

Polypropylene film

### ELECTRODES

Metallized film and aluminum foil

### ENCAPSULATION

Flame retardant plastic case and epoxy resin  
(UL-class 94 V-0)

### CONSTRUCTION

Internal serial construction

### LEADS

Tinned wire

### CAPACITANCE RANGE (E24 SERIES)

0.0047  $\mu$ F to 0.27  $\mu$ F

### FEATURES

15 mm to 27.5 mm pitch. Supplied loose and taped on reel

Material categorization:  
for definitions of compliance please see  
[www.vishay.com/doc?99912](http://www.vishay.com/doc?99912)

### CAPACITANCE TOLERANCE

$\pm 5\%$ ;  $\pm 3.5\%$

### RATED (DC) VOLTAGE

630 V; 1000 V

### RATED (AC) VOLTAGE

300 V; 400 V

### RATED PEAK-TO-PEAK VOLTAGE

850 V; 1100 V

### CLIMATIC CATEGORY

55/100/56

### RATED TEMPERATURE

85 °C

### MAXIMUM APPLICATION TEMPERATURE

100 °C

### REFERENCE SPECIFICATIONS

IEC 60384-17

### PERFORMANCE GRADE

Grade 1 (long life)

### STABILITY GRADE

Grade 2

### DETAIL SPECIFICATION


For more detailed data and test requirements see "Type  
Detail Specification HQN-384-17/101"



RoHS  
COMPLIANT  
HALOGEN  
FREE  
GREEN  
(5-2008)



**COMPOSITION OF CATALOG NUMBER**



**Note**

<sup>(1)</sup> For detailed tape specification refer to "Packaging Information": [www.vishay.com/doc?28139](http://www.vishay.com/doc?28139)

**SPECIFIC REFERENCE DATA (630 V<sub>DC</sub>)**

| DESCRIPTION   | VALUE                  |                         |
|---|------------------------|-------------------------|
|   | at 10 kHz              | at 100 kHz              |
| Tangent of loss angle:  |                        |                         |
| P = 15.0 mm   | ≤ 5 x 10 <sup>-4</sup> | ≤ 10 x 10 <sup>-4</sup> |
| P = 22.5 mm   | ≤ 6 x 10 <sup>-4</sup> | ≤ 15 x 10 <sup>-4</sup> |
| P = 27.5 mm   | ≤ 7 x 10 <sup>-4</sup> | ≤ 20 x 10 <sup>-4</sup> |
| Rated voltage pulse slope (dU/dt) <sub>R</sub> :                                      |                        |                         |
| P = 15.0 mm   | 4000 V/μs              |                         |
| P = 22.5 mm   | 1400 V/μs              |                         |
| P = 27.5 mm   | 900 V/μs               |                         |
| R between leads at 500 V; 1 min   | > 100 000 MΩ           |                         |
| R between interconnected leads and case; 500 V; 1 min                                 | > 100 000 MΩ           |                         |
| Ionization (AC) voltage (typical value) at 50 pC peak discharge                       | > 400 V                |                         |
| Withstanding (DC) voltage (cut off current 10 mA) <sup>(1)</sup> ; rise time 1000 V/s | 1008 V; 1 min          |                         |
| Withstanding (DC) voltage between leads and case                                      | 2840 V; 1 min          |                         |

**Note**

<sup>(1)</sup> See "Voltage Proof Test for Metalized Film Capacitors": [www.vishay.com/doc?28169](http://www.vishay.com/doc?28169)


 $U_{RDC} = 630 \text{ V}; U_{RAC} = 300 \text{ V}; U_{P-P} = 850 \text{ V}$ 

| C<br>( $\mu\text{F}$ )  | DIMENSIONS<br>W x H x L<br>(mm) | MASS<br>(g) <sup>(2)</sup> | CATALOG NUMBER BFC2 376 ..... AND PACKAGING |           |  |
|---|---------------------------------|----------------------------|---|-----------|--|
|   |                                 |                            | LOOSE IN BOX                                |           | REEL <sup>(1)</sup><br>H = 18.5 mm<br>P <sub>0</sub> = 12.7 mm |
|   |                                 |                            | $l_t = 5.0 \pm 1.0 \text{ mm}$              | ALL LEADS |  |
|   |                                 |                            | C-tol. = $\pm 5 \%$                         | SPQ       | SPQ  |
| Pitch = $15.0 \pm 0.4 \text{ mm}; d_t = 0.60 \pm 0.06 \text{ mm}$ |                                 |                            |   |           |  |
| 0.0068<br>0.0075<br>0.0082<br>0.0091                              | 5.0 x 11.0 x 17.5               | 1.1                        | 62682<br>62752<br>62822<br>62912            | 1000      | 1100   |
| 0.010<br>0.011<br>0.012<br>0.013                                  | 6.0 x 12.0 x 17.5               | 1.5                        | 62103<br>62113<br>62123<br>62133            | 1000      | 900  |
| Pitch = $15.0 \pm 0.4 \text{ mm}; d_t = 0.80 \pm 0.08 \text{ mm}$ |                                 |                            |   |           |  |
| 0.015<br>0.016<br>0.018   | 7.0 x 13.5 x 17.5               | 2.0                        | 62153<br>62163<br>62183                     | 1000      | 800  |
| 0.020<br>0.022  | 8.5 x 15.0 x 17.5               | 2.6                        | 62203<br>62223                              | 1000      | 650  |
| Pitch = $22.5 \pm 0.4 \text{ mm}; d_t = 0.80 \pm 0.08 \text{ mm}$ |                                 |                            |   |           |  |
| 0.024<br>0.027<br>0.030   | 6.0 x 15.5 x 26.0               | 2.8                        | 62243<br>62273<br>62303                     | 300       | 600  |
| 0.033<br>0.036<br>0.039   | 7.0 x 16.5 x 26.0               | 3.5                        | 62333<br>62363<br>62393                     | 200       | 550  |
| 0.043<br>0.047<br>0.051<br>0.056                                  | 8.5 x 18.0 x 26.0               | 4.5<br>4.5<br>4.5<br>5.1   | 62433<br>62473<br>62513<br>62563            | 200       | 450  |
| Pitch = $27.5 \pm 0.4 \text{ mm}; d_t = 0.80 \pm 0.08 \text{ mm}$ |                                 |                            |   |           |  |
| 0.062<br>0.068<br>0.075   | 9.0 x 19.0 x 31.0               | 6.2                        | 62623<br>62683<br>62753                     | 100       |  |
| 0.082<br>0.091<br>0.10<br>0.11                                    | 11.0 x 21.0 x 31.0              | 8.3                        | 62823<br>62913<br>62104<br>62114            | 100       |  |
| 0.12<br>0.13<br>0.15<br>0.16                                      | 13.0 x 23.0 x 31.0              | 10.8                       | 62124<br>62134<br>62154<br>62164            | 100       |  |
| 0.18<br>0.20  | 15.0 x 25.0 x 31.0              | 13.0                       | 62184<br>62204                              | 100       |  |
| 0.22<br>0.24<br>0.27  | 18.0 x 28.0 x 31.0              | 19.0                       | 62224<br>62244<br>62274                     | 100       |  |

## Notes

- SPQ = Standard Packing Quantity

<sup>(1)</sup> H = in-tape height; P<sub>0</sub> = sprocket hole distance; for detailed specifications refer to packaging information

<sup>(2)</sup> Weight for short lead product only

SPECIFIC REFERENCE DATA (1000 V<sub>DC</sub>)

| DESCRIPTION   | VALUE   |  |
|---|---|--|
|   | at 10 kHz   | at 100 kHz   |
| Tangent of loss angle:<br>P = 15.0 mm<br>P = 22.5 mm<br>P = 27.5 mm   | $\leq 5 \times 10^{-4}$<br>$\leq 6 \times 10^{-4}$<br>$\leq 8 \times 10^{-4}$ | $\leq 10 \times 10^{-4}$<br>$\leq 15 \times 10^{-4}$<br>$\leq 20 \times 10^{-4}$ |
| Rated voltage pulse slope (dU/dt) <sub>R</sub> :<br>P = 15.0 mm<br>P = 22.5 mm<br>P = 27.5 mm                           | 7000 V/μs<br>2500 V/μs<br>1600 V/μs   |  |
| R between leads at 500 V; 1 min   | > 100 000 MΩ  |  |
| R between interconnected leads and case; 500 V; 1 min   | > 100 000 MΩ  |  |
| Ionization (AC) voltage (typical value) at 50 pC peak discharge   | > 500 V   |  |
| Withstanding (DC) voltage (cut off current 10 mA) <sup>(1)</sup> ; rise time 1000 V/s<br>for C ≤ 47 nF<br>for C > 47 nF | 1600 V; 1 min<br>[1, 6 - (0, 0364 · √C - 47)] × 1000 V; 1 min                 |  |
| Withstanding (DC) voltage between leads and case  | 2840 V; 1 min   |  |

## Note

<sup>(1)</sup> See "Voltage Proof Test for Metalized Film Capacitors": [www.vishay.com/doc?28169](http://www.vishay.com/doc?28169)

U<sub>RDC</sub> = 1000 V; U<sub>RAC</sub> = 400 V; U<sub>P-P</sub> = 1100 V

| C<br>(μF)   | DIMENSIONS<br>W x H x L<br>(mm)         | MASS<br>(g) <sup>(2)</sup> | CATALOG NUMBER BFC2 376 ..... AND PACKAGING                          |            |  |
|---|---|----------------------------|--|------------|--|
|   |   |                            | LOOSE IN BOX   |            | REEL <sup>(1)</sup><br>H = 18.5 mm<br>P <sub>0</sub> = 12.7 mm |
|   |   |                            | l <sub>t</sub> = 5.0 ± 1.0 mm  | ALL LEADS  |  |
|   |   |                            | C-tol. = ± 5 %   | SPQ        | SPQ  |
| <b>Pitch = 15.0 ± 0.4 mm; d<sub>t</sub> = 0.60 ± 0.06 mm</b>        |   |                            |  |            |  |
| 0.0047<br>0.0051<br>0.0056  | 5.0 x 11.0 x 17.5                       | 1.1                        | 72472<br>72512<br>72562  | 1000       | 1100   |
| 0.0062<br>0.0068<br>0.0075<br>0.0082                                | 6.0 x 12.0 x 17.5                       | 1.5                        | 72622<br>72682<br>72752<br>72822                                     | 1000       | 900  |
| <b>Pitch = 15.0 ± 0.4 mm; d<sub>t</sub> = 0.80 ± 0.08 mm</b>        |   |                            |  |            |  |
| 0.0091<br>0.010<br>0.011<br>0.012                                   | 7.0 x 13.5 x 17.5                       | 2.0                        | 72912<br>72103<br>72113<br>72123                                     | 1000       | 800  |
| <b>Pitch = 22.5 ± 0.4 mm; d<sub>t</sub> = 0.80 ± 0.08 mm</b>        |   |                            |  |            |  |
| 0.013<br>0.015<br>0.016<br>0.018                                    | 6.0 x 15.5 x 26.0<br>7.0 x 16.5 x 26.0  | 2.8<br>3.5                 | 72133<br>72153<br>72163<br>72183                                     | 300<br>200 | 600<br>550   |
| 0.020<br>0.022<br>0.024<br>0.027<br>0.03<br>0.033<br>0.036<br>0.039 | 8.5 x 18.0 x 26.0<br>10.0 x 19.5 x 26.0 | 4.5<br>5.4                 | 72203<br>72223<br>72243<br>72273<br>72303<br>72333<br>72363<br>72393 | 200        | 450<br>350   |



| C<br>( $\mu$ F)                                     | DIMENSIONS<br>W x H x L<br>(mm) | MASS<br>(g) <sup>(2)</sup> | CATALOG NUMBER BFC2 376 ..... AND PACKAGING |           |  |
|---|---------------------------------|----------------------------|---|-----------|--|
|   |                                 |                            | LOOSE IN BOX                                |           | REEL <sup>(1)</sup><br>H = 18.5 mm<br>P <sub>0</sub> = 12.7 mm |
|   |                                 |                            | $l_t = 5.0 \pm 1.0$ mm                      | ALL LEADS |  |
|   |                                 |                            | C-tol. = $\pm 5$ %                          | SPQ       | SPQ  |
| LAST 5 DIGITS OF<br>CATALOG NUMBER                  |                                 |                            |   |           |  |
| Pitch = $27.5 \pm 0.4$ mm; $d_t = 0.80 \pm 0.08$ mm |                                 |                            |   |           |  |
| 0.043   | 9.0 x 19.0 x 31.0               | 6.2                        | 72433                                       | 100       |  |
| 0.047   |                                 |                            | 72473                                       |           |  |
| 0.051   |                                 |                            | 72513                                       |           |  |
| 0.056   | 11.0 x 21.0 x 31.0              | 8.3                        | 72563                                       | 100       |  |
| 0.062   |                                 |                            | 72623                                       |           |  |
| 0.068   |                                 |                            | 72683                                       |           |  |
| 0.075   |                                 |                            | 72753                                       |           |  |
| 0.082   | 13.0 x 23.0 x 31.0              | 10.8                       | 72823                                       | 100       |  |
| 0.091   |                                 |                            | 72913                                       |           |  |
| 0.10  |                                 |                            | 72104                                       |           |  |
| 0.11  | 15.0 x 25.0 x 31.0              | 13.0                       | 72114                                       | 100       |  |
| 0.12  |                                 |                            | 72124                                       |           |  |
| 0.13  |                                 |                            | 72134                                       |           |  |
| 0.15  |                                 |                            | 72154                                       |           |  |
| 0.16  | 18.0 x 28.0 x 31.0              | 19.0                       | 72164                                       | 100       |  |
| 0.18  |                                 |                            | 72184                                       |           |  |

Notes

- SPQ = Standard Packing Quantity

<sup>(1)</sup> H = in-tape height; P<sub>0</sub> = sprocket hole distance; for detailed specifications refer to packaging information

<sup>(2)</sup> Weight for short lead product only



## **Disclaimer**

ALL PRODUCT, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE TO IMPROVE RELIABILITY, FUNCTION OR DESIGN OR OTHERWISE.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product.

Vishay makes no warranty, representation or guarantee regarding the suitability of the products for any particular purpose or the continuing production of any product. To the maximum extent permitted by applicable law, Vishay disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Statements regarding the suitability of products for certain types of applications are based on Vishay's knowledge of typical requirements that are often placed on Vishay products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. Parameters provided in datasheets and / or specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein.

Except as expressly indicated in writing, Vishay products are not designed for use in medical, life-saving, or life-sustaining applications or for any other application in which the failure of the Vishay product could result in personal injury or death. Customers using or selling Vishay products not expressly indicated for use in such applications do so at their own risk. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay. Product names and markings noted herein may be trademarks of their respective owners.