

Aluminum Electrolytic Capacitors

Radial Standard Ultra Miniature





Fig. 1

| QUICK REFERENCE DATA | |
|---|------------------------|
| DESCRIPTION | VALUE |
| Nominal case sizes (Ø D x L in mm) | 5 x 11 to 18 x 40 |
| Rated capacitance range, C _R | 2.2 µF to 22 000 µF |
| Tolerance on C _R | ± 20 % |
| Rated voltage range, U _R | 6.3 V to 100 V |
| Category temperature range | -40 °C to +85 °C |
| Endurance test at 85 °C: | |
| Case size Ø D ≤ 8 mm | 2000 h |
| Case size Ø D ≥ 10 mm | 3000 h |
| Useful life at 85 °C: | |
| Case size Ø D ≤ 8 mm | 2500 h |
| Case size Ø D ≥ 10 mm | 3500 h |
| Useful life at 40 °C, 1.4 x I _R applied: | |
| Case size Ø D ≤ 8 mm | 60 000 h |
| Case size Ø D ≥ 10 mm | 90 000 h |
| Shelf life at 0 V, 85 °C | 1000 h |
| Based on sectional specification | IEC 60384-4 / EN130300 |
| Climatic category IEC 60068 | 40 / 085 / 56 |

FEATURES

- Polarized aluminum electrolytic capacitors, non-solid electrolyte
- Radial leads, cylindrical aluminum case, insulated with a blue sleeve
- Pressure relief for case Ø D ≥ 6.3 mm
- Charge and discharge proof
- Miniaturized, high CV-product per unit volume
- Material categorization: for definitions of compliance please see www.vishay.com/doc?99912


RoHS
COMPLIANT

APPLICATIONS

- General purpose, industrial, automotive, consumer, and audio-video
- Coupling, decoupling, timing, smoothing, filtering, buffering in SMPS
- Portable and mobile equipment (small size, low mass)

MARKING

The capacitors are marked (where possible) with the following information:

- Rated capacitance (in µF)
- Tolerance on rated capacitance, code letter in accordance with IEC 60062 (M for ± 20 %)
- Rated voltage (in V)
- Date code, in accordance with IEC 60062
- Code indicating factory of origin
- Name of manufacturer
- Negative terminal identification
- Series number (038)

| SELECTION CHART FOR C_R, U_R, AND RELEVANT NOMINAL CASE SIZES ($\varnothing D \times L$ in mm) | | | | | | | | |
|--|-----------|----------|----------|----------|----------|----------|----------|----------|
| C_R (μF) | U_R (V) | | | | | | | |
| | 6.3 | 10 | 16 | 25 | 35 | 50 | 63 | 100 |
| 2.2 | – | – | – | – | – | – | 5 x 11 | 5 x 11 |
| 3.3 | – | – | – | – | – | – | 5 x 11 | 5 x 11 |
| 4.7 | – | – | – | – | – | – | 5 x 11 | 5 x 11 |
| 10 | – | – | – | – | – | – | 5 x 11 | 6.3 x 11 |
| 22 | – | – | – | – | – | 5 x 11 | 5 x 11 | 6.3 x 11 |
| 33 | – | – | – | – | – | 5 x 11 | 6.3 x 11 | 8 x 11.5 |
| 47 | – | – | – | – | 5 x 11 | 6.3 x 11 | 6.3 x 11 | 10 x 12 |
| 100 | – | 5 x 11 | 5 x 11 | 6.3 x 11 | 6.3 x 11 | 8 x 11.5 | 10 x 12 | 10 x 20 |
| 220 | 5 x 11 | 5 x 11 | 6.3 x 11 | 8 x 11.5 | 8 x 11.5 | 10 x 12 | 10 x 16 | 13 x 25 |
| 330 | 6.3 x 11 | 6.3 x 11 | 8 x 11.5 | 8 x 11.5 | 10 x 12 | 10 x 16 | 10 x 20 | 13 x 25 |
| 470 | 6.3 x 11 | 6.3 x 11 | 8 x 11.5 | 10 x 12 | 10 x 16 | 10 x 20 | 13 x 20 | 16 x 25 |
| 1000 | 8 x 11.5 | 10 x 12 | 10 x 16 | 10 x 20 | 13 x 20 | 13 x 25 | 16 x 25 | 18 x 40 |
| 2200 | 10 x 16 | 10 x 20 | 13 x 20 | 13 x 25 | 6 x 25 | 16 x 31 | 18 x 35 | – |
| 3300 | 10 x 20 | 13 x 20 | 13 x 25 | 16 x 25 | 16 x 35 | 18 x 35 | – | – |
| 4700 | 13 x 20 | 13 x 25 | 16 x 25 | 16 x 31 | 18 x 35 | – | – | – |
| 6800 | 13 x 25 | 16 x 25 | 16 x 31 | 18 x 35 | – | – | – | – |
| 10 000 | 16 x 25 | 16 x 35 | 18 x 35 | – | – | – | – | – |
| 22 000 | 18 x 40 | – | – | – | – | – | – | – |




DIMENSIONS in millimeters AND AVAILABLE FORMS


Fig. 2 - Form CA


 Fig. 3 - Form CB:
Cut leads


Dimensions of pitch F see Table 1 and Table 2


 Fig. 4 - Form TNA, Form TFA:
Taped in box (ammopack), straight leads

 Case $\varnothing D = 5$ mm to 8 mm; pitch F is 5 mm

 Fig. 5 - Form TFA:
Taped in box (ammopack), formed leads

Table 1

| DIMENSIONS in millimeters, MASS AND PACKAGING QUANTITIES | | | | | | | | | |
|---|-----------|-----------------|------------------------|------------|---------------|----------------|----------------------|---------|---------------|
| NOMINAL CASE SIZE $\varnothing D \times L$ | CASE CODE | $\varnothing d$ | $\varnothing D_{max.}$ | $L_{max.}$ | F | MASS (g) | PACKAGING QUANTITIES | | |
| | | | | | | | FORM CA | FORM CB | FORM TFA, TNA |
| 5 x 11 | 11 | 0.5 | 5.5 | 12.5 | 2.0 ± 0.5 | ≈ 0.4 | 5000 | – | 2000 |
| 6.3 x 11 | 12 | 0.5 | 6.8 | 12.5 | 2.5 ± 0.5 | ≈ 0.6 | 5000 | – | 2000 |
| 8 x 11.5 | 13 | 0.6 | 8.5 | 12.5 | 3.5 ± 0.5 | ≈ 1.1 | 5000 | – | 1000 |
| 10 x 12 | 14 | 0.6 | 10.5 | 13.5 | 5.0 ± 0.5 | ≈ 1.6 | 3000 | 1000 | 500 |
| 10 x 16 | 15 | 0.6 | 10.5 | 17.5 | 5.0 ± 0.5 | ≈ 1.9 | 2500 | 1000 | 500 |
| 10 x 20 | 16 | 0.6 | 10.5 | 22.0 | 5.0 ± 0.5 | ≈ 2.2 | 2000 | 800 | 500 |
| 13 x 20 | 17 | 0.6 | 13.5 | 22.0 | 5.0 ± 0.5 | ≈ 4.0 | 1500 | 400 | 300 |
| 13 x 25 | 18 | 0.6 | 13.5 | 27.0 | 5.0 ± 0.5 | ≈ 5.0 | 1000 | 400 | 300 |
| 16 x 25 | 19 | 0.8 | 16.5 | 27.0 | 7.5 ± 0.5 | ≈ 8.0 | 750 | 200 | 200 |
| 16 x 31 | 20 | 0.8 | 16.5 | 33.5 | 7.5 ± 0.5 | ≈ 9.0 | 600 | 200 | 200 |
| 16 x 35 | 21 | 0.8 | 16.5 | 37.5 | 7.5 ± 0.5 | ≈ 11.0 | 500 | 200 | – |
| 18 x 35 | 22 | 0.8 | 18.5 | 37.5 | 7.5 ± 0.5 | ≈ 14.5 | 400 | 150 | – |
| 18 x 40 | 23 | 0.8 | 18.5 | 42.0 | 7.5 ± 0.5 | ≈ 16.0 | 400 | 150 | – |

Note

- Detailed tape dimensions see section "Packaging".



| ELECTRICAL DATA | |
|-----------------|--|
| SYMBOL | DESCRIPTION |
| C _R | Rated capacitance at 100 Hz, tolerance ± 20 % |
| I _R | Rated RMS ripple current at 100 Hz, 85 °C |
| I _{L2} | Max. leakage current after 2 min at U _R |
| tan δ | Max. dissipation factor at 100 Hz |

ORDERING EXAMPLE

Electrolytic capacitor 038 series

470 µF / 25 V; ± 20 %

Nominal case size: Ø 10 mm x 12 mm; form TFA

Ordering code: MAL2 038 36471 E3

Former 12NC: 2222 038 36471

Note

- Unless otherwise specified, all electrical values in Table 2 apply at T_{amb} = 20 °C, P = 86 kPa to 106 kPa, RH = 45 % to 75 %.

Table 2

| ELECTRICAL DATA AND ORDERING INFORMATION | | | | | | | | | | | | | | |
|--|----------------------------------|---|---|----------------------------------|-----------------|------------------------------|-----------------------------|-----------|------------|-----------|----------------|-----------|-------------|-----------|
| U _R (V) | C _R 100 Hz (µF) | NOMINAL CASE SIZE Ø D x L (mm) | I _R 100 Hz 85 °C (mA) | I _{L2} 2 min (µA) | tan δ 100 Hz | FREQ. CODE ⁽¹⁾ | ORDERING CODE MAL2038 | | | | | | | |
| | | | | | | | BULK PACKAGING | | | | TAPED AMMOPACK | | | |
| | | | | | | | LONG LEADS | | CUT LEADS | | FORM TFA | | FORM TNA | |
| | | | | | | | FORM CA | F (mm) | FORM CB | F (mm) | FORM TFA | F (mm) | FORM TNA | F (mm) |
| 6.3 | 220 | 5 x 11 | 200 | 14 | 0.23 | MF2 | 53221E3 | 2.0 | - | - | 33221E3 | 5.0 | 73221E3 | 2.5 |
| | 330 | 6.3 x 11 | 270 | 21 | 0.23 | MF2 | 53331E3 | 2.5 | - | - | 33331E3 | 5.0 | 73331E3 | 2.5 |
| | 470 | 6.3 x 11 | 320 | 30 | 0.23 | MF2 | 53471E3 | 2.5 | - | - | 33471E3 | 5.0 | 73471E3 | 2.5 |
| | 1000 | 8 x 11.5 | 540 | 63 | 0.23 | MF2 | 53102E3 | 3.5 | - | - | 33102E3 | 5.0 | 73102E3 | 3.5 |
| | 2200 | 10 x 16 | 785 | 139 | 0.25 | MF3 | 53222E3 | 5.0 | 63222E3 | 5.0 | 33222E3 | 5.0 | - | - |
| | 3300 | 10 x 20 | 1185 | 208 | 0.27 | MF3 | 53332E3 | 5.0 | 63332E3 | 5.0 | 33332E3 | 5.0 | - | - |
| | 4700 | 13 x 20 | 1545 | 296 | 0.29 | MF3 | 53472E3 | 5.0 | 63472E3 | 5.0 | 33472E3 | 5.0 | - | - |
| | 6800 | 13 x 25 | 1880 | 428 | 0.33 | MF3 | 53682E3 | 5.0 | 63682E3 | 5.0 | 33682E3 | 5.0 | - | - |
| | 10 000 | 16 x 25 | 2330 | 630 | 0.41 | MF3 | 53103E3 | 7.5 | 63103E3 | 7.5 | 33103E3 | 7.5 | - | - |
| | 22 000 | 18 x 40 | 3320 | 1386 | 0.65 | MF3 | 53223E3 | 7.5 | 63223E3 | 7.5 | - | - | - | - |
| 10 | 100 | 5 x 11 | 145 | 10 | 0.20 | MF2 | 54101E3 | 2.0 | - | - | 34101E3 | 5.0 | 74101E3 | 2.5 |
| | 220 | 5 x 11 | 160 | 22 | 0.20 | MF2 | 54221E3 | 2.0 | - | - | 34221E3 | 5.0 | 74221E3 | 2.5 |
| | 330 | 6.3 x 11 | 290 | 33 | 0.20 | MF2 | 54331E3 | 2.5 | - | - | 34331E3 | 5.0 | 74331E3 | 2.5 |
| | 470 | 6.3 x 11 | 350 | 47 | 0.20 | MF2 | 54471E3 | 2.5 | - | - | 34471E3 | 5.0 | 74471E3 | 2.5 |
| | 1000 | 10 x 12 | 650 | 100 | 0.20 | MF2 | 54102E3 | 5.0 | 64102E3 | 5.0 | 34102E3 | 5.0 | - | - |
| | 2200 | 10 x 20 | 1070 | 220 | 0.22 | MF3 | 54222E3 | 5.0 | 64222E3 | 5.0 | 34222E3 | 5.0 | - | - |
| | 3300 | 13 x 20 | 1420 | 330 | 0.24 | MF3 | 54332E3 | 5.0 | 64332E3 | 5.0 | 34332E3 | 5.0 | - | - |
| | 4700 | 13 x 25 | 1780 | 470 | 0.26 | MF3 | 54472E3 | 5.0 | 64472E3 | 5.0 | 34472E3 | 5.0 | - | - |
| | 6800 | 16 x 25 | 2220 | 680 | 0.30 | MF3 | 54682E3 | 7.5 | 64682E3 | 7.5 | 34682E3 | 7.5 | - | - |
| | 10 000 | 16 x 35 | 2760 | 1000 | 0.38 | MF3 | 54103E3 | 7.5 | 64103E3 | 7.5 | - | - | - | - |
| 16 | 100 | 5 x 11 | 160 | 16 | 0.16 | MF2 | 55101E3 | 2.0 | - | - | 35101E3 | 5.0 | 75101E3 | 2.5 |
| | 220 | 6.3 x 11 | 260 | 35 | 0.16 | MF2 | 55221E3 | 2.5 | - | - | 35221E3 | 5.0 | 75221E3 | 2.5 |
| | 330 | 8 x 11.5 | 370 | 53 | 0.16 | MF2 | 55331E3 | 3.5 | - | - | 35331E3 | 5.0 | 75331E3 | 3.5 |
| | 470 | 8 x 11.5 | 440 | 75 | 0.16 | MF2 | 55471E3 | 3.5 | - | - | 35471E3 | 5.0 | 75471E3 | 3.5 |
| | 1000 | 10 x 16 | 785 | 160 | 0.16 | MF2 | 55102E3 | 5.0 | 65102E3 | 5.0 | 35102E3 | 5.0 | - | - |
| | 2200 | 13 x 20 | 1295 | 352 | 0.18 | MF3 | 55222E3 | 5.0 | 65222E3 | 5.0 | 35222E3 | 5.0 | - | - |
| | 3300 | 13 x 25 | 1655 | 528 | 0.20 | MF3 | 55332E3 | 5.0 | 65332E3 | 5.0 | 35332E3 | 5.0 | - | - |
| | 4700 | 16 x 25 | 2090 | 752 | 0.22 | MF3 | 55472E3 | 7.5 | 65472E3 | 7.5 | 35472E3 | 7.5 | - | - |
| | 6800 | 16 x 31 | 2520 | 1088 | 0.26 | MF3 | 55682E3 | 7.5 | 65682E3 | 7.5 | 35682E3 | 7.5 | - | - |
| | 10 000 | 18 x 35 | 2920 | 1600 | 0.34 | MF3 | 55103E3 | 7.5 | 65103E3 | 7.5 | - | - | - | - |



| ELECTRICAL DATA AND ORDERING INFORMATION | | | | | | | | | | | | | | |
|--|----------------------------------|---|---|----------------------------------|-----------------|-------------------|-----------------------------|-----------|------------|-----------|----------------|-----------|-------------|-----------|
| U _R (V) | C _R 100 Hz (μF) | NOMINAL CASE SIZE Ø D x L (mm) | I _R 100 Hz 85 °C (mA) | I _{L2} 2 min (μA) | tan δ 100 Hz | FREQ. CODE (1) | ORDERING CODE MAL2038 | | | | | | | |
| | | | | | | | BULK PACKAGING | | | | TAPED AMMOPACK | | | |
| | | | | | | | LONG LEADS | | CUT LEADS | | FORM TFA | F (mm) | FORM TNA | F (mm) |
| | | | | | | | FORM CA | F (mm) | FORM CB | F (mm) | | | | |
| 25 | 100 | 6.3 x 11 | 190 | 25 | 0.14 | MF2 | 56101E3 | 2.5 | - | - | 36101E3 | 5.0 | 76101E3 | 2.5 |
| | 220 | 8 x 11.5 | 320 | 55 | 0.14 | MF2 | 56221E3 | 3.5 | - | - | 36221E3 | 5.0 | 76221E3 | 3.5 |
| | 330 | 8 x 11.5 | 440 | 83 | 0.14 | MF2 | 56331E3 | 3.5 | - | - | 36331E3 | 5.0 | 76331E3 | 3.5 |
| | 470 | 10 x 12 | 545 | 118 | 0.14 | MF2 | 56471E3 | 5.0 | 66471E3 | 5.0 | 36471E3 | 5.0 | - | - |
| | 1000 | 10 x 20 | 955 | 250 | 0.14 | MF2 | 56102E3 | 5.0 | 66102E3 | 5.0 | 36102E3 | 5.0 | - | - |
| | 2200 | 13 x 25 | 1540 | 550 | 0.16 | MF3 | 56222E3 | 5.0 | 66222E3 | 5.0 | 36222E3 | 5.0 | - | - |
| | 3300 | 16 x 25 | 1975 | 825 | 0.18 | MF3 | 56332E3 | 7.5 | 66332E3 | 7.5 | 36332E3 | 7.5 | - | - |
| | 4700 | 16 x 31 | 2420 | 1175 | 0.20 | MF3 | 56472E3 | 7.5 | 66472E3 | 7.5 | 36472E3 | 7.5 | - | - |
| | 6800 | 18 x 35 | 2880 | 1700 | 0.24 | MF3 | 56682E3 | 7.5 | 66682E3 | 7.5 | - | - | - | - |
| 35 | 47 | 5 x 11 | 130 | 17 | 0.12 | MF1 | 50479E3 | 2.0 | - | - | 30479E3 | 5.0 | 70479E3 | 2.5 |
| | 100 | 6.3 x 11 | 210 | 35 | 0.12 | MF2 | 50101E3 | 2.5 | - | - | 30101E3 | 5.0 | 70101E3 | 2.5 |
| | 220 | 8 x 11.5 | 385 | 77 | 0.12 | MF2 | 50221E3 | 3.5 | - | - | 30221E3 | 5.0 | 70221E3 | 3.5 |
| | 330 | 10 x 12 | 490 | 116 | 0.12 | MF2 | 50331E3 | 5.0 | 60331E3 | 5.0 | 30331E3 | 5.0 | - | - |
| | 470 | 10 x 16 | 740 | 165 | 0.12 | MF2 | 50471E3 | 5.0 | 60471E3 | 5.0 | 30471E3 | 5.0 | - | - |
| | 1000 | 13 x 20 | 1145 | 350 | 0.12 | MF2 | 50102E3 | 5.0 | 60102E3 | 5.0 | 30102E3 | 5.0 | - | - |
| | 2200 | 16 x 25 | 1785 | 770 | 0.14 | MF3 | 50222E3 | 7.5 | 60222E3 | 7.5 | 30222E3 | 7.5 | - | - |
| | 3300 | 16 x 35 | 2275 | 1155 | 0.16 | MF3 | 50332E3 | 7.5 | 60332E3 | 7.5 | - | - | - | - |
| | 4700 | 18 x 35 | 2700 | 1645 | 0.18 | MF3 | 50472E3 | 7.5 | 60472E3 | 7.5 | - | - | - | - |
| 50 | 22 | 5 x 11 | 95 | 11 | 0.10 | MF1 | 51229E3 | 2.0 | - | - | 31229E3 | 5.0 | 71229E3 | 2.5 |
| | 33 | 5 x 11 | 125 | 17 | 0.10 | MF1 | 51339E3 | 2.0 | - | - | 31339E3 | 5.0 | 71339E3 | 2.5 |
| | 47 | 6.3 x 11 | 165 | 24 | 0.10 | MF1 | 51479E3 | 2.5 | - | - | 31479E3 | 5.0 | 71479E3 | 2.5 |
| | 100 | 8 x 11.5 | 260 | 50 | 0.10 | MF2 | 51101E3 | 3.5 | - | - | 31101E3 | 5.0 | 71101E3 | 3.5 |
| | 220 | 10 x 12 | 455 | 110 | 0.10 | MF2 | 51221E3 | 5.0 | 61221E3 | 5.0 | 31221E3 | 5.0 | - | - |
| | 330 | 10 x 16 | 585 | 165 | 0.10 | MF2 | 51331E3 | 5.0 | 61331E3 | 5.0 | 31331E3 | 5.0 | - | - |
| | 470 | 10 x 20 | 755 | 235 | 0.10 | MF2 | 51471E3 | 5.0 | 61471E3 | 5.0 | 31471E3 | 5.0 | - | - |
| | 1000 | 13 x 25 | 1340 | 500 | 0.10 | MF2 | 51102E3 | 5.0 | 61102E3 | 5.0 | 31102E3 | 5.0 | - | - |
| | 2200 | 16 x 31 | 1885 | 1100 | 0.12 | MF3 | 51222E3 | 7.5 | 61222E3 | 7.5 | 31222E3 | 7.5 | - | - |
| 3300 | 18 x 35 | 2500 | 1650 | 0.14 | MF3 | 51332E3 | 7.5 | 61332E3 | 7.5 | - | - | - | - | |
| 63 | 2.2 | 5 x 11 | 28 | 3.0 | 0.09 | MF1 | 58228E3 | 2.0 | - | - | 38228E3 | 5.0 | 78228E3 | 2.5 |
| | 3.3 | 5 x 11 | 34 | 3.0 | 0.09 | MF1 | 58338E3 | 2.0 | - | - | 38338E3 | 5.0 | 78338E3 | 2.5 |
| | 4.7 | 5 x 11 | 45 | 3.0 | 0.09 | MF1 | 58478E3 | 2.0 | - | - | 38478E3 | 5.0 | 78478E3 | 2.5 |
| | 10 | 5 x 11 | 70 | 6.3 | 0.09 | MF1 | 58109E3 | 2.0 | - | - | 38109E3 | 5.0 | 78109E3 | 2.5 |
| | 22 | 5 x 11 | 105 | 14 | 0.09 | MF1 | 58229E3 | 2.0 | - | - | 38229E3 | 5.0 | 78229E3 | 2.5 |
| | 33 | 6.3 x 11 | 140 | 21 | 0.09 | MF1 | 58339E3 | 2.5 | - | - | 38339E3 | 5.0 | 78339E3 | 2.5 |
| | 47 | 6.3 x 11 | 170 | 30 | 0.09 | MF1 | 58479E3 | 2.5 | - | - | 38479E3 | 5.0 | 78479E3 | 2.5 |
| | 100 | 10 x 12 | 320 | 63 | 0.09 | MF2 | 58101E3 | 5.0 | 68101E3 | 5.0 | 38101E3 | 5.0 | - | - |
| | 220 | 10 x 16 | 490 | 139 | 0.09 | MF2 | 58221E3 | 5.0 | 68221E3 | 5.0 | 38221E3 | 5.0 | - | - |
| | 330 | 10 x 20 | 710 | 208 | 0.09 | MF2 | 58331E3 | 5.0 | 68331E3 | 5.0 | 38331E3 | 5.0 | - | - |
| | 470 | 13 x 20 | 900 | 296 | 0.09 | MF2 | 58471E3 | 5.0 | 68471E3 | 5.0 | 38471E3 | 5.0 | - | - |
| | 1000 | 16 x 25 | 1560 | 630 | 0.09 | MF2 | 58102E3 | 7.5 | 68102E3 | 7.5 | 38102E3 | 7.5 | - | - |
| 2200 | 18 x 35 | 1950 | 1386 | 0.11 | MF3 | 58222E3 | 7.5 | 68222E3 | 7.5 | - | - | - | - | |



| ELECTRICAL DATA AND ORDERING INFORMATION | | | | | | | | | | | | | | |
|--|----------------------------------|---|---|----------------------------------|-----------------|------------------------------|-----------------------------|-----------|------------|-----------|----------------|-----------|-------------|-----------|
| U _R (V) | C _R 100 Hz (μF) | NOMINAL CASE SIZE Ø D x L (mm) | I _R 100 Hz 85 °C (mA) | I _{L2} 2 min (μA) | tan δ 100 Hz | FREQ. CODE ⁽¹⁾ | ORDERING CODE MAL2038 | | | | | | | |
| | | | | | | | BULK PACKAGING | | | | TAPED AMMOPACK | | | |
| | | | | | | | LONG LEADS | | CUT LEADS | | | | | |
| | | | | | | | FORM CA | F (mm) | FORM CB | F (mm) | FORM TFA | F (mm) | FORM TNA | F (mm) |
| 100 | 2.2 | 5 x 11 | 33 | 3.0 | 0.08 | MF1 | 59228E3 | 2.0 | - | - | 39228E3 | 5.0 | 79228E3 | 2.5 |
| | 3.3 | 5 x 11 | 40 | 3.3 | 0.08 | MF1 | 59338E3 | 2.0 | - | - | 39338E3 | 5.0 | 79338E3 | 2.5 |
| | 4.7 | 5 x 11 | 48 | 4.7 | 0.08 | MF1 | 59478E3 | 2.0 | - | - | 39478E3 | 5.0 | 79478E3 | 2.5 |
| | 10 | 6.3 x 11 | 80 | 10 | 0.08 | MF1 | 59109E3 | 2.5 | - | - | 39109E3 | 5.0 | 79109E3 | 2.5 |
| | 22 | 6.3 x 11 | 115 | 22 | 0.08 | MF1 | 59229E3 | 2.5 | - | - | 39229E3 | 5.0 | 79229E3 | 2.5 |
| | 33 | 8 x 11.5 | 145 | 33 | 0.08 | MF1 | 59339E3 | 3.5 | - | - | 39339E3 | 5.0 | 79339E3 | 3.5 |
| | 47 | 10 x 12 | 235 | 47 | 0.08 | MF1 | 59479E3 | 5.0 | 69479E3 | 5.0 | 39479E3 | 5.0 | - | - |
| | 100 | 10 x 20 | 370 | 100 | 0.08 | MF2 | 59101E3 | 5.0 | 69101E3 | 5.0 | 39101E3 | 5.0 | - | - |
| | 220 | 13 x 25 | 675 | 220 | 0.08 | MF2 | 59221E3 | 5.0 | 69221E3 | 5.0 | 39221E3 | 5.0 | - | - |
| | 330 | 13 x 25 | 825 | 330 | 0.08 | MF2 | 59331E3 | 5.0 | 69331E3 | 5.0 | 39331E3 | 5.0 | - | - |
| | 470 | 16 x 25 | 1070 | 470 | 0.08 | MF2 | 59471E3 | 7.5 | 69471E3 | 7.5 | 39471E3 | 7.5 | - | - |
| | 1000 | 18 x 40 | 2410 | 1000 | 0.08 | MF2 | 59102E3 | 7.5 | 69102E3 | 7.5 | - | - | - | - |

Note

(1) Determines the applicable row in the table “Multiplier of Ripple Current (I_R) as a Function of Frequency”

| ADDITIONAL ELECTRICAL DATA | | |
|------------------------------------|---|---|
| PARAMETER | CONDITIONS | VALUE |
| Voltage | | |
| Surge voltage | | U _S ≤ 1.15 x U _R |
| Reverse voltage | | U _{REV} ≤ 1 V |
| Current | | |
| Leakage current | After 2 min at U _R | I _{L2} ≤ 0.01 C _R x U _R or 3 μA, whichever is greater |
| | After 5 min at U _R | I _{L5} ≤ 0.002 C _R x U _R + 3 μA |
| Inductance | | |
| Equivalent series inductance (ESL) | Case Ø D ≤ 8 mm | Typ. 13 nH |
| | Case Ø D = 10 mm | Typ. 16 nH |
| | Case Ø D ≥ 12.5 mm | Typ. 18 nH |
| Resistance | | |
| Equivalent series resistance (ESR) | Calculated from tan δ _{max} and C _R (see Table 2) | ESR = tan δ/2 π f C _R |

CAPACITANCE (C)




Fig. 6 - Typical multiplier of capacitance as a function of ambient temperature




Fig. 7 - Typical multiplier of capacitance as a function of frequency




RIPPLE CURRENT AND USEFUL LIFE

Table 3

| ENDURANCE TEST DURATION AND USEFUL LIFE | | |
|---|------------------------------|--------------------------------|
| NOMINAL CASE SIZE Ø D x L (mm) | ENDURANCE AT 85 °C (h) | USEFUL LIFE AT 85 °C (h) |
| 5 x 11 | 2000 | 2500 |
| 6.3 x 11 | 2000 | 2500 |
| 8 x 11.5 | 2000 | 2500 |
| 10 x 12 | 3000 | 3500 |
| 10 x 16 | 3000 | 3500 |
| 10 x 20 | 3000 | 3500 |
| 13 x 20 | 3000 | 3500 |
| 13 x 25 | 3000 | 3500 |
| 16 x 25 | 3000 | 3500 |
| 16 x 31 | 3000 | 3500 |
| 16 x 35 | 3000 | 3500 |
| 18 x 35 | 3000 | 3500 |
| 18 x 40 | 3000 | 3500 |

Note

- Multiplier of useful life code: CCC205



I_A = Actual ripple current at 100 Hz
 I_R = Rated ripple current at 100 Hz, 85 °C
 Useful life at 85 °C and I_R applied:
 Case $\varnothing D \leq 8$ mm: 2500 h
 Case $\varnothing D \geq 10$ mm: 3500 h

Fig. 8 - Multiplier of useful life as a function of ambient temperature and ripple current load

Table 4

| MULTIPLIER OF RIPPLE CURRENT (I_R) AS A FUNCTION OF FREQUENCY | | | | | |
|---|------------------------------------|------------|------------|-------------|-----------------|
| FREQ. CODE | FREQUENCY (Hz) | | | | |
| | 50 | 100 | 500 | 1000 | ≥ 10 000 |
| | I_R MULTIPLIER | | | | |
| MF1 | 0.70 | 1.00 | 1.30 | 1.40 | 1.50 |
| MF2 | 0.75 | 1.00 | 1.20 | 1.30 | 1.35 |
| MF3 | 0.80 | 1.00 | 1.10 | 1.12 | 1.15 |

Table 5

| TEST PROCEDURES AND REQUIREMENTS | | | |
|---|--|--|--|
| TEST | | PROCEDURE (quick reference) | REQUIREMENTS |
| NAME OF TEST | REFERENCE | | |
| Endurance | IEC 60384-4 / EN 130300 subclause 4.13 | $T_{amb} = 85\text{ °C}$; U_R applied; Case $\varnothing \leq 8\text{ mm}$: 2000 h Case $\varnothing \geq 10\text{ mm}$: 3000 h | $\Delta C/C: \pm 20\%$ $\tan \delta \leq 2 \times \text{spec. limit}$ $I_{L5} \leq \text{spec. limit}$ |
| Useful life | CECC 30301 subclause 1.8.1 | $T_{amb} = 85\text{ °C}$; U_R and I_R applied; Case $\varnothing \leq 8\text{ mm}$: 2500 h Case $\varnothing \geq 10\text{ mm}$: 3500 h | $\Delta C/C: \pm 50\%$ $\tan \delta \leq 3 \times \text{spec. limit}$ $I_{L5} \leq \text{spec. limit}$ no short or open circuit total failure percentage: $\leq 1\%$ |
| Shelf life (storage at high temperature) | IEC 60384-4 / EN 130300 subclause 4.17 | $T_{amb} = 85\text{ °C}$; no voltage applied; 1000 h after test: U_R to be applied for 30 min, 24 h to 48 h before measurement | $\Delta C/C: \pm 20\%$ $\tan \delta \leq 2 \times \text{spec. limit}$ $I_{L5} \leq 3 \times \text{spec. limit}$ |
| Surge | IEC 60384-4 / EN 130300 subclause 4.14 | From source of $1.15 \times U_R$; $RC = 0.1\text{ s} \pm 0.05\text{ s}$; 1000 cycles of 30 s on, 330 s off, at 85 °C | $\Delta C/C: \pm 25\%$ $\tan \delta \leq 1.5 \times \text{spec. limit}$ $I_{L5} \leq \text{spec. limit}$ |

Statements about product lifetime are based on calculations and internal testing. They should only be interpreted as estimations. Also due to external factors, the lifetime in the field application may deviate from the calculated lifetime. In general, nothing stated herein shall be construed as a guarantee of durability.



Disclaimer

ALL PRODUCT, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE TO IMPROVE RELIABILITY, FUNCTION OR DESIGN OR OTHERWISE.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product.

Vishay makes no warranty, representation or guarantee regarding the suitability of the products for any particular purpose or the continuing production of any product. To the maximum extent permitted by applicable law, Vishay disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Statements regarding the suitability of products for certain types of applications are based on Vishay's knowledge of typical requirements that are often placed on Vishay products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. Parameters provided in datasheets and / or specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein.

Except as expressly indicated in writing, Vishay products are not designed for use in medical, life-saving, or life-sustaining applications or for any other application in which the failure of the Vishay product could result in personal injury or death. Customers using or selling Vishay products not expressly indicated for use in such applications do so at their own risk. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay. Product names and markings noted herein may be trademarks of their respective owners.