


AC Capacitors, Suppression Capacitors, Class Y2 AC 250 V (MKT)



Dimensions in mm

LEAD LENGTH x (mm)	ORDERING CODE ⁽²⁾
4 ⁻¹	F1710-...-1004
6 ⁻¹	F1710-...-1000
15 ⁻¹	F1710-...-1015
30 ⁺⁵	F1710-...-1030

FEATURES

Compliant to RoHS directive 2002/95/EC

TERMINALS

Radial tinned copper wire

RATED VOLTAGE

AC 250 V, 50/60 Hz

COATING

Plastic case, epoxy resin sealed, flame retardant, UL-class 94V-0

TECHNICAL DATA

See page 71 (Document Number 26525)


RoHS
COMPLIANT

CAPACITANCE	TOL. (%)	PITCH (mm)	BOX NO.	DIMENSIONS W x H x L (mm) (+ 0.2 mm/- 0.4 mm)	WEIGHT LEAD LENGTH ≤ 6 ⁻¹ mm (g)	QUANTITY PACKAGE LEAD LENGTH ≤ 6 ⁻¹ mm (pcs)	ORDERING CODE ⁽²⁾
1000 pFY2	± 20	15	05	5.3 x 10.3 x 17.8	1.4	750	F1710-210-10 ..
1200 pFY2	± 20	15	05	5.3 x 10.3 x 17.8	1.4	750	F1710-212-10 ..
1500 pFY2	± 20	15	05	5.3 x 10.3 x 17.8	1.4	750	F1710-215-10 ..
1800 pFY2	± 20	15	05	5.3 x 10.3 x 17.8	1.4	750	F1710-218-10 ..
2200 pFY2	± 20	15	05	5.3 x 10.3 x 17.8	1.4	750	F1710-222-10 ..
2700 pFY2	± 20	15	05	5.3 x 10.3 x 17.8	1.4	750	F1710-227-10 ..
3300 pFY2	± 20	15	05	5.3 x 10.3 x 17.8	1.4	750	F1710-233-10 ..
3900 pFY2	± 20	15	05	5.3 x 10.3 x 17.8	1.4	750	F1710-239-10 ..
4700 pFY2	± 20	15	05	5.3 x 10.3 x 17.8	1.4	750	F1710-247-10 ..
5600 pFY2	± 20	15	05	5.3 x 10.3 x 17.8	1.4	750	F1710-256-10 ..
6800 pFY2	± 20	15	05	5.3 x 10.3 x 17.8	1.4	750	F1710-268-10 ..
8200 pFY2	± 20	15	06	6.3 x 12.3 x 17.8	2.0	500	F1710-282-10 ..
0.01 μFY2	± 20	15	06	6.3 x 12.3 x 17.8	2.0	500	F1710-310-10 ..
0.012 μFY2	± 20	15	07	7.3 x 13.3 x 17.8	2.4	450	F1710-312-10 ..
0.015 μFY2	± 20	15	07	7.3 x 13.3 x 17.8	2.4	450	F1710-315-10 ..
0.018 μFY2	± 20	15	28	8.3 x 17.3 x 17.8	3.4	300	F1710-318-10 ..
0.022 μFY2	± 20	15	28	8.3 x 17.3 x 17.8	3.4	300	F1710-322-10 ..
0.027 μFY2	± 20	22.5	09	6.3 x 14.3 x 26.3	3.5	260	F1710-327-10 ..
0.033 μFY2	± 20	22.5	09	6.3 x 14.3 x 26.3	3.5	260	F1710-333-10 ..
0.039 μFY2	± 20	22.5	11	7.3 x 15.3 x 26.3	3.9	235	F1710-339-10 ..
0.047 μFY2	± 20	22.5	12	8.3 x 16.3 x 26.3	4.8	200	F1710-347-10 ..
0.056 μFY2	± 20	22.5	13	10.3 x 18.3 x 26.3	6.6	170	F1710-356-10 ..
0.068 μFY2	± 20	22.5	13	10.3 x 18.3 x 26.3	6.6	170	F1710-368-10 ..
0.082 μFY2	± 20	27.5	14	11.0 x 20.3 x 31.3	9.4	125	F1710-382-10 ..
0.1 μFY2	± 20	27.5	14	11.0 x 20.3 x 31.3	9.4	125	F1710-410-10 ..

Notes

- Preferred values in bold print.

⁽¹⁾ Further information about packaging quantities with different lead length and/or taped versions



See page 16 (Document No 27608 Packaging Quantities). Use Box No. as reference

⁽²⁾ These capacitors can be delivered on continuous tape and reel see page 14/15 (Document Number 27622)

The ordering code is then: F1710-...-1900 at H = 16 mm, F1710-...-1901 at H = 18.5 mm.

APPROVALS

COUNTRY	SPECIFICATION	ELECTRICAL VALUES	APPROVAL REFERENCE	APPROVAL MARK
U.S.A. (for AC 250 V)	UL 1283 UL 1414	0.01 to 0.1 μ FX 0.01 to 0.1 μ FX	E 76297 E 100682	
Canada (for AC 250 V)	C 22.2 No. 1-M 1994	1000 pFY2 to 0.1 μ FY2	2167188	
CB TEST-CERTIFICATE (for AC 275 V)		1000 pFY2 to 0.1 μ FY2	DE 1-8790	
Germany	EN 132 400; 1999 IEC 60384-14, 2nd edition, 1995	1000 pFY2 to 0.1 μ FX2	94613	
This approval mark together with the CB-Certificate replace all national approval marks of the following countries (they have already signed the CB-Agreement):				
Austria	Belgium	Denmark	Finland	Sweden
France	Germany	Ireland	Italy	Switzerland
Netherlands	Israel	Portugal	Spain	Great Britain
Japan	Norway	China	Poland	Czech. Republic
Singapore	Rep. of Korea	Hungary	Iceland	Slovenia



Impedance (Z) as a function of frequency (f) at $T_a = 20\text{ }^\circ\text{C}$ (average)
Measurement with lead length 6 mm.



Disclaimer

All product specifications and data are subject to change without notice.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained herein or in any other disclosure relating to any product.

Vishay disclaims any and all liability arising out of the use or application of any product described herein or of any information provided herein to the maximum extent permitted by law. The product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein, which apply to these products.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay.

The products shown herein are not designed for use in medical, life-saving, or life-sustaining applications unless otherwise expressly indicated. Customers using or selling Vishay products not expressly indicated for use in such applications do so entirely at their own risk and agree to fully indemnify Vishay for any damages arising or resulting from such use or sale. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

Product names and markings noted herein may be trademarks of their respective owners.