


www.vishay.com

Vishay Beyschlag

## Sample Kit Precision Wide Terminal Thin Film Chip Resistors MCW 0406-25 0.1 % AT



**FEATURES** 






- Resistance range down to 1R
- Superior temperature cycling robustness
- Operating temperature up to 155 °C
- AEC-Q200 qualified (pending)
- Material categorization: for definitions of compliance please see <a href="https://www.vishay.com/doc?99912"><u>www.vishay.com/doc?99912</u></a>

Files contain lengths of cardboard tape, each holding 20 resistors. The kit contains every fourth value of the E 96-series. Parts are sorted in the ascending order of its resistance value and appropriately marked.

SPECIFICATIONS	
Laboratory kit	LCW AT 96/4
Resistor type	MCW 0406-25 0.1 % AT
Temperature coefficient	± 25 ppm/K
Tolerance	± 0.1 %
Resistance range/E-series	47 $\Omega$ to 100 k $\Omega$ /every 4 <sup>th</sup> value of E 96 <sup>(1)</sup>
Number of resistance values	80
Resistors per value/total	20/1600
Number of pages/files	8/1

## Notes

- The products are specified by the underlying standard product's datasheet "Precision Wide Terminal Thin Film Chip Resistor" in its most current edition at <a href="https://www.vishay.com/doc?28847"><u>www.vishay.com/doc?28847</u></a>
- (1) Supplemented by 47R



## Note

The product can be ordered using either the PART NUMBER or the PRODUCT DESCRIPTION