Vishay Beyschlag

Sample Kit High Pulse Load Carbon Film MELF Resistors CMB 0207



www.vishay.com

Files contain lengths of blister tape, each holding 20 resistors. The kit contains every value of the E 12-series. Parts are sorted in the ascending order of their resistance value and are appropriately marked.

FEATURES

- Approved to the safety requirements of IEC 60065, 14.2.a (= VDE 0860, 14.1.a) VDE-REG.-Nr. B583
- AEC-Q200 qualified
- Special carbon film technology
- Up to 3 kW single pulse capability
- ESD capability: 16 kV, human body model
- Intrinsic sulfur resistance
- Surge voltage capability up to 10 kV 1.2/50 µs pulse
- Material categorization: for definitions of compliance please see <u>www.vishay.com/doc?99912</u>

SPECIFICATIONS			
Laboratory kit	LMC 12/1		
Description	CMB 0207		
Temperature coefficient	See TCR graph ⁽¹⁾		
Tolerance	± 5 %	± 2 %	
Resistance range / E-series	2.2 Ω to 15 Ω / every value of E 12	18 Ω to 1.5 M Ω / every value of E 12	
Number of resistance values	11	59	
Resistors per value / total	20/220	20/1180	
Number of pages / files	7/1		

Notes

 The products are specified by the underlying standard product's datasheet "High Pulse Load Carbon Film MELF Resistors" in its most current edition at <u>www.vishay.com/doc?28755</u>

⁽¹⁾ Specified according to the TCR graph included in the underlying standard product's datasheet

PART NUMBER AND PRODUCT DESCRIPTION		
Part number	LMC121CMB02070JG00	
Product description	LMC 12 1 CMB 0207 2 % 5 %	

Note

• The product can be ordered using either the PART NUMBER or the PRODUCT DESCRIPTION



COMPLIANT HALOGEN FREE GREEN (5-2008)