




## Thick Film Chip Resistor Array



CRA06P thick film resistor array is constructed on a high grade ceramic body with concave terminations. A small package enables the design of high density circuits. The single component reduces board space, component counts and assembly costs.

### FEATURES

- Concave terminal array with square corners
- 4 and 8 terminal package with isolated resistors
- Wide ohmic range: 10R to 1M $\Omega$
- AEC-Q200 qualified
- Material categorization: for definitions of compliance please see [www.vishay.com/doc?99912](http://www.vishay.com/doc?99912)



RoHS  
COMPLIANT

STANDARD ELECTRICAL SPECIFICATIONS							
MODEL	CIRCUIT	POWER RATING $P_{70^\circ\text{C}}$ W	LIMITING ELEMENT VOLTAGE MAX. $V_{\Xi}$	TEMPERATURE COEFFICIENT $\pm$ ppm/K	TOLERANCE $\pm$ %	RESISTANCE RANGE $\Omega$	E-SERIES
CRA06P	03	0.063	50	100	1	10 to 1M	24 + 96
				200	2; 5		24
Zero-Ohm-Resistor: $R_{\text{max.}} = 50 \text{ m}\Omega$ , $I_{\text{max.}} = 1 \text{ A}$							

TECHNICAL SPECIFICATIONS		
PARAMETER	UNIT	CRA06P 03 CIRCUIT
Rated dissipation at 70 °C <sup>(2)</sup>	W per element	0.063
Limiting element voltage <sup>(1)</sup>	$V_{\Xi}$	50
Insulation voltage (1 min)	$V_{\text{DC/AC peak}}$	100
Category temperature range	°C	-55 to +155
Insulation resistance	$\Omega$	$> 10^9$

### Notes

- (1) Rated voltage:  $\sqrt{P \times R}$   
 (2) The power dissipation on the resistor generates a temperature rise against the local ambient, depending on the heat flow support of the printed-circuit board (thermal resistance). The rated dissipation applies only if the permitted film temperature of 155 °C is not exceeded

PART NUMBER AND PRODUCT DESCRIPTION																	
Part Number: CRA06P08347K0JTA																	
C	R	A	0	6	P	0	8	3	4	7	K	0	J	T	A		
MODEL	TERMINAL STYLE	PIN	CIRCUIT	VALUE	TOLERANCE	PACKAGING <sup>(2)</sup>	SPECIAL										
CRA06	P	04 08	3 = 03	R = decimal K = thousand M = million 0000 = 0 $\Omega$ jumper	F = $\pm 1\%$ G = $\pm 2\%$ J = $\pm 5\%$ Z = 0 $\Omega$ jumper	TA TC	Up to 2 digits										
Product Description: CRA06P 08 03 473 J RT1 e3																	
CRA06P	08	03	473	J	RT1	e3											
MODEL	TERMINAL COUNT	CIRCUIT TYPE	RESISTANCE VALUE	TOLERANCE	PACKAGING <sup>(4)</sup>	LEAD (Pb)-FREE											
CRA06P	04 08	03	473 = 47 k $\Omega$ 4702 = 47 k $\Omega$ 10R0 = 10 $\Omega$ 100 = 10 $\Omega$ 000 = 0 $\Omega$ jumper	F = $\pm 1\%$ G = $\pm 2\%$ J = $\pm 5\%$ Z = 0 $\Omega$ jumper	RT1 RT6	e3 = pure tin termination finish											
								First two digits (3 for 1 %) are significant. Last digit is the multiplier.									

### Notes


- (1) Preferred way for ordering products is by use of the PART NUMBER  
 (2) Please refer to the table PACKAGING, see next page




PACKAGING						
MODEL	TAPE WIDTH	DIAMETER	PITCH	PIECES/REEL	PACKAGING CODE	
					PAPER TAPE	
					PART NUMBER	PRODUCT DESCRIPTION
CRA06P	8 mm	180 mm/7"	4 mm	5000	TA	RT1
		330 mm/13"	4 mm	20 000	TC	RT6

**CIRCUIT**


03 CIRCUIT




**DERATING**



**DIMENSIONS**



PIN NO#	DIMENSIONS in millimeters						
	L	A	B	C	P	T	W
4	1.60	0.30	0.40	0.40	0.80	0.60	1.60
8	3.20	0.30	0.40	0.40	0.80	0.60	1.60
ToI.	± 0.20	± 0.20	± 0.15	± 0.20	-	± 0.10	± 0.15



SOLDER PAD DIMENSIONS in millimeters					
	c	w	p	a	b
WAVE	0.8	2.6	0.8	0.4	0.9



TEST PROCEDURES AND REQUIREMENTS			
EN 60115-1			
TEST (clause)	CONDITIONS OF TEST	REQUIREMENTS PERMISSIBLE CHANGE ( $\Delta R/R$ ) <sup>(1)</sup>	
		STABILITY CLASS 1 OR BETTER	STABILITY CLASS 2 OR BETTER
	Stability for product types:		
	<b>CRA06P</b>	10 $\Omega$ to 1 M $\Omega$	10 $\Omega$ to 1 M $\Omega$
Resistance (4.5)	-	$\pm 1\%$	$\pm 2\%$ ; $\pm 5\%$
Temperature coefficient (4.8.4.2)	(20 / -55 / 20) °C and (20 / 125 / 20) °C	$\pm 100$ ppm/K	$\pm 200$ ppm/K
Overload (4.13)	$U = 2.5 \times (P_{70} \times R)^{1/2}$ $\leq 2 \times U_{max.}$ ; 0.5 s	$\pm (0.25\% R + 0.05 \Omega)$	$\pm (0.5\% R + 0.05 \Omega)$
Solderability (4.17.5) <sup>(2)</sup>	Aging 4 h at 155 °C, dryheat Solder bath method; 235 °C; 2 s Visual examination	Good tinning ( $\geq 95\%$ covered) no visible damage	
Resistance to soldering heat (4.18.2)	Solder bath method; (260 $\pm$ 5) °C; (10 $\pm$ 1) s	$\pm (0.25\% R + 0.05 \Omega)$	$\pm (0.5\% R + 0.05 \Omega)$
Rapid change of temperature (4.19)	30 min at LCT = -55 °C; 30 min at UCT = 125 °C; 5 cycles	$\pm (0.25\% R + 0.05 \Omega)$	$\pm (0.5\% R + 0.05 \Omega)$
Damp heat, steady state (4.24)	(40 $\pm$ 2) °C; 56 days; (93 $\pm$ 3) % RH	$\pm (1\% R + 0.05 \Omega)$	$\pm (2\% R + 0.1 \Omega)$
Climatic sequence (4.23)	16 h at UCT = 125 °C; 1 cycle at 55 °C; 2 h at LCT = -55 °C; 1 h/1 kPa at 15 °C to 35 °C; 5 cycles at 55 °C $U = (P_{70} \times R)^{1/2}$ $U = U_{max.}$ ; whichever is less severe	$\pm (1\% R + 0.05 \Omega)$	$\pm (2\% R + 0.1 \Omega)$
Endurance at 70 °C (4.25.1)	$U = (P_{70} \times R)^{1/2}$ $U = U_{max.}$ ; whichever is less severe 1.5 h "ON"; 0.5 h "OFF"; 70 °C; 1000 h	$\pm (1\% R + 0.05 \Omega)$	$\pm (2\% R + 0.1 \Omega)$
Extended endurance (4.25.1.8)	Duration extended to 8000 h	$\pm (2\% R + 0.1 \Omega)$	$\pm (4\% R + 0.1 \Omega)$
Endurance at upper category temperature (4.25.3)	UCT = 125 °C; 1000 h	$\pm (1\% R + 0.05 \Omega)$	$\pm (2\% R + 0.1 \Omega)$

**Notes**

(1) Figures are given for a single element

(2) Solderability is specified for 2 years after production or requalification. Permitted storage time is 20 years

APPLICABLE SPECIFICATIONS	
• EN 60115-1	Generic specification
• EN 140400	Sectional specification
• EN 140401-802	Detail specification
• IEC 60068-2-X	Variety of environmental test procedures
• EIA 481	Packaging of SMD components



## **Disclaimer**

ALL PRODUCT, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE TO IMPROVE RELIABILITY, FUNCTION OR DESIGN OR OTHERWISE.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product.

Vishay makes no warranty, representation or guarantee regarding the suitability of the products for any particular purpose or the continuing production of any product. To the maximum extent permitted by applicable law, Vishay disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Statements regarding the suitability of products for certain types of applications are based on Vishay's knowledge of typical requirements that are often placed on Vishay products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. Parameters provided in datasheets and / or specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein.

Except as expressly indicated in writing, Vishay products are not designed for use in medical, life-saving, or life-sustaining applications or for any other application in which the failure of the Vishay product could result in personal injury or death. Customers using or selling Vishay products not expressly indicated for use in such applications do so at their own risk. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay. Product names and markings noted herein may be trademarks of their respective owners.