


Wirewound/Metal Oxide Resistors, Commercial Power, Vertical Mount



FEATURES

- Space saving
- Direct mounting on printed circuit board
- High power to size ratio
- Special cement potting compound and ceramic case provide high thermal conductivity in a fireproof package



RoHS
COMPLIANT

STANDARD ELECTRICAL SPECIFICATIONS				
GLOBAL MODEL	POWER RATING $P_{40^\circ\text{C}}$ W	RESISTANCE RANGE Ω $\pm 5\%, \pm 10\%$	TECHNOLOGY	WEIGHT (typical) g
CPCC02	2	0.1 - 100	Wirewound	4.7
CPCF02	2	101 - 10K	Metal Oxide	4.7
CPCC03	3	0.1 - 100	Wirewound	5.5
CPCF03	3	101 - 50K	Metal Oxide	5.5
CPCC05	5	0.1 - 100	Wirewound	6.9
CPCF05	5	101 - 50K	Metal Oxide	6.9
CPCC07	7	0.1 - 100	Wirewound	9.2
CPCF07	7	101 - 50K	Metal Oxide	9.2
CPCC10	10	0.1 - 100	Wirewound	14.3

TECHNICAL SPECIFICATIONS		
PARAMETER	UNIT	CPCC AND CPCF HIGH VOLUME RESISTOR CHARACTERISTICS
Temperature Coefficient	ppm/°C	± 400
Short Time Overload	-	5 x rated power for 5 s
Maximum Working Voltage	V	$(P \times R)^{1/2}$
Operating Temperature Range	°C	- 65 to + 275 for wirewound, - 65 to + 225 for metal oxide
Terminal Strength	lb	10 minimum
Dielectric Withstanding Voltage	V_{AC}	1000

GLOBAL PART NUMBER INFORMATION																	
Global Part Numbering Example: CPCC0515R00JE66																	
C	P	C	C	0	5	1	5	R	0	0	J	E	6	6			
GLOBAL MODEL (See Standard Electrical Specifications Global Model column for options)			VALUE R = Decimal K = Thousand R1500 = 0.15 W 1K500 = 1500 W			TOLERANCE J = $\pm 5.0\%$ K = $\pm 10\%$			PACKAGING E66 = Lead (Pb)-free, bulk			SPECIAL (Dash Number) (up to 3 digits) From 1 - 999 as applicable					




CPCC, CPCF High Volume

Wirewound/Metal Oxide Resistors, Commercial Power,
Vertical Mount

Vishay Dale

DIMENSIONS in inches [millimeters]



GLOBAL MODEL	DIMENSIONS in inches [millimeters]				
	H ± 0.060 [1.5]	W ± 0.040 [1.0]	L ± 0.040 [1.0]	LD ± 0.002 [0.05]	CC + 0.08 - 0.04 [+ 2 - 1]
CPCC02	0.787 [20]	0.433 [11]	0.138 [3.5]	0.031 [0.8]	0.197 [5]
CPCF02	0.787 [20]	0.433 [11]	0.138 [3.5]	0.031 [0.8]	0.197 [5]
CPCC03	0.984 [25]	0.472 [12]	0.315 [8]	0.031 [0.8]	0.197 [5]
CPCF03	0.984 [25]	0.472 [12]	0.315 [8]	0.031 [0.8]	0.197 [5]
CPCC05	0.984 [25]	0.512 [13]	0.354 [9]	0.031 [0.8]	0.197 [5]
CPCF05	0.984 [25]	0.512 [13]	0.354 [9]	0.031 [0.8]	0.197 [5]
CPCC07	1.535 [39]	0.512 [13]	0.354 [9]	0.031 [0.8]	0.197 [5]
CPCF07	1.535 [39]	0.512 [13]	0.354 [9]	0.031 [0.8]	0.197 [5]
CPCC10	1.378 [35]	0.630 [16]	0.472 [12]	0.031 [0.8]	0.295 [7.5]

MATERIAL SPECIFICATIONS

Part Marking: DALE, model, wattage, value, tolerance, date code

CPCC: Element: Copper-nickel alloy or nickel-chrome alloy, depending on resistance value

Core: Alumina ceramic

Body: Steatite ceramic case with cement potting compound

End Caps: Tin plated steel

Terminals: Tinned copper


CPCF: Element: Nickel oxide

Core: Alumina ceramic

Body: Steatite ceramic case with inorganic potting compound

End Caps: Brass alloy

Terminals: Tinned copper



PERFORMANCE		
TEST	CONDITIONS OF TEST	CPCC, CPCF TEST LIMITS
Thermal Shock	- 55 °C to + 275 °C (+ 225 °C for Metal Oxide), 5 cycles, 30 min dwell time	± (5.0 % + 0.05 Ω) ΔR
Short Time Overload	5 x rated power for 5 s	± (4.0 % + 0.05 Ω) ΔR
Dielectric Withstanding Voltage	1000 V _{rms} for 1 min	± (2.0 % + 0.05 Ω) ΔR
Low Temperature Operation	- 65 °C, full rated working voltage for 45 min	± (3.0 % + 0.05 Ω) ΔR
Bias Humidity	75 °C, 90 % - 100 % RH, 240 h	± (5.0 % + 0.05 Ω) ΔR
Load Life	1000 h at rated power, + 25 °C, 1.5 h "ON", 0.5 h "OFF"	± (10.0 % + 0.05 Ω) ΔR
Terminal Strength	5 to 10 s 10 pound pull test	± (2.0 % + 0.05 Ω) ΔR
Resistance to Solder Heat	Terminal immersed 3.5 s in molten solder up to body	± (4.0 % + 0.05 Ω) ΔR



Disclaimer

All product specifications and data are subject to change without notice.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained herein or in any other disclosure relating to any product.

Vishay disclaims any and all liability arising out of the use or application of any product described herein or of any information provided herein to the maximum extent permitted by law. The product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein, which apply to these products.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay.

The products shown herein are not designed for use in medical, life-saving, or life-sustaining applications unless otherwise expressly indicated. Customers using or selling Vishay products not expressly indicated for use in such applications do so entirely at their own risk and agree to fully indemnify Vishay for any damages arising or resulting from such use or sale. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

Product names and markings noted herein may be trademarks of their respective owners.