



Thick Film Resistor Networks, Dual-In-Line Small Outline Molded Dip, 01, 03, 05 Schematics



FEATURES

- 0.110" [2.79 mm] maximum seated height
- Rugged, molded case construction
- 0.050" [1.27 mm] lead spacing
- Reduces total assembly costs
- Compatible with automatic surface mounting equipment
- Uniform performance characteristics
- Meets EIA PDP 100, SOGN-0003 outline dimensions
- Available in tube pack or tape and reel pack
- Lead (Pb)-free version is RoHS compliant



RoHS*
COMPLIANT

STANDARD ELECTRICAL SPECIFICATIONS

GLOBAL MODEL	SCHEMATIC	RESISTOR CIRCUIT W @ 70°C	PACKAGE POWER W @ 70°C	TOLERANCE ± %	RESISTANCE RANGE Ω	OPERATING VOLTAGE VDC	TEMPERATURE COEFFICIENT ppm/°C
SOGC16	01	0.1	1.6	2 (1, 5*)	10-1M0	50 max	100
	03	0.19	1.6	2 (1, 5*)	10-1M0	50 max	100
	05	0.1	1.6	2 (5*)	10-1M0	50 max	100
SOGC20	01	0.1	2.0	2 (1, 5*)	10-1M0	50 max	100
	03	0.19	2.0	2 (1, 5*)	10-1M0	50 max	100
	05	0.1	2.0	2 (5*)	10-1M0	50 max	100

* Tolerances in brackets available upon request.
• 100 milliohm maximum on zero ohm jumper

GLOBAL PART NUMBER INFORMATION

New Global Part Numbering: SOGC200310K0GDC (preferred part numbering format)

S O G C 2 0 0 3 1 0 K 0 G D C

GLOBAL MODEL	PIN COUNT	SCHEMATIC	RESISTANCE VALUE	TOLERANCE CODE	PACKAGING	SPECIAL
SOGC	16 20	01 = Bussed 03 = Isolated 00 = Special	R = Decimal K = Thousand M = Million 10R0 = 10 Ω 680K = 680 KΩ 1M00 = 1.0 MΩ	F = ± 1% G = ± 2% J = ± 5% S = Special Z = 0 Ω Jumper	EJ = Lead Free, Tube EA = Lead (Pb)-free, Tape & Reel DC = Tin/Lead, Tube RZ = Tin/Lead, Tape & Reel	Blank = Standard (Dash Number) (up to 3 digits) From 1-999 as applicable

Historical Part Number example: SOGC2003103G (will continue to be accepted)

SOGC 20 03 103 G D02
HISTORICAL MODEL PIN COUNT SCHEMATIC RESISTANCE VALUE TOLERANCE CODE PACKAGING

New Global Part Numbering: SOGC1605131AGRZ (preferred part numbering format)


S O G C 1 6 0 5 1 3 1 A G R Z

GLOBAL MODEL	PIN COUNT	SCHEMATIC	RESISTANCE VALUE	TOLERANCE CODE	PACKAGING	SPECIAL
SOGC	16 20	05 = Dual Terminator	3 digit Impedance code, followed by Alpha modifier (see Impedance Codes table)	F = ± 1% G = ± 2% J = ± 5%	EJ = Lead Free, Tube EA = Lead (Pb)-free, Tape & Reel DC = Tin/Lead, Tube RZ = Tin/Lead, Tape & Reel	Blank = Standard (Dash Number) (up to 3 digits) From 1-999 as applicable

Historical Part Number example: SOGC1605221331G (will continue to be accepted)

SOGC 16 05 221 331 G R61
HISTORICAL MODEL PIN COUNT SCHEMATIC RESISTANCE VALUE 1 RESISTANCE VALUE 2 TOLERANCE CODE PACKAGING

* Pb containing terminations are not RoHS compliant, exemptions may apply

DIMENSIONS in inches [millimeters]

TECHNICAL SPECIFICATIONS

PARAMETER	UNIT	SOGC16	SOGC20
Package Power Rating (max. at + 70°C)	W	1.6	2.0
TC Tracking (- 55°C to + 125°C)	ppm/°C	± 50	
Voltage Coefficient of Resistance:	ppm/V	< 50 typical	
Maximum Operating Voltage:	VDC	50	
Operating Temperature Range:	°C	- 55 to + 125	
Storage Temperature Range:	°C	- 55 to + 150	

MECHANICAL SPECIFICATIONS

Marking:	Model number, schematic number, value tolerance, pin 1 indicator, date code
Marking Resistance to Solvents:	Permanency testing per MIL-STD-202, Method 215
Maximum Solder Reflow Temperature:	+ 255 °C
Solderability:	Per MIL-STD-202, Method 208E
Terminals:	Copper alloy. Solder dipped terminal
Body:	Molded epoxy

IMPEDANCE CODES					
CODE	R ₁ (Ω)	R ₂ (Ω)	CODE	R ₁ (Ω)	R ₂ (Ω)
500B	82	130	141A	270	270
750B	120	200	181A	330	390
800C	130	210	191A	330	470
990A	160	260	221B	330	680
101C	180	240	281B	560	560
111C	180	270	381B	560	1.2K
121B	180	390	501C	620	2.7K
121C	220	270	102A	1.5K	3.3K
131A	220	330	202B	3K	6.2K

CIRCUIT APPLICATIONS

01 Schematic

15 or 19 resistors with one pin common

The SOGCxx01 circuit provides a choice of 15 or 19 nominally equal resistors, each connected between a common lead (16 or 20) and a discrete PC board pin. Commonly used in the following applications:

- MOS/ROM Pull-up/Pull-down
- Open Collector Pull-up
- "Wired OR" Pull-up
- Power Driven Pull-up
- TTL Input Pull-down
- Digital Pulse Squaring
- TTL Unused Gate Pull-up
- High Speed Parallels Pull-up

03 Schematic

8 or 10 isolated resistors

The SOGCxx03 circuit provides a choice of 8 or 10 nominally equal resistors with each resistor isolated from all others and wired directly across. Commonly used in the following applications:


- "Wired OR" Pull-up
- Power Driven Pull-up
- Powergate Pull-up
- Line Termination
- Long-line Impedance Balancing
- LED Current Limiting
- ECL Output Pull-down
- TTL Input Pull-down

05 Schematic

TTL dual-line terminator; pulse squaring, 14 or 18 pairs of resistors
(R₁ Resistors are common to leads 16 or 20)
(R₂ Resistors are common to leads 8 or 10)

The SOGCxx05 circuit contains 14 or 18 pairs of resistors. Each pair is connected between ground and a common line. The junctions of these resistor pairs are connected to the input leads.

The 05 circuits are designed for TTL dual-line termination and pulse squaring.



PERFORMANCE	
TEST	MAX. ΔR (TYPICAL TEST LOTS)
Power Conditioning	± 0.50 % ΔR
Thermal Shock	± 0.50 % ΔR
Short Time Overload	± 0.25 % ΔR
Low Temperature Operation	± 0.25 % ΔR
Moisture Resistance	± 0.50 % ΔR
Resistance to Soldering Heat	± 0.25 % ΔR
Shock	± 0.25 % ΔR
Vibration	± 0.25 % ΔR
Load Life	± 0.50 % ΔR
Terminal Strength	± 0.25 % ΔR
Insulation Resistance	10 000 Megohm (minimum)
Dielectric Withstanding Voltage	No evidence of arcing or damage (200 V RMS for 1 minute)



Disclaimer

All product specifications and data are subject to change without notice.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained herein or in any other disclosure relating to any product.

Vishay disclaims any and all liability arising out of the use or application of any product described herein or of any information provided herein to the maximum extent permitted by law. The product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein, which apply to these products.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay.

The products shown herein are not designed for use in medical, life-saving, or life-sustaining applications unless otherwise expressly indicated. Customers using or selling Vishay products not expressly indicated for use in such applications do so entirely at their own risk and agree to fully indemnify Vishay for any damages arising or resulting from such use or sale. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

Product names and markings noted herein may be trademarks of their respective owners.