


Thick Film Resistor Networks, Flat Pack



FEATURES

- Isolated and bussed schematics available
- 0.065" (1.65 mm) height for high density packaging
- Low temperature coefficient (- 55 °C to + 125 °C) ± 100 ppm/°C
- Hot solder dipped leads
- Highly stable thick film
- Wide resistance range
- All devices are capable of passing the MIL-STD-202, method 210, condition C "Resistance to Soldering Heat" test

STANDARD ELECTRICAL SPECIFICATIONS


GLOBAL MODEL	POWER RATING		CIRCUIT SCHEMATIC	MAXIMUM WORKING VOLTAGE (3) V _{DC}	TEMPERATURE (1) COEFFICIENT ± ppm/°C	TOLERANCE (2) ± %	RESISTANCE RANGE Ω	TCR TRACKING ± ppm/°C
	ELEMENT P _{25 °C} W	PACKAGE P _{25 °C} W						
DFP	0.25 0.15	0.65 0.65	11 12	75 75	100 100	1, 2, 5 1, 2, 5	10 to 1M 10 to 1M	50 50

Notes

- Consult factory for stocked values.
- (1) Temperature range: - 55 °C to + 125 °C.
- (2) ± 2 % standard, ± 1 % and ± 5 % available.
- (3) Continuous working voltage shall be $\sqrt{P \times R}$ or maximum working voltage, whichever is less.

TECHNICAL SPECIFICATIONS

11 Schematic




7 or 8 isolated resistors

The DFPxx11 provides the user with 7 or 8 nominally equal resistors with each resistor isolated from all others. Commonly used in the following applications:

- "Wired OR" pull-up
- Power driven pull-up
- Power gate pull-up
- Line termination
- Long-line impedance balancing
- LED current limiting
- ECL output pull-down
- TTL input pull-down

12 Schematic



13 or 15 resistors with one pin common

The DFPxx12 provides the user with a choice of 13 or 15 nominally equal resistors, each connected to a common pin (14 or 16). Commonly used in the following applications:

- MOS/ROM pull-up/pull-down
- Open collector pull-up
- "Wired OR" pull-up
- Power driven pull-up
- TTL input pull-down
- Digital pulse squaring
- TTL unused gate pull-up
- High speed parallel pull-up

GLOBAL PART NUMBER INFORMATION

New Global Part Numbering: DFP14121K00GD05 (preferred part number information)





GLOBAL MODEL	PIN COUNT	SCHEMATIC	RESISTANCE VALUE	TOLERANCE CODE	PACKAGING	SPECIAL
DFP	14 16	11 = Isolated 12 = Bussed	R = Ω K = kΩ M = MΩ 10R0 = 10 Ω 680K = 680 kΩ 1M00 = 1.0 MΩ	F = ± 1 % G = ± 2 % J = ± 5 %	E05 = Lead (Pb)-free, tube D05 = Tin/lead, tube	Blank = Standard (Dash number) (Up to 3 digits) From 1 to 999 as applicable

Historical Part Number Example: DFP1412102G (will continue to be accepted)

DFP	14	12	102	G	D05
HISTORICAL MODEL	PIN COUNT	SCHEMATIC	RESISTANCE VALUE	TOLERANCE CODE	PACKAGING

DIMENSIONS in inches (millimeters)




GLOBAL MODEL	DIMENSION A
DFP14	0.037 ± 0.010 (0.94 ± 0.25)
DFP16	0.012 ± 0.010 (0.30 ± 0.25)


TECHNICAL SPECIFICATIONS		
PARAMETER	UNIT	DFP14/16
Isolation resistance 11 schematic	MΩ	> 100
Voltage coefficient of resistance	ppm/V	< 50 typical
Maximum operating voltage	V _{DC}	75
Operating temperature range	°C	- 55 to + 125
Storage temperature range	°C	- 55 to + 150

MECHANICAL SPECIFICATIONS	
Marking	Model number, schematic number, value tolerance, pin 1 indicator, date code
Marking resistance to solvents	Permanency testing per MIL-STD-202, method 215
Solderability	Per MIL-STD-202, method 208E
Terminals	Per MIL-STD-1276 DFPxx11, DFPxx12 = type G (hot solder dipped). Hot solder dipped leads supplied as standard finish.
Body	Epoxy filled ceramic sandwich

11 Schematic



12 Schematic



PERFORMANCE		
TEST	CONDITIONS	MAX. ΔR (TYPICAL TEST LOTS)
Power conditioning	1.5 x rated power, applied 1.5 h "ON" and 0.5 h "OFF" for 100 h ± 4 h at + 25 °C ambient temperature	± 0.50 % ΔR
Thermal shock	5 cycles between - 65 °C and + 125 °C	± 0.50 % ΔR
Short time overload	2.5 x rated working voltage, 5 s	± 0.25 % ΔR
Low temperature operation	45 min at full rated working voltage at - 65 °C	± 0.25 % ΔR
Moisture resistance	240 h with humidity ranging from 80 % RH to 98 % RH	± 0.50 % ΔR
Resistance to soldering heat	Leads immersed in + 260° ΔC solder to within 1/16" of body for 10 s	± 0.25 % ΔR
Shock	Total of 18 shocks at 100 g's	± 0.25 % ΔR
Vibration	12 h at maximum of 20 g's between 10 Hz and 2000 Hz	± 0.25 % ΔR
Load life	1000 h at + 70 °C, rated power applied 1.5 h "ON", 0.5 h "OFF" for full 1000 h period. Derated according to the curve.	± 0.50 % ΔR
Terminal strength	1.5 pound pull for 30 s	± 0.25 % ΔR
Insulation resistance	10 000 MΩ (minimum)	-
Dielectric withstanding voltage	No evidence of arcing or damage (200 V _{RMS} for 1 min)	-



Disclaimer

ALL PRODUCT, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE TO IMPROVE RELIABILITY, FUNCTION OR DESIGN OR OTHERWISE.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product.

Vishay makes no warranty, representation or guarantee regarding the suitability of the products for any particular purpose or the continuing production of any product. To the maximum extent permitted by applicable law, Vishay disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Statements regarding the suitability of products for certain types of applications are based on Vishay's knowledge of typical requirements that are often placed on Vishay products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. Parameters provided in datasheets and/or specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein.

Except as expressly indicated in writing, Vishay products are not designed for use in medical, life-saving, or life-sustaining applications or for any other application in which the failure of the Vishay product could result in personal injury or death. Customers using or selling Vishay products not expressly indicated for use in such applications do so at their own risk and agree to fully indemnify and hold Vishay and its distributors harmless from and against any and all claims, liabilities, expenses and damages arising or resulting in connection with such use or sale, including attorneys fees, even if such claim alleges that Vishay or its distributor was negligent regarding the design or manufacture of the part. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay. Product names and markings noted herein may be trademarks of their respective owners.

Material Category Policy

Vishay Intertechnology, Inc. hereby certifies that all its products that are identified as RoHS-Compliant fulfill the definitions and restrictions defined under Directive 2011/65/EU of The European Parliament and of the Council of June 8, 2011 on the restriction of the use of certain hazardous substances in electrical and electronic equipment (EEE) - recast, unless otherwise specified as non-compliant.

Please note that some Vishay documentation may still make reference to RoHS Directive 2002/95/EC. We confirm that all the products identified as being compliant to Directive 2002/95/EC conform to Directive 2011/65/EU.